



Sparkle Power Inc.

A Leading Power Supply manufacturer
Web site: www.sparklepower.com



FSP250-60ATV (For Pentium 4 and Athlon XP) **250 Watts ATX12V Switching Power Supply**

Features

- Complied with ATX and ATX12V standard
- High efficiency and reliability
- Remote On/Off function
- Internal 12V DC fan included
- Noise Killer (Thermal fan speed control function)
- Low noise and ripple
- Complies with FCC part 15 subpart J class B and CISPR 22 Class B
- Output over voltage, short circuit, and over current protection
- 100% Hi-pot, ATE, and burn-in tested
- Re-settable power shut down
- Approved by UL 1950, CSA C22.2 Level 3, TUV EN 60950, NEMKO (CB Report)

Input Characteristics

Input Range: 95~132/190~264V AC, Manual-select
Frequency: 47~63Hz
Input Current: 10A (RMS) @115V AC, 5A (RMS) @230VAC
Inrush Current: 60A Max for 115V AC, 90A Max for 230V AC

Output Characteristics

Output Voltage	Minimum Load	Maximum Load	Load Reg.	Line Reg.	Ripple & Noise
+3.3V	0.3A	12.12/20A	± 5%	± 1%	50mV P-P
+5V	0.5A	27/21.8A	± 5%	± 1%	50mV P-P
+12V	0.0A	17A	± 5%	± 1%	120mV P-P
-5V	0.0A	0.3A	± 10%	± 2%	120mV P-P
-12V	0.0A	0.8 A	± 10%	± 2%	120mV P-P
+5Vsb	0.0A	2.0 A	± 5%	± 1%	50mV P-P

*+5V and +3.3V total output not exceed 175W

*When +3.3V is load to 20A, the +5V maximum load is 21.8A

*When +3.3V is load to 12A, the +5V maximum load is 27A

*+3.3V, +5V, and +12V total output not exceed 230W

Specification

- **Temperature Range:** Operating 0° C ~ +25° C on full load; storage & shipping -20° C ~ +65° C
- **Humidity:** 90% on operating and 95% on storage
- **Dielectric Withstand:** Primary to frame ground 1800V AC for 1 second
- **Efficiency:** 65% at minimum measured at nominal AC main voltage and frequency with maximum load on all output
- **Rise Time:** Less than 20ms on all output
- **Hold-up Time:** 16.6ms minimum at 115V/60Hz; 20ms minimum at 230V/50Hz input voltage
- **Power Good Signal:** Power on delay time 100 ms to 500 ms, off delay 1ms minimum (TTL and CMOS compatible)
- **Leakage Current:** Less than 3.5mA
- **MTBF:** 100,000 hours on maximum load at +25° C degree
- **Dimension (WxHxL):** 150x86x140mm/5.9"x3.4"x5.5" inches

Sparkle Power Inc.

Main Office

1000 Rock Avenue
San Jose, CA 95131
TEL: 408-519-8888
FAX: 408-519-9999
E-MAIL: info@sparklepower.com

Sparkle Power Inc.

Los Angeles Office

17071 Green Drive
City of Industry, CA 91745
TEL: 626-839-7180
FAX: 626-839-3395

Sparkle Power Inc.

Colorado Office

1316 Indian Paintbrush Lane
Longmont, CO 80503
TEL: 303-776-3281
FAX: 303-776-7645