

PRODUCT NUMBER

SEE TABLE

68402-XXX-LF

LEAD FREE OPTION

PACKAGING OPTION NOTE 6. OMIT IF NOT REQUIRED

NO OF POSITIONS PER ROW

PLATING CODE

BASE PART NUMBER







FIGURE 1
SMALL CAP FOR LESS THAN 6 POSITION

mat'l. code				surface		tolerance		projection		product family			
				ISO 1302		ISO 406 ISO 1101				DUBOX			
ltr		ecn no	dr	date		tolerances unless otherwise specified							
V		EX- N-17326	ZK	03/28/14		angles		linear		.XX±.01/.3		INCH/MM	
W		EX-N-18093	Henry	06/26/14						.XXX±.005/.13		DUBOX SURFACE MOUNT S/R	
						0°±2°				.XXXX±.0020/.051		VERTICAL CARD CONNECTOR	
R		V03-0309	HTB	04/28/03		dr		J. SHEREINER		11/07/90		dwg no	
S		V05-0463	DPU	06/28/05		enr		M. HAHN		11/07/90		sheet. 1 of 5	
T		M07-0114	AGS	02/15/07		chr		M. HAHN		11/07/90		size	
U		M07-0198	MHT	4/24/07		appd		M. HAHN		11/07/90		A3	
												type	
sheet		revision		W		W		W		W		Product	
index		sheet		1		2		3		4		Customer	
												Drawing	




FIGURE A
TOP ENTRY
.025/.64 SQ PIN




FIGURE B
BOTTOM ENTRY (THROUGH PWB)
.025/.64 SQ PIN

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family DUBOX		
ltr	ecn no	dr	date	tolerances unless otherwise specified		INCH/MM scale 5:1	title DUBOX SURFACE MOUNT S/R VERTICAL CARD CONNECTOR		
W				angles	linear				
				0°±2°	.XX±.01/.3 .XXX±.005/.13 .XXXX±.0020/.051				
				dr	J. SHEREINER 11/07/90	FCI	dwg no	sheet. 2 of 5	size
				enr	M. HAHN 11/07/90		68402		A3
				chr	M. HAHN 11/07/90				
				appd	M. HAHN 11/07/90				
sheet index	revision			sheet			type Product Customer Drawing		

PRODUCT NO NOTE 14	PLATING CONTACT AREA NOTE 16	PLATING SOLDER TAIL	MATERIAL REF.
68402-2XX	15u"/.38u Au OR GXT MIN OVER 50u"/1.27u NI MIN	100μ"/160μ" SN 2.54μ/4.06μ	NOTE 3 & 4
68402-3XX	30u"/.76u Au OR GXT MIN OVER 50u"/1.27u NI MIN	100μ"/160μ" SN 2.54μ/4.06μ	NOTE 3 & 4
68402-4XX	100u"/2.54u Sn MIN OVER 50u"/1.27u NI	100μ"/160μ" SN 2.54μ/4.06μ	NOTE 3 & 4
68402-6XX	30u"/.76u Au OR GXT MIN OVER 50u"/1.27u NI MIN	100μ"/160μ" SN 2.54μ/4.06μ	NOTE 3 & 4
68402-8XX	30u"/.76u Au MIN OVER 50u"/1.27u NI MIN	100μ"/160μ" SN 2.54μ/4.06μ	NOTE 3 & 4

OBSOLETE

mat'l. code				surface ISO 1302 ☒	tolerance ISO 406 ISO 1101	projection 	product family DUBOX
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
W				angles	linear		DUBOX SURFACE MOUNT S/R
					.XX±.01/.3		VERTICAL CARD CONNECTOR
				0°±2°	.XXX±.005/.13		
					.XXXX±.0020/.051	scale 5:1	
				dr	J. SHEREINER 11/07/90		dwg no
				enr	M. HAHN 11/07/90		sheet. 3 of 5
				chr	M. HAHN 11/07/90		size
				appd	M. HAHN 11/07/90		A3
sheet	revision						type
index	sheet						Product Customer Drawing

PRODUCT NUMBER

SEE TABLE

NOTES:

- ①. TERMINAL MATERIAL: PHOSPHOR BRONZE.
EXTRA HARD
2. RECOMMENDED APPLICATION DATA:
 - A. RECOMMENDED SOLDER PAD PATTERN IS SHOWN IN FIGURE A & B.
 - B. ALL MATING PINS TO BE .025/.64 SQUARE ON TRUE CENTER OF GIVEN TERMINAL SPACING. WITHIN .015/.38 DIA.
 - C. SUGGESTED MATING PIN LENGTH $.210 \pm .010$ [5.33±.51]
- ③. HOUSING MATERIAL: P.P.S., FILLED.
FLAME RETARDANT PER UL 94 V-0.
THIS PART WILL WITHSTAND EXPOSURES TO 260°C
PEAK TEMPERATURE FOR 20 SECONDS IN WAVE SOLDER,
INFRA-RED OR VAPOR PHASE SOLDER PROCESS.
- ④. PRESTAMPED POST PLATED TERMINAL.
5. FCI, FCI PART NUMBER AND DATE CODE
TO BE MARKED ON TUBE LABEL.
- ⑥. ADD SUFFIX 'P' TO DASH NUMBER AS FOURTH DIGIT FOR
TAPE & REEL PACKAGING.
ADD SUFFIX 'W' TO DASH NUMBER AS WITHOUT CAP ASSEMBLY
FOR TAPE & REEL PACKAGING.
7. TAPE AND REEL PACKAGING PER GES-14-334.
- ⑧. VACUUM CAP MATERIAL: L.C.P., FLAME RETARDANT UL 94 V-0.
COLOR: BLACK
- ⑨. TAPE AND REEL PACKAGING FOR 24mm WIDE AND BELOW HAVE
PILOT HOLES ON ONE SIDE OF TAPE ONLY. SIZES ABOVE 24mm
HAVE PILOT HOLES ON BOTH SIDES OF TAPE.
- ⑩. TAPE & REEL PACKAGING 32mm TAPE WIDTH, WITH 12mm POCKET PITCH.
- ⑪. MAXIMUM LENGTH OF CONNECTOR FOR TAPE AND REEL PACKAGING IS
2.50 INCHES LONG /63.5mm
- ⑫. PART NUMBER WITH "U" SUFFIX IS FOR SAWING PURPOSES ONLY.
13. STANDARD TUBE PACKAGE PER BUS-14-097/3.
- ⑭. ADD LF SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
15. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY
REGULATION AS DESCRIBED IN GS-22-008.
- ⑮. PLATING OPTIONS:
MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.

VACUUM PICK-UP CAP
CENTRALLY LOCATEDDUBOX VERTICAL RECEPTACLE
DOUBLE ROW.157[3.99]
NOTE 9

.069[1.75]

TAPE WIDTH
NOTE 10POCKET PITCH
NOTE 10FIGURE 2
TAPE & REEL PACKAGING

mat'l. code				surface ISO 1302	tolerance ISO 406 ISO 1101	projection INCH/MM	product family DUBOX	
ltr	ecn no	dr	date	tolerances unless otherwise specified		INCH/MM	title	
W				angles	linear		DUBOX SURFACE MOUNT S/R VERTICAL CARD CONNECTOR	
				0°±2°	.XX±.01/.3 .XXX±.005/.13 .XXXX±.0020/.051	scale 5:1	dwg no	sheet. 4 of 5 size
				dr	J. SHEREINER 11/07/90	FCI	68402 A3	
				enr	M. HAHN 11/07/90			
				chr	M. HAHN 11/07/90			
				appd	M. HAHN 11/07/90			
sheet index	revision sheet						type Product Customer Drawing	

FCI

Copyright FCI

FCIconnect.com

PRODUCT NO.	NO. OF POSITIONS	C DIM	D DIM	TAPE & REEL PACKAGING	LF OPTIONS
68402-Y02	1 X 2	.100/2.540	.217/5.511	NO	NOTE 14
-Y03	1 X 3	.200/5.080	.317/8.051	NO	
-Y04	1 X 4	.300/7.620	.417/10.591	NO	
-Y05	1 X 5	.400/10.160	.517/13.131	NO	
-Y06	1 X 6	.500/12.700	.617/15.671	NO	
-Y07	1 X 7	.600/15.240	.717/18.211	NO	
-Y08	1 X 8	.700/17.780	.817/20.751	NO	
-Y09	1 X 9	.800/20.320	.917/23.291	NO	
-Y10	1 X 10	.900/22.860	1.017/25.831	NO	
-Y11	1 X 11	1.000/25.400	1.117/28.371	NO	
-Y12	1 X 12	1.100/27.940	1.217/30.911	NO	
-Y13	1 X 13	1.200/30.480	1.317/33.451	NO	
-Y14	1 X 14	1.300/33.020	1.417/35.991	NO	
-Y15	1 X 15	1.400/35.560	1.517/38.531	NO	
-Y16	1 X 16	1.500/38.100	1.617/41.071	NO	
-Y17	1 X 17	1.600/40.640	1.717/43.611	NO	
-Y18	1 X 18	1.700/43.180	1.817/46.151	NO	
-Y19	1 X 19	1.800/45.720	1.917/48.691	NO	
-Y20	1 X 20	1.900/48.260	2.017/51.231	NO	
-Y21	1 X 21	2.000/50.800	2.117/53.771	NO	
-Y22	1 X 22	2.100/53.340	2.217/56.311	NO	
-Y23	1 X 23	2.200/55.880	2.317/58.851	NO	
-Y24	1 X 24	2.300/58.420	2.417/61.391	NO	
-Y25	1 X 25	2.400/60.960	2.517/63.931	NO	
68402-Y26	1 X 26	2.500/63.50	2.617/66.47	NO	
68402-Y26U	1 X 26	2.500/63.50	2.617/66.47	NO	
68402-Y06P	1 X 6	.500/12.700	.617/15.671	YES	
68402-Y27-Y50	---	---	---	NO	NOTE 12 NOTE 6 NOT AVAILABLE

mat'l. code

litr ecn no dr date

w

angles

linear

0°±2'

dr J. SHEREINER 11/07/90

enr M. HAHN 11/07/90

chr M. HAHN 11/07/90

appd M. HAHN 11/07/90

sheet index

revision sheet

surface ISO 1302

tolerance ISO 406 ISO 1101

tolerances unless otherwise specified

.XX±.01/.3

.XXX±.005/.13

.XXXX±.0020/.051

projection

INCH/MM

scale 5:1

product family DUBOX

title DUBOX SURFACE MOUNT S/R VERTICAL CARD CONNECTOR

dwg no 68402

sheet. 5 of 5

size A3

type Product Customer Drawing

FCI

STATUS:Released

Printed: Jun 27, 2014