

PRODUCT FAMILIES

Pin Headers and Sockets

Clips and Insulators

Banana Plugs and Jacks

Grabbers, Probes and Spade Terminals

Test Leads and Patch Cords

Plunger Test Leads

Banana Plug Test Leads

Alligator Clip Patch Cords

Coaxial Cable Assemblies

DMM Kits

ISO 9001:2000

Alligator Clip Patch Cords

Insulated Mini-Alligator Lead Set



Model # BU-00285

- Material: Clip: nickel-plated steel with PVC insulators; Hook-up Wire: #22 (19/34) AWG copper with 105°C PVC insulation
- Length: 18" (.46m)
- Colors: Includes 2 each: Black, Red, Yellow, Green, White
- Rating: Hands free testing at 300V, 5 Amp

TOOL

SEARCH TOOLS

MUELLER OR DISTRIBUTOR STOCK SEARCH

PART #

SEARCH

TOOL

CROSS COMPETITOR PART #

Choose a Brand

PART #

SEARCH

TOOL

MeterMate® DMM ACCESSORY SELECTOR

Select Meter Make

Select a Make First

TOOL

BUILD A PCB HEADER OR SOCKET

OVER 10,000 IN STOCK!

GO

Insulated Alligator Lead Set



Model # BU-00286

- Material: Clip: nickel-plated steel with PVC insulators; Hook-up Wire: #22 (19/34) AWG copper with 105°C PVC insulation
- Length: 12" (.3m)
- Colors: Includes 1 each: Black, Red, Yellow, Green, White
- Rating: Hands free testing at 300V, 7 Amp

Insulated Alligator Lead Set



Model # BU-00287

- Material: Clip: nickel-plated steel with PVC insulators; Hook-up Wire: #22 (19/34) AWG copper with 105°C PVC insulation
- Length: 18" (.46m)
- Colors: Includes 2 each: Black, Red, Yellow, Green, White
- Rating: Hands free testing at 300V, 7 Amp

Insulated Alligator Clips on Both Ends



Model # BU-3030-A-**-*

- Material: Alligator Clip: nickel-plated steel with PVC insulator; Hook-up Wire: #20 (41/36) AWG tinned copper with 105°C PVC insulation
- **Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
- *Std. Colors: -0 Black, -2 Red
- Rating: Hands free testing at 300V, 10 Amps

Insulated Alligator Clips on Both Ends - Coiled Cord



Model # BU-3030-C-24-*

- Material: Clip: nickel-plated steel alligator with insulator (BU-60 and BU-62-*); Coiled Cord: single conductor 18AWG wire with 4mm O.D.
- 24" (.6m) retracted, 120" (3.) extended
- *Std. Colors: -0 Black, -2 Red
- Rating: Hands free testing at 300V, 15 Amps

Insulated Alligator Clip to Stackable Dual Banana Plug with RG58



Model # BU-3070-C-**-0

- Material: Alligator Clip: nickel-plated steel with PVC insulator; Double Banana Plug: ABS housing, brass body and beryllium copper, nickel-plated, nine-leaf cage spring; Coaxial Cable: Shielded RG58C/U, MIL-C-17F, 50 ohm
- **Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
- Rating: Hands free testing at 300 VRMS

Insulated Mini-Alligator Clip on Both Ends



Model # BU-3131-A-**-*

- Material: Alligator Clip: nickel-plated steel with PVC insulator; Hook-up Wire: #20 (41/36) AWG tinned copper with 105°C PVC insulation
- **Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
- *Std. Colors: -0 Black, -2 Red
- Rating: Hands free testing at 300 VAC, 5 Amps

Shrouded Banana Plug to Piercing Clip - Silicone



Model # JP-7505-83-**-*

- Piercing clips are J.S. Popper brand
- Material: Piercing Clip: JP-8783; Banana Plugs: nickel-plated brass body, nickel-plated beryllium copper spring; Hook-up Wire: #18 AWG, silicone insulator
- **Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m)
- *Std. Colors: -0 Black, -2 Red, -4 Yellow, -6 Blue
- Rating: 300V, 3 Amp

Ultra-Flex Test Lead Wires

Model # W-I-M-18-*

- Material: Wire: #18 AWG, silicone
- *Std. Colors: -0 Black, -2 Red, -4 Yellow, -5 Green, -6 Blue, -9 White
- Rating: 3kV, 22 Amp