


SSA-118-W-G



SSA-115-S-T



SSA-108-W-T-RA

(2,54 mm) .100"

SSA SERIES

LOW COST SOCKET STRIPS

Mates with:
TS, HTS, BBS,
BBL, BHS

SPECIFICATIONS

For complete specifications
see www.samtec.com?SSA

Insulator Material:

Black PET Polyester

Contact Material:

Phosphor Bronze

Plating:

Au or Sn over

50μ" (1,27 μm) Ni

Flammability Rating:

UL 94V-O

Insulation Resistance:

5000 MΩ min

Operating Temp Range:

-55°C to +125°C with Gold

-55°C to +105°C with Tin

Heat Deflection Temp:

215°C @ 264 psi (1,8 MPa)

Dielectric Withstanding

Voltage:

1000 VRMS

Contact Resistance:

10 mΩ

Lead Size Range:

(0,38 mm) .015" to

(0,56 mm) .022" DIA

and most IC leads

Insertion Depth:

(1,27 mm) .050" to

(3,30 mm) .130"

Insertion Force:

(Single contact only)

10 oz (2,78 N) average

Withdrawal Force:

(Single contact only)

5 oz (1,39 N) average

RoHS Compliant:

Yes

Lead-Free Solderable:

Wave only

RECOGNITIONS

For complete scope of
recognitions see
www.samtec.com/quality



FILE NO. E111594





Note: Some lengths, styles
and options are non-standard,
non-returnable.

SSA

1

NO. OF
POSITIONSLEAD
STYLEPLATING
OPTIONRA
OPTION

01 thru 32

- S
= P.C.- G
= 10μ" (0,25 μm)
Gold- T
= Matte Tin- RA
= Right Angle- W
= Wire Wrap

High reliability
double side-wipe
contacts

Snap-Strip
feature

UL Rated 94 V-O
High Temp PET
Polyester Body

Selectively plated
for lower contact
resistance

Standoffs allow for
easy board cleaning

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685