

SMS-122-01-G-S

SLM-134-01-G-D

(1,27 mm) .050"

SLM, SMS SERIES

THROUGH-HOLE MICRO SOCKETS

SPECIFICATIONS

For complete specifications see www.samtec.com?SLM or www.samtec.com?SMS

Insulator Material:

SLM: Black Glass Filled Polyester

SMS: Black LCP

Contact Material:

Phosphor Bronze

Plating:

Au or Sn over

50µ" (1,27 µm) Ni

Current Rating (SLM/TMS):

5.2 A per pin

(1 pin powered per row)

Current Rating (SMS/TMS):

5.0 A per pin

(1 pin powered per row)

Operating Temp Range:

-55°C to +125°C with Gold

-55°C to +105°C with Tin

Contact Resistance:

10 mΩ

Insertion Depth:

SLM: (2,03 mm) .080"

to (3,05 mm) .120"

SMS: (3,43 mm) .135" to

(6,35 mm) .250" with

(0,38 mm) .015" wipe

Insertion Force:

(Single contact only)

8 oz (2,22 N) avg.

Withdrawal Force:

(Single contact only)

6 oz (1,67 N) avg.

RoHS Compliant:

Yes

Processing:

Lead-Free Solderable:

SLM: Wave Only

SMS: Yes

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



FILE NO. E111594

FILE NO. 000071_0_000 (SAS ONLY)

SLM

1

NO. PINS PER ROW

01

PLATING OPTION


ROW OPTION

Mates with:

HTMS, TMS, MTMS, DWM,

HDWM, FTR, HMTMS

01 thru 50



—L
= 10µ" (0,25 µm) Gold on contact,
Matte Tin on tail

—G
= 20µ" (0,51 µm) Gold on contact,
Gold flash on balance

—S
= Single
Row

—D
= Double
Row

ALSO AVAILABLE (MOQ Required)

- Other platings
Contact Samtec.

SMS

1

NO. PINS PER ROW

LEAD STYLE

PLATING OPTION

ROW OPTION

Mates with:


HTMS, TMS, MTMS,

DWM, HDWM,

FTR, TML,

ZML, HMTMS

01 thru 50



Specify
LEAD
STYLE
from
chart

—L
= 10µ" (0,25 µm)
Gold on contact,
Matte Tin on tail

—G
= 10µ" (0,25 µm)
Gold

—S
= Single
Row

—D
= Double
Row

LEAD STYLE	A
—01	(2,54) .100
—02	(4,83) .190

ALSO AVAILABLE (MOQ Required)

- Other platings
Contact Samtec.

Note: Some lengths, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
 SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
 SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
 SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
 SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685