

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0082243405](#)
Status: **Obsolete**
Description: 2.00mm (.079") Pitch Flextran High Flex Life Cable - 24 AWG (19 x 36) Stranded, Topcoat, 5 Circuits, Reel 30.48m (100.0') Length

Documents:
[Drawing \(PDF\)](#)

Agency Certification

CSA	LR61126
UL	E61522

General

Product Family	Cable
Series	24473
Crimp Quality Equipment	Yes
Product Name	Flextran High Flex Life, Ribbon

Physical


Cable Length	30.48m (100.0')
Circuits (Loaded)	5
Insulation	PVC
Packaging Type	Reel
Pitch - Termination Interface	2.00mm (.079")
Temperature Range - Operating	-20°C to +105°C
Wire Size AWG	24
Wire/Cable Type	(19x36) Stranded, Topcoat

Electrical

Current - Maximum per Contact	N/A
Voltage - Maximum	300V

Material Info

Old Part Number	24473-05-100B
-----------------	---------------



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[24473Series](#)

Use With
[30452](#) , [52484](#)