


THESE DRAWINGS ARE THE PROPERTY OF QUALTEK ELECTRONICS AND NOT TO BE REPRODUCED FOR OR COMMUNICATED TO A THIRD PARTY WITHOUT THE EXPRESS WRITTEN PERMISSION OF AN OFFICER OF QUALTEK ELECTRONICS.

| REVISION |                        |          |          |
|----------|------------------------|----------|----------|
| REV.     | DESCRIPTION            | DATE     | APPROVED |
| B        | RoHS Compliancy        | 06-01-06 | DP       |
| C        | Updated Specifications | 09-18-08 | LY       |
|          |                        |          |          |



NOTES:

1. RATING: 10A 125VAC
2. CORDAGE: SPT-1, 18/2, 105°C, 300V
3. CORD LENGTH: 609.6mm
4. TERMINATION: BLUNT CUT
5. APPROVALS: UL, cUL
6. RoHS COMPLIANT

CONTROLLED

| Dim<br>range<br>(mm) | Tolerance<br>+/-<br>(mm) | Qualtek Electronics Corp.<br>FAN-S DIVISION |                   |                 |
|----------------------|--------------------------|---------------------------------------------|-------------------|-----------------|
|                      |                          | Part Number: 07145-24                       | RoHS<br>Compliant |                 |
| 0-1                  | 0.15                     | Description:<br>MOLDED FAN CORD FEMALE 45°  |                   |                 |
| 1-6                  | 0.20                     |                                             |                   |                 |
| 6-18                 | 0.30                     |                                             | UNIT: mm          | REV: C          |
| 18-50                | 0.50                     |                                             |                   |                 |
| 50-120               | 0.70                     | Drawn / Date                                | Checked / Date    | Approved / Date |
| 120-250              | 0.90                     | K.Huang<br>08-21-98                         | 08-21-98          | JJH / 08-21-98  |
| 250-500              | 1.20                     |                                             |                   |                 |