

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/22/04	

6

5

4



3

2

1

APPROVED: _____

DATE: _____ TITLE: _____



Plug Dimensions			
POSITIONS	A	B	D
9	1.212 [30.80]	.984 [24.99]	.666 [16.92]
15	1.541 [39.14]	1.312 [33.32]	.994 [25.25]
25	2.086 [53.00]	1.852 [47.04]	1.534 [38.96]
37	2.729 [69.32]	2.500 [63.50]	2.182 [55.42]

SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Shell: Steel, Zinc plated

Plating:

5u" Gold nom over Nickel underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 5 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 5000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 1000 VAC for 1 minute

Temperature Rating:

Operating temperature: -65°C to +125°C

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

DUAL PORT D-SUB, RIGHT ANGLE

MALE / MALE, XX POSITION, .625" PORT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		TITLE	
INCHES		DUAL PORT D-SUB, RIGHT ANGLE	
HOLES		MALE / MALE, XX POSITION, .625" PORT	
.X ± .10 ØXX ± .10		DRAWN	
.XX ± .020 ØXX ± .015		SS	
.XXX ± .015 ØXXX ± .010		11/22/04	
APPROVALS		DATE	
DRAWN		SS	
CHECKED		11/22/04	
APPROVED		11/22/04	
SIZE		PART NO.	
X		DPD-XX-11-C3	
REF:		SCALE: NTS	
SHEET 1 OF 1		REV.	