

SPECIFICATIONS SHEET

PRODUCT TYPE : MAGNETIC TRANSDUCER

PRODUCT SERIES : 41.T70P015H-LF

COLOR : BLACK

ELECTRICAL SPECIFICATIONS

MODEL NO.	41.T70P015H-LF
OPERATING VOLTAGE RANGE (V)	1.0 ~ 5.0
RATED VOLTAGE (V)	1.5
+ MAX. RATED CURRENT (mA)	30.0
COIL RESISTANCE (Ω)	16.0 +/- 4.5
COIL IMPEDANCE (Ω)	40.0
+ MIN. SOUND OUTPUT AT 10 cm (dBA)	85.0
RESONANT FREQUENCY (Hz)	2048
OPERATING TEMPERATURE (° C)	- 20 ~ + 60
TERMINAL	PIN
HOUSING MATERIAL	NORYL
WEIGHT (g)	2.0

+ Value applying rated voltage resonant frequency, 1/2 duty , square wave

* Value applying resonant frequency, 1/2 duty , square wave , measuring current 60uA

DIMENSIONS

UNIT : mm

