

## STRADA-C2 LENS FOR NICHIA 119 / 219 LEDs




- Extremely wide BATWING design with very and uniform light distribution.
- Comes with integrated positioning pins.
- Lens material optical grade PMMA with high UV and temperature resistance (105°C/220°F). Allows use of high current and temperature conditions.
- Best available optical efficiency, approximately 92%.
- Fastening to heat sink with or without PU foam adhesive tape of automotive grade, please select which suits the best for your needs.
- Please check fastening details from this link:  
([http://www.ledil.com/datasheets/DataSheet\\_TAPE.pdf](http://www.ledil.com/datasheets/DataSheet_TAPE.pdf))

### LENS TYPES


| NAME           | ORDERING CODE              | FWHM Angle |
|----------------|----------------------------|------------|
| Strada-C2      | C11252_Strada-C2-N19       | ±62°       |
| Strada-C2-TAPE | CA11253_Strada-C2-N19-tape | ±62°       |

## MEASUREMENT DATA & DRAWING

Relative Intensity of C11252\_Strada-C2-N119



© Ledil Oy – PRELIMINARY - Subject to change without prior notice



© Ledil Oy – PRELIMINARY - Subject to change without prior notice

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Ledil:

[C11252\\_STRADA-C2](#) [CA11253\\_STRADA-C2](#) [C11252\\_Strada-C2-N119](#) [CA11253\\_Strada-C2-N119-tape](#)