


2014




Professional Pliers/Cutters & Crimpers



Complete Pliers/Cutters Program



Insulated Pliers/Cutters

Description	Page
 Insulated Lineman's Pliers	4
 Insulated Combination Pliers	4
 Insulated Heavy Duty Diagonal Cutters	5
 Insulated High Leverage Diagonal Cutters	5
 Insulated Serrated Edge Cutters	5
 Insulated Pliers - Long & Flat Nose	6
 Insulated Pliers - Bent & Round Nose	6
 Insulated Wire Stripper	6
 Insulated Waterpump Pliers	7
 Insulated Pliers Sets	8
Insulated Belt Pack Pouch Sets	7

Insulated Adjustable Wrenches

Description	Page
 Insulated Adjustable Wrenches 8", 10", 12", 15" OAL	9


Insulated Industrial Pliers/Cutters

Description	Page
 Insulated Lineman's Pliers	9
 Insulated Long Nose Pliers	9
 Insulated Diagonal Cutters	9
 Insulated High Leverage Cutters	10
 Insulated Serrated Edge Cutters	10
 Insulated Stripping Pliers	10
 Insulated Crimping Pliers	10
 Insulated Industrial Tool Sets	10-11

Insulated Inomic Pliers

Description	Page
 Insulated Inomic Pliers Inomic Combo Pliers Inomic Long Nose Pliers Inomic Diagonal Cutters	8

Vinyl Grip Pliers & Cutters

Description	Page
 Combination Pliers	12
 Stripping Pliers	13
 Long Nose Pliers	13
 Bent Long Nose Pliers	13
 Long Flat Nose Pliers	13
 Long Round Nose Pliers	13
 Adjustable Pliers	14
 Cable Cutters	15
 Diagonal Cutters	15
 High Lev. End Cutting Nippers	16
 Carpenter's End Nippers	16
 Mason Nippers	16
 Retaining Ring Pliers	18-19
 MagicTip Safety Notched Ring Pliers	20-21
 Crimping Pliers	15,45
 Standard Pliers/Cutters Sets	17
 Belt Pack Pouch Sets	17
 Molded Grip Shears	16



Pipe Wrenches Narrow Style

Description	Page
 Narrow Style Pipe Wrenches S-Jaw, 45° Angle, 90° Angle	22

ComfortGrip Crimpers

Description	Page
 Ratchet End Sleeve Crimper	23
 Ratchet Crimper For Standard Connectors	23
 Ratchet Crimper Push On Terminals	23
 Ratchet Crimper For Eye Terminals	23




Industrial SoftGrip Pliers & Cutters

Description	Page
 Combination Pliers	24
 Linemans Crimpers	24
 Stripping Pliers	24
 Long Nose Pliers	25
 Bent Long Nose Pliers	25
 Flat Nose Pliers	25
 Long Round Nose	25
 Diagonal Cutters	26
 Cable Cutters	26
 Adjustable Pliers	26
 Industrial SoftGrip Tool Sets	27


Precision Electronic Pliers/Cutters

Description	Page
 Electronic Diagonal Cutters Wide Pointed Head	28
 Electronic Diagonal Cutters Wide Shape with Wire Holding Spring	28
 Electronic Diagonal Cutters Narrow Shape	28
 Electronic Diagonal Cutters Full Flush Cutters w/Wire Trapping Spring	29
 Electronic Diagonal Cutters 48° Front Cutter/Long Nose Pliers	29
 Electronic Diagonal Cutters Oblique 30° Cutting Nippers	29
 Electronic Diagonal Cutters Short Nose Precision Pliers	29
 Electronic Stripping Pliers	25,29

ESD Safe Pliers/Cutters

Description	Page
 ESD Safe Diagonal Cutters Small, Wide & Oval Tapered Head	30-32
 ESD Safe Diagonal Cutters With Carbide Cutters	32
 ESD Safe Oblique Angled Cutters	33
 ESD Safe Oblique Front Cutters	33
 ESD Safe End Cutters	34
 ESD Safe Snipe/Bent Nose Pliers	34
 ESD Safe Needle Nose Pliers	34
 ESD Safe Short Round Nose	35
 ESD Safe Short Flat Nose	35
 ESD Safe Tool Sets	33,35

ESD Safe Protturn Pliers & Cutters

Description	Page
 Protturn Wire Strippers 30 to 20 AWG	36
 Protturn Pliers Long, Flat, Bent, Round Nose	36-37
 Precision Cutters/Flush Cut 21° & 45° Angle	37-38

Stripping & Crimping Tools

Description	Page
 PortaCrimp Frame	39
 PortaCrimp Dies	40-42
 PortaCrimp Sets	39
 Professional Crimp Tools	42
 Crimping Tools	43-44
 Self Adj. Cut & Strip Tools	45

Wiha Insulated Pliers & Cutters

Tools Meet 10,000 Volt
Test Standards
Certified to 1000 Volt ac
or 1500 Volt dc

Chrome finish
for long lasting
corrosion
protection



Safety slip
guard

1000V

Cutters additionally
induction hardened

Insulation Standards:

EN/IEC 60900, ASTM F-1505-01,
VDE 0682/part 201, NFPA70E and CSA

Wiha Canvas Pliers Holster



- Canvas holster with belt clip and belt loop
- Security pliers strap
- Screwdriver holder in the front

91256 Pliers Canvas Holster

Item	Width	Height		
No.	Size	Size	lbs.	pkg.
91256	3.5 x	6.75	.15	1

Insulated Lineman's Pliers With Crimpers

1000volt

5-in-1 Lineman's Pliers



With lower crimping jaw

SHOP

32821 Insulated Lineman's Pliers "5-in-1" Professional Design

Insulation According to EN/IEC, ASTM, NFPA70E & CSA, up to 1000 Volt. Individually Tested. Deep cut radius conduit jaws for non-slip gripping. Extra long induction hardened precision matched cutting edges. Lower crimping jaw accepts most standard non-insulated electrical connectors. Large head with square anvil surface on each side. Made from premium C70 tool steel forgings. 64HRC cutting edges.

Item	mm	Inch	Cutting Capacity Copper AWG	Pkg.	lbs.
No.					
32821	225	9.0	#4	1	.88

Insulated Combination Lineman's Pliers

Serrated jaws

1000volt



SHOP

328 Combination Pliers. Insulation According to VDE 0682/part

201, EN/IEC 60900, ASTM F-1505-01, NFPA70E and CSA, up to 1000 Volt. Individually Tested. DIN ISO 5746 Extra long cutting edge for flat & round cables. Cutting edges additionally induction hardened to approx. 64HRC. Special C70 tool steel forgings, Chrome finish. Use for gripping and holding as well as cutting soft and hard wires and cables.

Item	mm	Inch	Cutting Capacity Copper AWG	Pkg.	lbs.
No.					
32814	160	6.3	#10	1	.53
32816	180	7.0	#9	1	.58
32818	200	8.0	#8	1	.72

Insulated High Leverage Combination Pliers

1000volt



Lineman's

SHOP

32820 High Leverage Combination Pliers. Insulation According to

EN/IEC 60900, ASTM F-1505-01, NFPA70E and CSA, up to 1000 Volt. Individually Tested. DIN ISO 5746 Extra long cutting edge for flat and round cables. Cutting edges additionally induction hardened to approx. 64HRC. C70 Special tool steel. Use for gripping, pulling & holding as well as cutting wires and cables ranging in hardness from soft to extremely hard. Two component soft grip ergonomic handles.

Item	mm	Inch	Cutting Capacity Copper AWG	Pkg.	lbs.
No.					
32820	225	9.0	#4	1	.86

Insulated Crimping Pliers



SHOP

32841 Insulated Crimping Pliers. Insulation According to

VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E and CSA, up to 1000 Volt. Individually Tested.

Semi-circular profiles for secure connection between end sleeve and conductor. Long life is achieved through additional induction hardening to 64HRC. C70 special tool steel hardened & tempered.

Item	mm	Inch	mm ²	AWG	Pkg.	lbs.
No.						
32841	180	7.0	0.25-2.5	6-30	1	.57

Insulated Electrician's Diagonal Cutters


[SHOP](#)

32861 Diagonal Cutters W/Stripping Holes. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E and CSA,  up to 1000 Volt. Individually Tested.

Drop-forged from special tool steel, cutters additionally induction hardened to approx. 64HRC, chrome-nickel plated, mirror-polished. Ergonomic comfort grip with slip guard. Holes in the cutting edge for stripping copper wire of Ø 1.5 and 2.5. Strips AWG sizes #10 & #14.

Item	↔	↔	Cutting Capacity	↔	↔
No.	mm	Inch	Copper AWG	Pkg.	lbs.
32861	160	6.3	#6	1	.55

Insulated Diagonal Cutters


[SHOP](#)

328 Diagonal Cutters. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E and CSA,  up to 1000 Volt. Individually Tested. DIN ISO 5749 Low wear lap joint, riveted and able to withstand high levels of load. Lightweight action, clean cutting. Long term cutting is achieved through additional inductive hardening to approx. 64HRC. Special tool steel hardened & tempered. For soft & medium hard wire. 32832 & 32834 for soft, hard & piano wire.

Item	↔	↔	Cutting Capacity	↔	↔
No.	mm	Inch	Copper AWG	Pkg.	lbs.
32830	140	5.5	#6	1	.47
32832	160	6.3	#6	1	.49
32834	180	7.0	#6	1	.62

Insulated High Leverage Diagonal Cutters



New dynamic joint provides 40% easier cuts and significantly longer tool life

 1000volt

[SHOP](#)

328 High Leverage Diagonal Cutters. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E and CSA,  up to 1000 Volt. Individually Tested. DIN ISO 5749 Semi-circular. Low wear lap joint, riveted and able to withstand high levels of load. Lightweight action, clean cutting. Long term cutting is achieved through additional inductive hardening to approx. 64HRC. C70 special tool steel hardened and tempered to high quality. For soft, hard and piano wire, lay-on joint, optimized power transmission.

Item	↔	↔	Cutting Capacity	↔	↔
No.	mm	Inch	Copper AWG	Pkg.	lbs.
32835	160	6.3	#6	1	.64
32836	180	7.0	#5	1	.67
32838	200	8.0	#4	1	.80

Insulated Serrated Edge Cable Cutters


[SHOP](#)

328 Serrated Edge Cable Cutters. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E and CSA,  up to 1000 Volt. Individually Tested. Light, clean cutting ground precision cutting edges. Durable cutting is achieved through additional inductive hardening to approx. 64HRC. Special tool steel, hardened & tempered. For cutting of copper & aluminum cables without crushing.

Item	↔	↔	↔	↔	↔	↔
No.	mm	Inch	Ø	mm2	Pkg.	lbs.
32826	160	6.3	16	50	1	.42
32828	200	8.0	20	60	1	.67

Insulated Stripping Pliers


 1000volt


64HRC cutting edges

[SHOP](#)

32860 Stripping Pliers. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E and CSA,  up to 1000 Volt. Individually Tested. Heavy duty forged with induction hardened cutting edges for even stripping of insulation. Drop-forged from special tool steel, chrome & nickel plated, mirror-polished. Ergo comfort grip with slip guard. Spring & adjusting screw, for stripping up to Ø 5mm/#4 Awg.

Item	↔	↔	Stripping Capacity	↔	↔
No.	mm	Inch	Copper AWG	Pkg.	lbs.
32860	160	6.3	#8 - #28	1	.50

Insulated Long Nose Pliers



SHOP

328 Long Nose Pliers With Cutters. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA, **up to 1000 Volt. Individually Tested.** Drop-forged from C70 special tool steel, cutters additionally induction hardened to approx. 64HRC, chrome-nickel plated, mirror-polished, ergonomic comfort grip with slip guard, half-round jaws, serrated gripping surface.

Item	mm	Inch	Cutting Capacity Copper AWG	Pkg.	lbs.
32806	160	6.3	#10	1	.32
32808	200	8.0	#8	1	.42

Insulated Bent Nose Pliers

Angled 40°



SHOP

328 Bent Nose Pliers With Cutters. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E and CSA, **up to 1000 Volt. Individually Tested.**

Drop-forged from C70 special tool steel, cutters additionally induction hardened to approx. 64HRC, chrome-nickel plated, mirror-polished. Ergonomic comfort grip with slip guard. Half-round jaws, serrated gripping surface, nose bent 40°.

Item	mm	Inch	Cutting Capacity Copper AWG	Pkg.	lbs.
32804	200	8.0	#8	1	.43
32807	160	6.3	#10	1	.32

Round Nose Pliers



SHOP

32870 Round Nose Pliers. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E and CSA, **up to 1000 Volt. Individually Tested.** Drop-forged from C70 special tool steel, individually induction hardened, chrome and nickel plated, mirror-polished. Ergonomic comfort grip with slip guard. Serrated jaws.

Item	mm	Inch	Pkg.	lbs.
32870	160	6.3	1	.34

Insulated Long Flat Nose Pliers



SHOP

32810 Long Flat Nose Pliers. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E and CSA, **up to 1000 Volt. Individually Tested.** DIN ISO 5745 Extra long head. Serrated Jaws are induction hardened. Special C70 tool steel forgings, Chrome finish. Two component Soft Grip handles. Use for Gripping and right-angle bending of wires and sheet metal parts.

Item	mm	Inch	Pkg.	lbs.
32810	160	6.3	1	.39

Wiha Insulated Ratcheting Cable Cutters



Insulation: VDE, EN/IEC, ASTM, NFPA70E, CSA & OSHA
Tested to 10,000 volts with 1000 volts safety rating



1000Volt

SHOP

11980 Insulated ACSR Ratcheting Cable Cutter

Replaceable tool steel cutting blades are securely mounted for accurate cutting. Handles lock in closed position for easier storage. High leverage ratchet mechanism for best cutting performance.

Item	OAL	OAL	up to	Inch	Capacity	lbs.	pkg.
No.	mm	Inch	MCM	Dia.			
11980	353	13.9	477	1.25"	32ml	3.42	1



Insulation: VDE, EN/IEC, ASTM, NFPA70E and CSA, 1000 Volt. Individually Tested.

SHOP

1000Volt

119 High Voltage Double-Insulated Ratcheting Cable Cutters

High leverage ratchet cable cutter with shear type blades cuts stranded and flexible copper and aluminum cable. Not for use on steel. Features built in safety release in all cutting positions, and high-visibility comfort grip handles.

Item	OAL	OAL	up to	Inch	Capacity	lbs.	pkg.
No.	mm	Inch	MCM	Dia.			
11960	250	10.0"	500	1.25"	32ml	1.58	1
11975	280	11.0"	750	2.0"	52ml	2.02	1

Insulated Stripping Pliers



△1000Volt

SHOP

10250 Insulated Stripping Pliers. Insulation According to EN/IEC 60900, DIN ISO 8976, ASTM F-1505 & CSA Specification. Individually Tested. Wide long head with ridged gripping surface, shears blade and firm wire stripping stations. Wire stripping stations 0.81 / 1.0 / 1.3 / 1.6 / 2.0 / 2.59mm, AWG 20 / 18 / 16 / 14 / 12 / 10.

Item No.	mm	Inch	Ø	AWG	Pkg.	lbs.
10250	160	6.3"	0.81-2.59	20-10	5	.26

Insulated End Cutters



For cutting solid aluminum, copper & medium hard wires

△1000Volt

SHOP

29250 End Cutters, With Insulated Handle. Insulation According to EN/IEC 60900, DIN ISO 8976, ASTM F-1505 & CSA Specification. Individually Tested. Blade alloyed tool steel. Induction hardened.

Item No.	OAL	OAL	Capacity	↔	↔
	mm	Inch	Inch	lbs.	pkg.
29250	250	10.0"	7/8"	1.1	1

Wiha Insulated Waterpump Pliers



△1000Volt

SHOP

29240 Waterpump Pliers, With Insulated Handle
Insulation According to EN/IEC 60900, DIN ISO 8976, ASTM F-1505 & CSA Specification, Up To 1000 Volt. Individually Tested.
Box joint. Chrome-vanadium steel, drop forged, oil hardened.

Item No.	OAL	OAL	Capacity	↔	↔
	mm	Inch	Inch	lbs.	pkg.
29240	240	9.5"	7/8"	1.1	1



△1000Volt

SHOP

116 Waterpump Pliers, With Insulated Handle
Insulation According to EN/IEC 60900, DIN ISO 8976, ASTM F-1505 & CSA Specification, Up To 1000 Volt. Individually Tested.
Chrome-vanadium steel, drop forged, oil hardened.

Item No.	OAL	OAL	Capacity	↔	↔
	mm	Inch	lbs.	pkg.	
11625	250	10.0"	1.2	1	
11630	300	12.0"	1.8	1	

Wiha Insulated Belt Pack Pouch Sets

△1000Volt



32871 3 Piece Insulated Pliers/Cutters & Multi-Bit Set In Belt Pack Pouch. Tools meet EN/IEC, ASTM, VDE, NFPA70E & CSA standards. Pliers chrome finish for long lasting corrosion protection. Soft grip ergo designed handle body, safety slip guard. Insulated Multi-bit screwdriver includes Slotted, Phillips & Square bits.

Item No.	Pliers/Cutters & Multi-Bit Set	SHOP
32871	6.3" / 160mm Diagonal Cutters	
↔	8.0" / 200mm Long Nose Pliers	
lbs.	Set Includes Bit Holder & The Following Bits:	
1.67	Slotted: 4.5, 6.5mm Phillips: 1, 2 Square: 1, 2	

△1000Volt



SHOP

32873 3 Piece Insulated Pliers/Cutters In Belt Pack Pouch. Tools meet EN/IEC, ASTM, VDE, NFPA70E & CSA standards. Pliers chrome finish for long lasting corrosion protection. Soft grip ergo designed handle body, safety slip guard.

Item No.	Pliers & Cutters
32873	6.3" / 160mm Diagonal Cutters
↔	8.0" / 200mm Long Nose Pliers
lbs. 2.07	8.0" / 200mm Combination Pliers

△1000Volt



32872 5 Piece Insulated Pliers/Cutters & Screwdrivers In Belt Pack Pouch. Tools meet EN/IEC, ASTM, VDE, NFPA70E & CSA standards. Pliers chrome finish for long lasting corrosion protection. Soft grip ergo designed handle body, safety slip guard. Insulated cushion grip drivers, multi-component. Blade CVM tool steel, hardened.

Item No.	Pliers/Cutters & Screwdrivers	SHOP
32872	6.3" / 160mm Diagonal Cutters	
↔	8.0" / 200mm Long Nose Pliers	
lbs.	Insulated Screwdrivers:	
1.77	Slotted: 3.0, 4.5mm Phillips: 2	

Wiha Insulated Pliers and Cutters Sets


 1000volt

- Pliers drop-forged from special tool steel, individually high frequency induction hardened, chrome and nickel plated, mirror-polished.

- In zipper carry case

32891 10 Piece Pliers & Screwdriver Set. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E and CSA,  up to 1000 volt. Individually Tested.



Item# 32891 Set Includes:	 lbs. 5.44
32818 - 8.0" Combination Pliers	32808 - 8.0" Long Nose
32838 - 8.0" Side Cutters	32848 - 6.75" Cable Cutters
32860 - 6.3" Universal Wire Stripper	
Insulated Phillips #1, #2, #3	Insulated Slotted 4.5, 6.5mm


 1000volt

- Pliers drop-forged from special tool steel, individually high frequency induction hardened, chrome and nickel plated, mirror-polished.

32889 8 Piece Pliers & Cutters Set. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E and CSA,  up to 1000 volt. Individually Tested.



Item# 32889 Set Includes:	 lbs. 4.53
32806 - 6.3" Long Nose Pliers	32808 - 8.0" Long Nose Pliers
32814 - 6.3" Lineman's Pliers	32832 - 6.3" Diagonal Cutters
32820 - 9.0" Lineman's Pliers	32838 - 8.0" High Lev. Cutters
32860 - 6.3" Wire Stripping Pliers	15000 - Electrician's Knife

Wiha Inomic 1000Volt Insulated Pliers

Insulation Standards:

EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA

Tools Meet 10,000 Volt Test Standards Rated to 1000 Volt ac or 1500 Volt dc


 1000volt

32850 Inomic Combo Pliers. Insulation According to EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA,  up to 1000 volt. Individually Tested. DIN ISO 5749 Precision machined forged head. Induction hardened for longest tool life. Cross hatched flat jaw & deep cut radius jaws for secure gripping of the work piece. Cutting edges are matched for precise cutting action. Award winning ergonomic design with head mounted at 23° angle to grip for reduced user fatigue. Palm side of grip has molded soft panel for added comfort in prolonged use.


Item No.	mm	Inch	Cutting Capacity Copper AWG	Pkg.	lbs.
32850	180	7.0	#6	1	.46

32852 Inomic Long Nose Pliers

Item No.	mm	Inch	Cutting Capacity Copper AWG	Pkg.	lbs.
32852	160	6.3	#6	1	.43

32854 Inomic Diagonal Cutters

Item No.	mm	Inch	Cutting Capacity Copper AWG	Pkg.	lbs.
32854	160	6.3	#6	1	.41



Award winning ergonomic design with head mounted at 23° angle to grip for reduced user fatigue

Each tool includes a convenient jaw lock & handle return spring

Heads drop forged CV premium tool steel

Tools Meet 10,000 Volt Test Standards Rated to 1000 Volt ac or 1500 Volt dc

 1000V

32859 3 Pc. Insulated Inomic Pliers/Cutters Set Meets ASTM, EN/IEC, NFPA, CSA, ISO specifications. Award winning ergonomic design with head mounted at 23° angle to grip for reduced user fatigue.

Item# 32859 Set Includes:	 lbs. 1.45
32850 - Combo Pliers	32854 - Diagonal Cutters
32852 - Long Nose Pliers	91230 - Inomic Holster (Includes 3)




Three Holsters Included



91230 Inomic Canvas Holster

Item No.	Width Size	Height Size	 lbs.	 pkg.
91230	4.0 x	4.5	.05	1

Holds any Inomic Pliers



Wiha Insulated Adjustable Wrenches



1000Volt

[SHOP](#)

76208 Insulated 8" Adjustable Wrench

Insulation According to ASTM, EN/IEC, NFPA, CSA and ISO Specification, up to 1000 Volt. Individually Tested. Etched on scale for pre-setting size. Slip guard handle for added protection.

Item No.	OAL Inch	OAL mm	Capacity Opening	Capacity lbs.	Capacity pkg.
76208	8.0	200	1"	.7	1

1000Volt

[SHOP](#)

76210 Insulated 10" Adjustable Wrench

Item No.	OAL Inch	OAL mm	Capacity Opening	Capacity lbs.	Capacity pkg.
76210	10.0	250	1-1/4"	1.4	1

1000Volt

[SHOP](#)

76212 Insulated 12" Adjustable Wrench

Item No.	OAL Inch	OAL mm	Capacity Opening	Capacity lbs.	Capacity pkg.
76212	12.0	300	1-1/2"	1.9	1

1000Volt

[SHOP](#)

76215 Insulated 15" Adjustable Wrench

Item No.	OAL Inch	OAL mm	Capacity Opening	Capacity lbs.	Capacity pkg.
76215	15.0	380	1-11/16"	2.8	1



1000Volt

[SHOP](#)

76290 3 Pc. Insulated Adjustable Wrenches

Etched on scale for pre-setting size. Slip guard handle for added protection.

Set includes the following:

lbs. 4.0 8.0", 10.0", 12.0" Adjustable Pliers

Protturn Insulated Electrician's Shears



1000volt

[SHOP](#)

32951 Protturn Insulated Electrician's Shears

Insulation meets VDE, ASTM F1505, EN/IEC 60900, CSA, NFPA 70E, OSHA Specifications. Made from stainless 420 grade steel

Item No.	mm	Inch	Pkg.	lbs.
32951	160	6.3	1	.22


Insulated Industrial Pliers & Cutters

10,000 Volt tested
1000 Volt Rated

Induction hardened
jaws and cutters
to 64HRC

Two component ergo
cushion grip handles

Industrial
brushed finish



New dynamic joint
provides 40% easier
cuts and significantly
longer tool life



1000V

Insulated Lineman's Pliers With Crimpers



1000volt



Long life high performance
dynamic 60/40 joint

[SHOP](#)

32917 Insulated Industrial Lineman's Pliers "5-In-1" Professional Design

Insulation According to EN/IEC, ASTM, NFPA70E & CSA,

up to 1000 volt. Individually Tested.

Item No.	mm	Inch	Cutting Capacity Copper AWG	Pkg.	wt.
32917	225	9.0	#4	1	.98

Insulated Long Nose Pliers With Cutters



1000volt

[SHOP](#)

329 Insulated Industrial Long Nose Pliers With Cutters.

Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA, up to 1000 volt. Individually Tested.

Item No.	mm	Inch	Cutting Capacity Copper AWG	Pkg.	wt.
32926	160	6.3	#10	1	.36
32923	200	8.0	#8	1	.46

Insulated Diagonal Cutters



1000volt



Long life high performance
dynamic 60/40 joint


[SHOP](#)

329 Insulated Industrial Diagonal Cutters. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA,

up to 1000 volt. Individually Tested. DIN ISO 5749

Item No.	mm	Inch	Cutting Capacity Copper AWG	Pkg.	wt.
32933	160	6.3	#6	1	.64
32929	200	8.0	#6	1	.80

Insulated Combo Pliers With Dynamic Joint



△1000volt



Long life high performance
dynamic 60/40 joint

SHOP

32930 Insulated Industrial High Leverage Combination Pliers. Insulation According to EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA, △ up to 1000 volt. Individually Tested. DIN ISO 5746

Item	↔	↔	Cutting Capacity	↔	↔
No.	mm	Inch	Copper AWG	Pkg.	wt.
32930	200	8.0	#4	1	.92

Insulated Heavy Duty Cable Cutters



△1000volt

SHOP

32927 Insulated Industrial Serrated Edge Cable Cutters. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E and CSA, △ up to 1000 Volt. Individually Tested.

Item	↔	↔	↔	↔	↔	↔
No.	mm	Inch	Ø	mm2	Pkg.	lbs.
32927	200	8.0	20	60	1	.78

Insulated Stripping Pliers



△1000volt

SHOP

32947 Insulated Industrial Stripping Pliers. Insulation According to VDE 0682/part 201, DIN 7437, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA, 1000 volt rated. Individually Tested. DIN ISO 5745

Item	↔	↔	Stripping Capacity	↔	↔
No.	mm	Inch	Copper AWG	Pkg.	wt.
32947	160	6.3	#8 - #28	1	.46

Insulated Crimpers



△1000volt

SHOP

32945 Insulated Industrial Crimping Pliers. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E and CSA, △ up to 1000 Volt. Individually Tested.

Item	↔	↔	↔	↔	↔
No.	mm	Inch	mm2	AWG	Pkg. wt.
32945	180	7.0	0.25-2.5	6-30	1 .64

Insulated Water Pump Pliers



Tools meet ASTM, IEC, VDE, EN, NFPA & CSA standards

△1000volt

SHOP

32954 Insulated Industrial Water Pump Pliers

10 opening settings provides optimal adjustment to objects being gripped. Chrome-vanadium tool steel forgings, hardened and tempered.

Item	↔	↔	Capacities	↔	↔
No.	mm	Inch	Round Hex	Pkg.	wt.
32954	250	10.0	1 3/4 2	1	.90

Insulated Push Button Water Pump Pliers



Tools meet ASTM, IEC, VDE, EN, NFPA & CSA standards

△1000volt

SHOP

32956 Insulated Industrial Push Button Water Pump Pliers Extra narrow head for working in small spaces. Rapid and simple push button setting & locking. Finger jam protection for safe operation at all settings.

Item	↔	↔	Capacities	↔	↔
No.	mm	Inch	Round Hex	Pkg.	wt.
32956	250	10.0	1 3/4 2"	1	.90

Wiha Insulated Industrial Tool Sets

Tools meet ASTM, IEC, VDE, EN, NFPA & CSA standards



△1000Volt

SHOP

32981 3 Pc. Insulated Industrial Pliers & Cutters

Item No. Insulated Pliers & Cutters

32981 8.0" Combo Pliers, 8.0" Long Pliers, 8.0" Diagonal Cutters
↔ lbs. 2.18



Tools meet ASTM, IEC, VDE, EN, NFPA & CSA standards



△1000Volt

SHOP

32983 5 Pc. Insulated Industrial Diagonal Cutters & Screwdrivers

Item No. Insulated Diagonal Cutters & Screwdrivers

32983 6.3"/160mm Diagonal Cutter

Insulated Drivers: Slotted: 3.0, 4.5mm • Phillips: #1, #2

↔ lbs. 1.17



SHOP

32984 6 Pc. Insulated Industrial Combo Pliers & Screwdrivers

Item No. Insulated Combination Pliers & Screwdrivers

32984 8.0" Combination Pliers & 8" Long Nose Pliers

Drivers: Slotted: 3.0, 4.5mm • Phillips: #2 • Square: #2

↔ lbs. 2.06

Wiha Insulated Industrial Tool Sets

In Roll
Out
Pouch



1000Volt



SHOP

32986 11 Pc. Pliers/Cutters & Screwdriver Set. Insulation According to VDE 0682/part 201, DIN EN 60900, EN/IEC 60900, ASTM F-1505-01, NFPA70E, up to 1000 volt. Individually Tested.

Item# 32986 Set Includes:	lbs. 3.62
32926 - 6.3" Long Nose Pliers	32933 - 6.3" Diagonal Cutters
32930 - 8.0" Combination Pliers	32947 - 6.3" Stripping Pliers
Insulated Slotted: 3.0, 4.5, 5.5mm	
Insulated Phillips: #1, #2 Insulated Square: #1, #2	

In Roll
Out
Pouch



1000Volt



SHOP

32987 8 Pc. Pliers & Cutters Set. Insulation According to VDE 0682/part 201, DIN EN 60900, EN/IEC 60900, ASTM F-1505-01, NFPA70E, up to 1000 volt. Individually Tested. In Roll Out Pouch

Item# 32987 Set Includes:	lbs. 5.52
32926 - 6.3" Long Nose Pliers	32933 - 6.3" Diagonal Cutters
32923 - 8.0" Long Nose Pliers	32929 - 8.0" H.D. Diagonal Cutters
32917 - 9.0" Lineman's w/Cutters	32947 - 6.3" Stripping Pliers
32927 - 8.0" Cable Cutters	32945 - 7.0" Crimpers

1000Volt



In Roll
Out
Pouches



SHOP

32988 22 Pc. Pliers/Cutters & SlimLine Blade Set. Insulation According to VDE 0682/part 201, DIN EN 60900, EN/IEC 60900, ASTM F-1505-01, NFPA70E, up to 1000 volt. Individually Tested.

Item# 32988 Set Includes:	lbs. 5.74
32923 - 8.0" Long Nose Pliers	32933 - 6.3" Diagonal Cutters
32917 - 9.0" Lineman's w/Cutters	32929 - 8.0" H.D. Diagonal Cutters
32927 - 8.0" Cable Cutters	32947 - 6.3" Stripping Pliers
32945 - 7.0" Crimpers	
15 Pc. SlimLine Blade Set includes: Insulated SlimLine Blade Holder	
Slotted: 3.0, 4.0, 5.5, 6.5	Phillips: #1, #2 Xeno: #1, #2
TORX®: T8, T10, T15, T20 Square: #1, #2	

Tools meet ASTM,
IEC, VDE, EN,
NFPA & CSA
standards



In Belt Pack
Pouch



1000Volt

32985 7 Pc. Insulated Industrial Pliers/Cutters & Screwdrivers

Item No. Insulated Pliers/Cutters & Screwdrivers	
32985	8.0" Combo Pliers, 6.3" Long Nose, 6.3" Diagonal Cutters
Insulated Drivers: Slotted: 3.0, 4.5mm • Phillips: #1, #2	
lbs. 2.30	

SHOP



Tools meet ASTM,
IEC, VDE, EN,
NFPA & CSA
standards

Tool box set
in blow molded tray

1000Volt

32999 9 Piece Insulated Industrial Pliers & Cutters Set

Insulated pliers & cutters set in a light weight tool box tray.

Item No.	
32999	9.0" Lineman's Pliers 8.0" High Leverage Combo Pliers
	6.3" Long Nose Pliers 8.0" Cable Cutters
	8.0" Long Nose Pliers 6.3" Stripping Pliers
lbs.	6.3" Diagonal Cutters 7.0" Crimping Pliers
6.34	8.0" Diagonal Cutters

SHOP



1000Volt



SHOP


32390 11 Pc. Pliers & Driver Set. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA, up to 1000 volt. Individually Tested. In canvas tool bag

Item# 32390 Set Includes:	lbs. 7.5
8.0" Linemans Pliers	6.3" Long Nose Pliers W/Cutters
8.0" Long Nose Pliers W/Cutters	6.3" Diagonal Cutters
8.0" High Leverage Cutters	
Insulated Phillips #0	Insulated Slotted 3.0mm(1/8")
Insulated Phillips #1	Insulated Slotted 4.5mm(3/16")
Insulated Phillips #2	Insulated Slotted 6.5mm(1/4")

Wiha Soft Grip Pliers & Cutters

Wiha Pliers & Cutters, professional quality at competitive prices. A wide selection covering most applications in which pliers & cutters are required.

Precision formed
64HRC
Cutting Edges
Jaws and
cutters induction
hardened



Heavy duty steel
riveted joints
Soft grips are
oil & solvent
resistant
High frequency induction
hardened body from C.V.
tool steel forgings



Lineman's Pliers With Crimpers

5-in-1 Lineman's Pliers



With Lower Crimping Jaw



32616 Lineman's Pliers "5-in-1" Professional Design

Deep cut radius conduit jaws for non-slip gripping. Extra long induction hardened precision matched 64HRC cutting edges. Lower crimping jaw accepts most standard non-insulated electrical connectors. Large head with square anvil surface on each side. Made from premium C70 tool steel forgings. Vinyl coated cushion grips for best user comfort.

Item	↔	↔	Cutting Capacity		
No.	mm	Inch	Copper AWG	Pkg.	lbs.
32616	225	9.0	#4	1	.88

Combination Pliers With Cutters



326 Combination Pliers With Cutters DIN ISO 5746

Extra long cutting edge for flat and round cables. Serrated jaws. Cutting edges additionally induction hardened to approx. 64HRC. C70 Special tool steel. For gripping and holding as well as cutting soft and hard wires and cables. Soft vinyl grips, oil & solvent resistant.

Item	↔	↔	Cutting Capacity		
No.	mm	Inch	Copper AWG	Pkg.	lbs.
32603	160	6.3	#10	1	.41
32606	180	7.0	#9	1	.50
32609	200	8.0	#8	1	.63

High Leverage Combination Pliers



326 High Leverage Heavy Duty Combination Pliers DIN ISO 5746

Extra long cutting edge for flat and round cables. Serrated jaws. Cutting edges additionally induction hardened to approx. 64HRC. C70 Special tool steel forgings. Use For gripping, pulling & holding as well as cutting soft, hard & piano wires and cables. Soft vinyl grips are oil & solvent resistant.

Item	↔	↔	Cutting Capacity		
No.	mm	Inch	Copper AWG	Pkg.	lbs.
32612	200	8.0	#4	1	.61
32615	225	9.0	#4	1	.78

Long Nose Pliers With Cutters



326 Long Nose Pliers With Cutters DIN ISO 5745

Long nose pliers. Extra long cutters for flat and round cables. Serrated Jaws. Cutting edges additionally induction hardened to approx. 64HRC. Special C70 tool steel forgings. Soft vinyl grips are oil & solvent resistant.

Item	↔	↔	Cutting Capacity		
No.	mm	Inch	Copper AWG	Pkg.	lbs.
32618	160	6.3	#10	1	.28
32621	200	8.0	#8	1	.86

Bent Long Nose Pliers With Cutters

Angled 40°



326 Bent Long Nose Pliers With Cutters DIN ISO 5745

Long nose pliers angled 40°. Extra long cutters for flat and round wire. Partially Serrated Jaws. Cutting edges additionally induction hardened to approx. 64HRC. Special C70 tool steel forgings. Soft vinyl grips are oil & solvent resistant.

Item	↔	↔	Cutting Capacity	↔	↔
No.	mm	Inch	Copper AWG	Pkg.	lbs.
32623	160	6.3	#10	1	.28
32625	200	8.0	#8	1	.96

Long Flat Nose Pliers



32630 Long Flat Nose Pliers DIN ISO 5745

Extra long head. Serrated Jaws are induction hardened. Special C70 tool steel forgings. Use for gripping and right-angled bending of wires and sheet metal parts. Soft vinyl grips are oil & solvent resistant.

Item	↔	↔		↔	↔
No.	mm	Inch	Pkg.	lbs.	
32630	160	6.3	1	.26	

Long Round Nose Pliers



32633 Long Round Nose Pliers DIN ISO 5745

Extra long head. Serrated Jaws are induction hardened. Special C70 tool steel forgings. Use for gripping and uniform round bending of wires and sheet metal parts. Soft vinyl grips are oil & solvent resistant.

Item	↔	↔		↔	↔
No.	mm	Inch	Pkg.	lbs.	
32633	160	6.3	1	.25	

Stripping Pliers



32645 Stripping Pliers DIN ISO 5744

Heavy duty forged with induction hardened cutting edges for even stripping of insulation. Easy to use adjusting screw allows the stripping diameter to be set. Opening spring for effortless and sensitive handling of pliers. C70 special tool steel. 64HRC cutting edges. For Stripping up to Ø 5mm/#4 AWG conductor cross-section. Soft vinyl grips.

Item	↔	↔	Stripping Capacity	↔	↔
No.	mm	Inch	Copper Awg#	Pkg.	lbs.
32645	160	6.3	#8 - #28	1	.31

Protum Stripping Pliers



57872 Protum Stripping Pliers

Wide long head with ridged gripping surface, shears blade and firm wire stripping stations. With opening spring and locking mechanism. Wire stripping stations 0.81 / 1.0 / 1.3 / 1.6 / 2.0 / 2.59mm, AWG 20 / 18 / 16 / 14 / 12 / 10.

#57872	mm	Inch	Ø	AWG	Pkg.	lbs.
	180	7.0	0.81-2.59	20-10	1	.124

SHOP

Wiha Soft Grip Pliers & Cutters

Standard Adjustable Pliers



SHOP

326 Adjustable Pliers - Box Type DIN ISO 5745

10 different opening sizes provide optimal adjustment to objects being gripped. Long durability achieved through additional induction hardening of jaws to approx. 58-60 HRC. Chrome-vanadium tool steel, hardened and tempered. Soft vinyl grips are oil and solvent resistant.

Item No.	mm	Inch	Capacities		Pkg.	lbs.
			Round	Hex		
32660	180	7.0	1.25	1 1/2	1	.35
32661	250	10.0	1.75	2.0	1	.67
32663	300	12.0	2.0	2 1/4	1	1.17

Slide Lock Adjustable Pliers - "QuickFix"



SHOP

32668 Slide Lock Adjustable Pliers - Wiha QuickFix - Box Type

DIN ISO 8976 Super fast and easily adjusted pliers. Long durability achieved through additional induction hardening of jaws to approx. 56 HRC. Finger jam protection for safe operation in all settings. Chrome-vanadium tool steel, hardened and tempered. Soft vinyl grips.

Item No.	mm	Inch	Capacities		Pkg.	lbs.
			Round	Hex		
32668	250	10.0	1 1/4	1 1/2	1	.72

- Open and slide to adjust opening size
- Audible click at each locking position
- Close to lock

Rapid Adjustable - Push Button Pliers



SHOP

326 Push Button Adjustable Water Pump Pliers - DIN ISO 8976

Extra narrow head for working in restricted spaces. Rapid and simple push button setting and locking. Long durability achieved by additional inductive hardening of gripper jaws to approx. 58-60 HRC. Finger jam protection in all settings ensures safe operation. Chrome-vanadium tool steel, hardened and tempered. Soft vinyl grips. For gripping and holding pipes and angular profiles such as hex nuts in the installation area.

Item No.	mm	Inch	Capacities		Pkg.	lbs.
			Round	Hex		
32664	180	7.0	1.25	1 1/2	1	.35
32665	250	10.0	1.75	2.0	1	.80
32667	300	12.0	2.0	2 1/4	1	1.21

- Fast push button jaw release
- Finger jam protection in all settings



SHOP

32669 3 Piece Push Button Set

Drop-forged from special tool steel, individually high frequency induction hardened. Precision formed. Soft vinyl grips, oil & solvent resistant.

Item# 32669 Set Includes: lbs. 2.50

32664 - Push Button Adjustable Water Pump Pliers - 7.0"

32665 - Push Button Adjustable Water Pump Pliers - 10.0"

32667 - Push Button Adjustable Water Pump Pliers - 12.0"



SHOP

32670 3 Piece Adjustable Pliers Set

Drop-forged from special tool steel, individually high frequency induction hardened. Precision formed. Soft vinyl grips, oil & solvent resistant.

Item# 32670 Set Includes: lbs. 2.52

32660 - Adjustable Pliers, Box Type - 7.0"

32661 - Adjustable Pliers, Box Type - 10.0"

32663 - Adjustable Pliers, Box Type - 12.0"

Wiha Soft Grip Pliers & Cutters

Diagonal Cutters


[SHOP](#)

326 Diagonal Cutters DIN ISO 5749

Low wear lap joint, riveted and able to withstand high levels of load. Low force cutting action, clean cutting. Long life edge is achieved through additional induction hardening to approx. 64HRC. Special C70 tool steel hardened and tempered. For soft & medium hard wire. Soft vinyl grips.

Item No.	mm	Inch	Cutting Capacity Copper AWG	Pkg.	lbs.
32638	140	5.5	#6	1	.33
32642	160	6.3	#6	1	.49
32639	180	7.0	#6	1	.54

High Leverage Cutters


[SHOP](#)

326 High Leverage Cutters DIN ISO 5749

Semi-circular. Low wear lap joint, riveted and able to withstand high levels of load. Low force action, clean cutting. Long life is achieved through additional induction hardening of cutting edge to 64HRC. C70 special tool steel hardened and tempered. Soft vinyl grips.

Item No.	mm	Inch	Cutting Capacity Copper AWG	Pkg.	lbs.
32646	160	6.3	#6	1	.42
32649	180	7.0	#5	1	.50
32652	200	8.0	#4	1	.63

Cable Cutters



64HRC
cutting edges

[SHOP](#)

326 Cable Cutters Light, energy-saving & clean cutting with specially ground precision cutting edges. Long life is achieved through additional induction hardening of cutting edge to 64HRC. C70 special tool steel hardened and tempered. Soft vinyl grips. For cutting of copper & aluminum cables without crushing, also suitable for stripping. Not for steel cable, wires and copper conductors with hard coatings.

Item No.	mm	Inch	Cutting Capacity Copper/Aluminum	Pkg.	lbs.
32600	160	6.3	16mm	1	.34
32602	200	7.9	20mm	1	.62

Flush Cutting Diagonal Cutters


[SHOP](#)

- Flush cutting,
with return spring

326 Flush Cutting Diagonal Cutters With Return Spring For Cutting Plastic DIN ISO 5749 Low wear lap joint, riveted and able to withstand high levels of load. Lightweight action, clean cutting. Long life edge is achieved through additional induction hardening to approx. 64HRC. Special C70 tool steel hardened and tempered. For cutting plastic tie wraps & injection mold components. Soft vinyl grips.

Item No.	mm	Inch	Pkg.	lbs.
32607	127	5.0	1	.14
32614	160	6.3	1	.36

Soft Grip Crimping Pliers


[SHOP](#)

326 Crimping Pliers DIN ISO 5743

Semi-circular profiles for secure connection between end sleeve and conductor. Long life is achieved through additional induction hardening to 64HRC. C70 special tool steel hardened & tempered. Soft vinyl grips.

Item No.	mm	Inch	mm ²	AWG	Pkg.	lbs.
32604	145	5.75	0.25-2.5	14-32	1	.29
32605	180	7.0	0.25-16	6-32	1	.57


Wiha Soft Grip Pliers & Cutters



32698 3 Piece Pliers & Cutters Set

Drop-forged from special tool steel, individually high frequency induction hardened. Precision formed. Soft vinyl grips, oil & solvent resistant.

Item# 32698 Set Includes:	 lbs. 1.39
32606 - Combination Pliers	32642 - Diagonal Cutters
32618 - Long Nose Pliers	



32648 2 Piece Pliers & Cutters Set

Drop-forged from special tool steel, individually high frequency induction hardened. Precision formed. Soft vinyl grips, oil & solvent resistant.

Item# 32648 Set Includes:	 lbs. .78
32621 - Long Nose Pliers With Cutters - 8.0"	
32642 - Diagonal Cutters - 6.3"	



32610 Multipurpose Electrician's Heavy Duty Shears

High alloy carbon steel, hardened, burnished surface. Sturdy model, straight, very robust, micro-toothed cutting.

Item No.	mm	Inch	Pkg.	lbs.
32610	145	5.75	1	.05

32611 SoftGrip Electrician's & Craftsman Shears

Item No.	mm	Inch	Pkg.	lbs.
32611	145	5.75	1	.05

Wiha Soft Grip Nippers



326 High Leverage End Cutting Nippers DIN ISO 5749 Low wear lap joint, riveted and able to withstand high levels of load. Low force action, clean cutting. Long life cutting edges are achieved through additional induction hardening to approx. 60 HRC. Special C70 tool steel forgings hardened and tempered. Soft vinyl grips are oil & solvent resistant.

Item No.	mm	Inch	Cutting Capacity Copper AWG	Pkg.	lbs.
32657	160	6.3	#6	1	.41
32658	180	7.0	#6	1	.61
32659	200	8.0	#6	1	.75



326 Carpenter's End Nippers DIN ISO 9243

High cutting performance and reduced effort achieved through the precise formation of the cutting blade after assembly. Long life cutting edges achieved by additional induction hardening. Special C70 tool steel, hardened and tempered. Soft vinyl grips are oil & solvent resistant.

Item No.	mm	Inch	Pkg.	lbs.
32671	180	7.0	1	.62
32672	200	8.0	1	.86



326 Mason Nippers DIN ISO 9243

High cutting performance and reduced effort achieved through the precise formation of the cutting blade after assembly. Long life induction hardened cutting edges. Special C70 tool steel, hardened & tempered. Soft vinyl Grips are oil & solvent resistant.

Item No.	mm	Inch	Cutting Capacity Hard Wire AWG	Pkg.	lbs.
32674	220	8.75	#12	1	.76
32676	250	10.0	#12	1	.98
32678	280	11.0	#12	1	1.00
32680	300	12.0	#12	1	1.06

Wiha Soft Grip Pliers & Cutters



SHOP

32601 4 Piece Pliers & Cutters Set

Drop-forged from C70 special tool steel, individually high frequency induction hardened. Precision formed. Soft vinyl grips, oil & solvent resistant. In roll-up pouch.

Item# 32601 Set Includes:	 lbs. 3.16
32609 - Combination Pliers - 8.0"	32661 - Water Pump Pliers - 10.0"
32618 - Long Nose Pliers - 6.3"	32642 - Diagonal Cutters - 6.3"




SHOP

32608 8 Piece Pliers & Cutters In Canvas Pouch

Pliers precision formed. Jaws & cutters induction hardened. Long life edge is achieved through additional induction hardening to approx. 60 HRC. Soft vinyl grips are oil & solvent resistant.

Item No. Set Includes:	
32608	6.3" / 160mm Combination Pliers
	6.3" / 160mm Long Nose Pliers
	8.0" / 200mm Long Nose Pliers
lbs.	6.3" / 160mm Diagonal Cutters
4.42	6.3" / 160mm Long Flat Nose Pliers
	6.3" / 160mm Long Round Nose Pliers
	8.0" / 200mm High Leverage Cutters
	9.0" / 225mm High Leverage Combo Pliers

Wiha Soft Grip Pliers & Cutters



Tool box set
in blow molded tray

Wiha Soft Grip Belt Pack Pouch Sets



Durable
Canvas Belt
Pack Pouch



SHOP

32653 3 Piece Pliers/Cutters In Belt Pack Pouch

Pliers precision formed. Jaws & cutters induction hardened. Soft vinyl grips are oil & solvent resistant. SoftFinish cushion grip drivers, multi-component. Durable canvas belt pack pouch.

Item No.	Pliers & Cutters
32653	8.0" / 200mm High Leverage Cutters
	8.0" / 200mm Combo Pliers
	8.0" / 200mm Long Nose Pliers
	lbs. 2.02



SHOP



Durable
Canvas Belt
Pack Pouch



32655 5 Piece Pliers/Cutters & Screwdrivers In Belt Pack Pouch

Pliers precision formed. Jaws & cutters induction hardened. Soft vinyl grips are oil & solvent resistant. Screwdriver blades CVM tool steel, hardened, hard chromed. SoftFinish cushion grip drivers, multi-component. Durable canvas belt pack pouch.

Item No.	Pliers & Cutters
32655	6.3" / 160mm Diagonal Cutters
	8.0" / 200mm Long Nose Pliers
	Cushion Grip Screwdrivers:
	Slotted: 3.0, 4.5mm Phillips: 2
	lbs. 1.62

SHOP

32679 9 Piece Pliers & Cutters Set In Tool Box Tray

Pliers & cutters set in a light weight tool box tray.

Item No.		
32679	9.0" Lineman's Pliers	8.0" Combo Pliers
	6.3" Long Nose Pliers	8.0" Cable Cutters
	8.0" Long Nose Pliers	6.3" Stripping Pliers
lbs.	6.3" Diagonal Cutters	7.0" Crimping Pliers
6.34	8.0" Diagonal Cutters	

Wiha Soft Grip Pliers & Cutters

Retaining Ring Pliers - Internal



326 Straight Internal Retaining Ring Pliers DIN ISO 5256

Shape C, straight tips. Die forged cylindrical precision formed. Chrome-vanadium special tool steel. For inserting & removing internal retaining rings.

Item	↔	↔	⊙	⊙	● Tip	☐	↔
No.	mm	Inch	Inch	mm	Inch/mm	Pkg.	lbs.
32681	139	5.5	5/16-1/2	8-13	.035/.9	1	.27
32682	140	5.5	1/2-1	12-25	.050/1.3	1	.27
32683	180	7.0	3/4-2 3/8	19-60	.070/1.5	1	.42
32684	225	8.9	1 1/2-4	40-100	.090/2.3	1	.63
32654	310	12.2	3.5-5.5	85-140	.126/3.2	1	1.13

90° Angle Retaining Ring Pliers - Internal



326 90° Angle Internal Retaining Ring Pliers DIN ISO 5254

Shape D, 90° angled tips. Die forged cylindrical precision formed. CV Special tool steel. For inserting & removing internal retaining rings. Soft vinyl grips.

Item	↔	↔	⊙	⊙	● Tip	☐	↔
No.	mm	Inch	Inch	mm	Inch/mm	Pkg.	lbs.
32685	139	5.5	5/16-1/2	8-13	.035/.9	1	.27
32686	140	5.5	1/2-1	12-25	.050/1.3	1	.27
32687	165	7.0	3/4-2 3/8	19-60	.070/1.5	1	.43
32688	225	8.9	1 1/2-4	40-100	.090/2.3	1	.62
32656	310	12.2	3.5-5.5	85-140	.126/3.2	1	1.14

Retaining Ring Pliers - External



326 Straight External Retaining Ring Pliers DIN ISO 5254

Shape A, straight tips. Die forged cylindrical precision formed. CV special tool steel. For fitting & removing external retaining rings. Soft vinyl grips.

Item	↔	↔	⊙	⊙	● Tip	☐	↔
No.	mm	Inch	Inch	mm	Inch/mm	Pkg.	lbs.
32689	139	5.5	1/8-3/8	3-10	.035/.9	1	.28
32690	140	5.5	3/8-1	10-25	.050/1.3	1	.28
32691	180	7.0	3/4-2 3/8	19-60	.070/1.5	1	.45
32692	225	8.9	1 1/2-4	40-100	.090/2.3	1	.62
32662	310	12.2	3.5-5.5	85-140	.126/3.2	1	1.13

90° Angle Retaining Ring Pliers - External



326 90° Angled External Retaining Ring Pliers DIN ISO 5254

Shape B, 90° angled tips. Die forged cylindrical precision formed. CV special tool steel. For fitting & removing external retaining rings. Soft vinyl grips.

Item	↔	↔	⊙	⊙	● Tip	☐	↔
No.	mm	Inch	Inch	mm	Inch/mm	Pkg.	lbs.
32694	139	5.5	1/8-3/8	3-10	.035/.9	1	.28
32695	140	5.5	3/8-1	10-25	.050/1.3	1	.28
32696	180	7.0	3/4-2 3/8	19-60	.070/1.5	1	.44
32697	225	8.9	1 1/2-4	40-100	.090/2.3	1	.63
32666	310	12.2	3.5-5.5	85-140	.126/3.2	1	1.16

Wiha Forged Retaining Ring Pliers


[SHOP](#)

32693 8 Piece Straight Retaining Ring Pliers Set Straight tips.

Die forged cylindrical precision formed. Chrome-vanadium special tool steel. For inserting & removing internal and external retaining rings.

Item# 32693 Set Includes:

⚖️ lbs. 3.65

Internal Retaining Ring - Shape C

External Retaining Ring - Shape A

32681 5/16-1/2" / 8-13mm / tip .035

32689 1/8 - 3/8" / 3-10mm / tip .035

32682 1/2-1" / 12-25mm / tip .050

32690 3/8 - 1" / 10-25mm / tip .050

32683 3/4-2-3/8" / 19-60mm / tip .070

32691 3/4 - 2-3/8" / 19-60mm / tip .070

32684 1-1/2-4" / 40-100mm / tip .090

32692 1/2 - 4" / 40-100mm / tip .090


[SHOP](#)

32626 4 Piece Straight Internal Ring Pliers Set Shape C, straight tips. Die forged cylindrical precision formed. Chrome-vanadium special tool steel. For inserting & removing internal retaining rings.

Item# 32626 Set Includes:

⚖️ lbs. 1.60

32681 5/16-1/2" / 8-13mm / tip .035

32683 3/4-2 3/8" 19-60mm / tip .070

32682 1/2-1" 12-25mm / tip .050

32684 1 1/2-4" 40-100mm / tip .090


[SHOP](#)

32628 4 Piece Straight External Ring Pliers Set Shape A, straight tips. Die forged cylindrical precision formed. CV special tool steel. For fitting & removing external retaining rings. Soft vinyl grips.

Item# 32628 Set Includes:

⚖️ lbs. 1.52

32689 1/8-3/8" / 3-10mm / tip .035

32691 3/4-2 3/8" 19-60mm / tip .070

32690 3/8-1" 10-25mm / tip .050

32692 1 1/2-4" 40-100mm / tip .090


[SHOP](#)

32627 4 Piece 90° Angle Internal Ring Pliers Set Shape D, 90° angled tips. Die forged cylindrical precision formed. CV Special tool steel. For inserting & removing internal retaining rings. Soft vinyl grips.

Item# 32627 Set Includes:

⚖️ lbs. 1.56

32685 5/16-1/2" / 8-13mm / tip .035

32687 3/4-2 3/8" 19-60mm / tip .070

32686 1/2-1" 12-25mm / tip .050

32688 1 1/2-4" 40-100mm / tip .090


[SHOP](#)

32629 4 Piece 90° Angle External Ring Pliers Set Shape B, 90° angled tips. Die forged cylindrical precision formed. CV special tool steel. For fitting & removing external retaining rings. Soft vinyl grips.

Item# 32629 Set Includes:

⚖️ lbs. 1.52

32694 1/8-3/8" / 3-10mm / tip .035

32696 3/4-2 3/8" 19-60mm / tip .070

32695 3/8-1" 10-25mm / tip .050

32697 1 1/2-4" 40-100mm / tip .090

Wiha MagicTip Safety Ring Pliers

Patents Pending



High performance precision notched tips for maximum stability & secure holding
 (Safety notched on .070, .090 & .126)



Hardened MagicTips are notched to hold rings securely on .070, .090 & .126 sizes

Tips made of premium quality hardened CVM tool steel, HRC 64

Heavy duty forged pliers with soft vinyl grips

- Faster & Easier Application
- Fewer Lost Rings
- Safer To Use
- Saves Time & Money



MagicTip Safety Ring Pliers-Internal



346 MagicTip Straight Internal Safety Ring Pliers DIN ISO 5256

Shape C, straight tips. Precision machined tips of Chrome-vanadium special tool steel. For inserting & removing internal retaining rings.

Item No.	mm	Inch	Inch	mm	Inch/mm	Pkg.	lbs.
34610	180	7.1	3/4-2 3/8	19-60	.070/1.5	1	.34
34611	220	8.7	1 1/2-4	40-100	.090/2.3	1	.54
34612	305	12.0	3.5-5.5	85-140	.126/3.2	1	.90

MagicTip 90° Angle Safety Ring Pliers - Internal



346 MagicTip 90° Angle Internal Safety Ring Pliers DIN ISO 5254

Shape D, 90° angled tips. Precision machined tips of Chrome-vanadium Special tool steel. For inserting & removing internal retaining rings. Soft vinyl grips.

Item No.	mm	Inch	Inch	mm	Inch/mm	Pkg.	lbs.
34615	180	7.1	3/4-2 3/8	19-60	.070/1.5	1	.34
34616	220	8.7	1 1/2-4	40-100	.090/2.3	1	.54
34617	305	12.0	3.5-5.5	85-140	.126/3.2	1	.94

No Dropped Rings!



Hardened MagicTips are notched to hold rings securely on .070, .090 & .126 sizes

Safety Notched "MagicTips"

Precision Machined To Hold Rings Securely

Saves Time & Money

Improves Productivity

MagicTip Safety Ring Pliers-External



SHOP

346 MagicTip Straight External Safety Ring Pliers DIN ISO 5254

Shape A, straight tips. Precision machined tips of Chrome-vanadium special tool steel. For fitting & removing external retaining rings. Soft vinyl grips.

Item No.	mm	Inch	Inch	mm	Tip Inch/mm	Pkg.	lbs.
34620	185	7.3	3/4-2 3/8	19-60	.070/1.5	1	.34
34621	240	9.5	1 1/2-4	40-100	.090/2.3	1	.57
34622	300	11.8	3.5-5.5	85-140	.126/3.2	1	1.04

MagicTip 90° Angle Safety Ring Pliers - External




SHOP

346 MagicTip 90° Angled External Safety Ring Pliers DIN ISO 5254

Shape B, 90° angled tips. Precision machined tips of Chrome-vanadium special tool steel. For fitting & removing external retaining rings. Soft vinyl grips.

Item No.	mm	Inch	Inch	mm	Tip Inch/mm	Pkg.	lbs.
34625	185	7.3	3/4-2 3/8	19-60	.070/1.5	1	.36
34626	240	9.5	1 1/2-4	40-100	.090/2.3	1	.57
34627	300	11.8	3.5-5.5	85-140	.126/3.2	1	1.06



In Canvas
Roll-Up
Pouch

SHOP

34697 6 Pc. Straight Internal & External Ring Pliers Set

Precision machined tips of Chrome-vanadium special tool steel. For inserting & removing retaining rings. Soft vinyl grips

Item#	34697	Set Includes:	lbs. 4.04
34610	3/4-2-3/8" / 19-60mm / tip .070	34620 3/4-2-3/8" / 19-60mm / tip .070	
34611	1-1/2-4" / 40-100mm / tip .090	34621 1-1/2-4" / 40-100mm / tip .090	
34612	3.5-5.5" / 85-140mm / tip .126	34622 3.5-5.5" / 85-140mm / tip .126	




In Canvas Roll-Up Pouch

SHOP

34699 12 Pc. Straight And 90° Internal & External Ring Pliers Set

Precision machined tips of Chrome-vanadium special tool steel. For inserting & removing retaining rings. Soft vinyl grips

Item#	34699	Set Includes:	lbs. 8.52
34610	3/4-2-3/8" / 19-60mm / tip .070	34620 3/4-2-3/8" / 19-60mm / tip .070	
34611	1-1/2-4" / 40-100mm / tip .090	34621 1-1/2-4" / 40-100mm / tip .090	
34612	3.5-5.5" / 85-140mm / tip .126	34622 3.5-5.5" / 85-140mm / tip .126	
34615	3/4-2-3/8" / 19-60mm / tip .070	34625 3/4-2-3/8" / 19-60mm / tip .070	
34616	1-1/2-4" / 40-100mm / tip .090	34626 1-1/2-4" / 40-100mm / tip .090	
34617	3.5-5.5" / 85-140mm / tip .126	34627 3.5-5.5" / 85-140mm / tip .126	



In Canvas
Roll-Up
Pouch

SHOP

34698 6 Pc. 90° Angle Internal & External Ring Pliers Set

Precision machined tips of Chrome-vanadium special tool steel. For inserting & removing retaining rings. Soft vinyl grips

Item#	34698	Set Includes:	lbs. 4.06
34615	3/4-2-3/8" / 19-60mm / tip .070	34625 3/4-2-3/8" / 19-60mm / tip .070	
34616	1-1/2-4" / 40-100mm / tip .090	34626 1-1/2-4" / 40-100mm / tip .090	
34617	3.5-5.5" / 85-140mm / tip .126	34627 3.5-5.5" / 85-140mm / tip .126	

Wiha Pipe Wrenches Narrow Style

Pipe Wrenches Narrow Style / S-Jaw


[SHOP](#)

329 Pipe Wrenches Narrow Style / S-Jaw

S-Jaw shape angled 45°. Self clamping gripping of pipes and hex nuts at 3 points. Comfortable handle profile. Rapid adjusting nut. Hardened chrome-vanadium steel, induction hardened jaws. Safe and secure grip on pipes and hex nuts.

Item No.	Inch Length	Max. grip pipe dia.	maximum jaw opening	lbs.	Pkg.
32970	12.60	1	40mm (1.5")	2.4	1
32971	16.38	1.5	55mm (2.1")	2.4	1
32972	21.06	2	67mm (2.6")	3.9	1

All Steel Narrow Profile Pipe Wrenches

Easy access 20%
Narrower profile
heads

Comfortable
handle profile

Rapid adjusting nut
with acme thread

Extra heavy duty hardened CV
steel, induction hardened jaws

Safe and secure grip with back
raked serrated jaws




Pipe Wrenches Narrow Style - 45°


[SHOP](#)

329 Pipe Wrenches Narrow Style - 45°

Narrow shape angled 45°. Safe and secure grip angled jaw teeth. Comfortable handle profile. Rapid adjusting nut. Hardened chrome-vanadium steel, induction hardened jaws. Safe and secure grip on pipes, flat work-pieces and nuts.

Item No.	Inch Length	Max. grip pipe dia.	Clamping range	lbs.	Pkg.
32974	12.36	1	40mm (1.5")	1.8	1
32975	16.77	1.5	55mm (2.1")	2.1	1
32976	22.44	2	67mm (2.6")	6.3	1


[SHOP](#)

32995 3 Piece Pipe Wrench Sets

Hardened chrome-vanadium steel, induction hardened jaws. Safe and secure grip on pipes, flat work-pieces and nuts.

Item#	Set Includes:	lbs.
32970 - 12.60" S-Jaws	32978 - 12.20" 90° Jaws	5.60
32974 - 12.36" 45° Jaws		


Pipe Wrenches Narrow Style - 90°


[SHOP](#)

329 Pipe Wrenches Narrow Style - 90°

Narrow shape angled 90°. Safe and secure grip angled jaw teeth. Comfortable handle profile. Rapid adjusting nut. Hardened chrome-vanadium steel, induction hardened jaws. Safe and secure grip on pipes, flat work-pieces and nuts.

Item No.	Inch Length	Max. grip pipe dia.	Clamping range	lbs.	Pkg.
32978	12.20	1	40mm (1.5")	2.2	1
32979	16.54	1.5	55mm (2.1")	3.2	1
32980	22.05	2	67mm (2.6")	6.0	1


[SHOP](#)

32996 3 Piece Narrow Style 90° Pipe Wrench Sets

Narrow shape angled 90°. Safe and secure grip angled jaw teeth. Comfortable handle profile. Rapid adjusting nut.

Item#	Set Includes:	lbs.
32978 - 12.20" Narrow Style 90°	32980 - 22.05" Narrow Style 90°	10.80
32979 - 16.54" Narrow Style 90°		

Wiha Ratchet Crimpers

Ratchet End Sleeve Crimper



5 die nests
side entry
crimp


[SHOP](#)

43612 Ratchet End Sleeve Crimper

Crimps Insulated & non-insulated end sleeves. 6 crimp positions range AWG 26-18, 18-16, 14, 12, 10, 8. Soft grip non-slip handles. Factory set auto release at end of crimp cycle.

Item No.	Inch Length	AWG Range	lbs.	Pkg.
43612	220mm/8.6"	26-8	1.18	1

Ratchet Crimper Push On Terminals



Crimp Profile
"F"/"B"


[SHOP](#)

43624 Ratchet Crimper Push On Terminals

Crimps Insulated & non-insulated terminals. 4 crimp positions range AWG 24-20, 20-18, 16-14, 12-10. Soft grip non-slip handles. Factory set auto release at end of crimp cycle.

Item No.	Inch Length	AWG Range	lbs.	Pkg.
43624	220mm/8.6"	24-10	1.06	1

Ratchet Crimper For Standard Connectors



Crimp Profile


[SHOP](#)

43618 Ratchet Crimper For Standard Connectors

Crimps Insulated & non-insulated connectors. 3 crimp positions range AWG 20-18 red, 16-14 blue, 12-10 yellow. Soft grip non-slip handles. Factory set auto release at end of crimp cycle.

Item No.	Inch Length	AWG Range	lbs.	Pkg.
43618	220mm/8.6"	20-10	1.06	1

Ratchet Crimper For Eye Terminals



Self adjusting
side entry crimp


[SHOP](#)

43643 Ratchet Crimper For Eye Terminals

Crimps Insulated & non-insulated terminals. 4 crimp positions range AWG 26-22, 20-18, 12-10, 8-6. Soft grip non-slip handles. Factory set auto release at end of crimp cycle.

Item No.	Inch Length	AWG Range	lbs.	Pkg.
43643	220mm/8.6"	26-6	1.02	1

Wiha Industrial SoftGrip Pliers & Cutters

Made by Wiha

Maximum comfort in daily use, smooth operation & optimum force transmission without uncomfortable pressure points. Natural brushed finish.



New dynamic joint provides
40% easier cuts & significantly
longer tool life

Induction hardened
cutters

Ergonomic
shape for maximum
user comfort



Slip guards
molded into grip

Anti-slip soft dual
material handles
for safe gripping

40/60
Dynamic Joint


Industrial SoftGrip Combination Pliers

[SHOP](#)
309 Industrial Combination Pliers DIN ISO 5746

Extra long cutting edge for flat and round cables. Serrated jaws. Cutting edges additionally induction hardened to approx. 64HRC. Special C70 tool steel. For gripping and holding as well as cutting soft and hard wires and cables. Two component Industrial SoftGrip ergonomic handles.

Item No.	mm	Inch	Cutting Capacity AWG	Pkg.	lbs.
30901	160	6.3	#10	1	.52
30903	180	7.0	#9	1	.67
30905	200	8.0	#8	1	.83

Industrial SoftGrip Heavy Duty Combo Pliers

[SHOP](#)
309 Industrial Heavy Duty Combination Pliers DIN ISO 5746

Larger Head and extra long cutting edges for flat and round cables. Serrated jaws. Cutting edges additionally induction hardened to approx. 64HRC. Special C70 tool steel. For gripping & holding as well as cutting wires & cables ranging in hardness from soft to extremely hard. Two component SoftGrip ergo handles.

Item No.	mm	Inch	Cutting Capacity Copper AWG	Pkg.	lbs.
30907	200	8.0	#7	1	.81
30909	225	9.0	#6	1	1.02

Industrial SoftGrip Linemans Crimpers

[SHOP](#)
30912 Industrial Linemans Crimpers DIN ISO 5746

Extra large head and extra long cutting edges for flat and round cables. Cutting edges additionally induction hardened to approx. 64HRC. Special C70 tool steel. For gripping & holding as well as cutting wires & cables ranging in hardness from soft to extremely hard. Two component SoftGrip ergo handles.

Item No.	mm	Inch	Cutting Capacity Copper AWG	Pkg.	lbs.
30912	225	9.0	#4	1	1.05

Industrial SoftGrip Stripping Pliers

[SHOP](#)
30947 Industrial Stripping Pliers DIN ISO 5743

Heavy duty forged with induction hardened cutting edges for even stripping of insulation. Easy to use adjustment screw allows stripping diameter to be quickly changed. Return spring for effortless use. Special C70 tool steel edges. Stripping Diameter: .019" to .393".

Item No.	mm	Inch	Stripping Capacity Copper AWG	Pkg.	lbs.
30947	160	6.3	#8 - #28	1	.48

For stripping up to
Ø 5mm/#4 AWG

Made by Wiha

Industrial SoftGrip Long Nose Pliers



309 Industrial Long Nose Pliers With Cutting Edge DIN ISO 5745

Long nose pliers. Extra long cutters for flat and round wires. Gripping surfaces serrated in parts. Cutting edges additionally induction hardened to approx. 64HRC. C70 Special tool steel. Two component SoftGrip handle.

Item	↔	↔	Cutting Capacity	↔	↔
No.	mm	Inch	AWG	Pkg.	lbs.
30911	160	6.3	#10	1	.41
30913	200	8.0	#8	1	.56

Industrial SoftGrip Bent Long Nose Pliers

Angled approx. 40°



309 Industrial Bent Nose Pliers With Cutters DIN ISO 5745

Long nose pliers angled approx. 40°. Extra long cutting edge for flat and round wires. Gripping surfaces serrated in parts. Cutting edges additionally induction hardened to approx. 64HRC. C70 Special tool steel. Two component SoftGrip handle.

Item	↔	↔	Cutting Capacity	↔	↔
No.	mm	Inch	Copper AWG	Pkg.	lbs.
30915	160	6.3	#10	1	.42
30917	200	8.0	#8	1	.57

Industrial SoftGrip Flat Nose Pliers



30919 Industrial Long Flat Nose Pliers DIN ISO 5745

Extra long head. Gripping surfaces serrated and induction hardened. C70 Special tool steel. Two component SoftGrip handle. Gripping and right-angled bending of wires and sheet metal parts.

Item	↔	↔	↔	↔
No.	mm	Inch	Pkg.	lbs.
30919	160	6.3	1	.43

Industrial SoftGrip Long Round Nose Pliers



30921 Industrial Long Round Nose Pliers DIN ISO 5745

Extra long head. Gripping surfaces serrated and induction hardened. C70 Special tool steel. Two component SoftGrip handle. Gripping and bending of wires and sheet metal parts.

Item	↔	↔	↔	↔
No.	mm	Inch	Pkg.	lbs.
30921	160	6.3	1	.39

Stripping Pliers



56871 Stripping Pliers

Wide long head with ridged gripping surface, shears blade and firm wire stripping stations. With opening spring and locking mechanism. Wire stripping stations 0.81 / 1.0 / 1.3 / 1.6 / 2.0 / 2.59mm, AWG 20 / 18 / 16 / 14 / 12 / 10.

#56871	mm	Inch	Ø	AWG	Pkg.	lbs.
	180	7.0	0.81-2.59	20-10	5	.15

Industrial SoftGrip Cable Cutters



309 Industrial Cable Cutters DIN ISO 5749

Energy saving & clean cutting cable cutters with specially ground precision cutting edges. Long life cutting edges are achieved through additional induction hardening to approx. 64HRC. C70 special CV tool steel hardened and tempered. Two component SoftGrip ergo handle.

Item	↔	↔	Cutting Capacity	↔	↔
No.	mm	Inch	Copper/Aluminum	Pkg.	lbs.
30926	160	6.3	16mm	1	.56
30928	200	8.0	20mm	1	.87

Wiha Industrial SoftGrip Pliers & Cutters

Made by Wiha

Industrial SoftGrip Diagonal Cutters

[SHOP](#)
309 Industrial Diagonal Cutters DIN ISO 5749

Low wear lap joint, riveted and able to withstand high levels of load. Low force action, clean cutting. Long life cutting edge is achieved with additional induction hardening to approx. 64HRC. Special C70 tool steel forgings hardened and tempered. For soft & medium hard wire.

Item No.	mm	Inch	Cutting Capacity Copper AWG	Pkg.	lbs.
30923	140	5.5	#6	1	.45
30925	160	6.3	#6	1	.57
30927	180	7.0	#6	1	.69

Industrial SoftGrip H. Leverage Diag. Cutters

[SHOP](#)
309 Industrial High Leverage Diagonal Cutters DIN ISO 5749

Semi-circular. Low wear lap joint, riveted and able to withstand high levels of load. Low force action, clean cutting. Long life cutting edges are achieved through additional induction hardening to approx. 64HRC. C60 special C70 tool steel hardened and tempered.

Item No.	mm	Inch	Cutting Capacity Copper AWG	Pkg.	lbs.
30929	160	6.3	#6	1	.57
30931	180	7.0	#5	1	.68
30933	200	8.0	#4	1	.89

Industrial SoftGrip Heavy Duty End Nippers

30939 Industrial Heavy Duty End Cutting Nippers

Induction hardened cutting edges. Special tool steel. Two component SoftGrip handle. Gripping and right-angled bending of wires and sheet metal parts. Two component SoftGrip handle.

Item No.	mm	Inch	Pkg.	lbs.
30939	200	8.0	1	.54

[SHOP](#)
Industrial SoftGrip Standard Adj. Pliers


With box joint

[SHOP](#)
30937 Industrial Adjustable Pliers DIN ISO 8976

10 opening settings provides optimal adjustment to objects being gripped. Long life achieved through additional induction hardening of jaws to approx. 64HRC. Chrome-vanadium tool steel forgings, hardened and tempered. Two component SoftGrip ergonomic handle. Black finish.

Item No.	mm	Inch	Capacities Round Hex	Pkg.	lbs.
30937	250	10.0	1 3/4" 2"	1	.94

Industrial SoftGrip Push Button Adj. Pliers


With box joint

[SHOP](#)
30943 Industrial Slide Lock Adjustable Pliers - Box Joint - With Push Button Setting. DIN ISO 8976

Extra narrow head for working small spaces. Rapid and simple push button setting and locking. Long life achieved through additional induction hardening of jaws to approx. 64HRC. Finger jam protection for safe operation at all settings. CVM tool steel forgings, hardened and tempered. SoftGrip handles.

Item No.	mm	Inch	Capacities Round Hex	Pkg.	lbs.
30943	250	10.0	1 3/4" 2"	1	.95

ComfortGrip Slide Lock Adjustable Pliers

With box joint



Rapid adjust

- Close to lock
- Open and slide to adjust opening size
- Audible click at each locking position



32969 Slide Lock Adjustable Pliers - Wiha QuickFix - Box Joint

DIN ISO 8976 Super fast and easily adjusted pliers. Long durability achieved through additional induction hardening of jaws to approx. 56 HRC. Finger jam protection for safe operation at all settings. Chrome-vanadium tool steel forgings, hardened and tempered. Chrome finish with ergonomic ComfortGrip handles.

Item	↔	↔	Capacities		↔	↔
No.	mm	Inch	Round	Hex	Pkg.	lbs.
32969	250	10.0	1 1/4"	1 1/2"	1	.80

Industrial SoftGrip Pliers & Cutters Sets



30993 3 Piece Industrial SoftGrip Pliers & Cutters Set

Maximum comfort in daily use, smooth operation and optimum force transmission without uncomfortable pressure points. Cutters additionally induction hardened. Anti-slip soft dual material handles for safe gripping, ergonomic shape for maximum user comfort.

Item# 30993 Set Includes:	↔
30905 Combination Pliers - 8.0"	lbs.
30925 Diagonal Cutters - 6.3"	1.76
30911 Long Nose Pliers - 6.3"	



30990 4 Piece Industrial SoftGrip Pliers & Cutters Set

Maximum comfort in daily use, smooth operation and optimum force transmission without uncomfortable pressure points. Cutters additionally induction hardened. Anti-slip soft dual material handles for safe gripping, ergonomic shape for maximum user comfort.

Item# 30990 Set Includes:	↔
9.0" - Heavy Duty Combination Pliers	lbs.
8.0" - Long Nose Pliers	2.81
8.0" - High Leverage Diagonal Cutters	
7.0" - ComfortGrip Stripping Pliers	

Industrial SoftGrip Pliers & Cutters Sets



30998 8 Piece Industrial SoftGrip Pliers & Cutters Set

Maximum comfort in daily use, smooth operation and optimum force transmission without uncomfortable pressure points. Cutters additionally induction hardened. Anti-slip soft dual material handles for safe gripping, ergonomic shape for maximum user comfort.

Item# 30998 Set Includes:	↔
6.3" - Combination Pliers	lbs.
9.0" - Heavy Duty Combination Pliers	4.91
6.3" - Long Nose Pliers	
8.0" - Long Nose Pliers	
5.5" - Diagonal Cutters	
8.0" - High Leverage Diagonal Cutters	
10.0" - Adjustable Pliers	
7.0" - ComfortGrip Stripping Pliers	



30991 18 Piece Industrial SoftGrip Pliers/Cutters, Screwdrivers & Wrenches Set

Maximum comfort in daily use, smooth operation and optimum force transmission without uncomfortable pressure points. Cutters additionally induction hardened. Anti-slip soft dual material handles for safe gripping, ergonomic shape for maximum user comfort.

Item# 30991 Set Includes:	↔
8.0" - Combination Pliers	lbs.
6.3" - Long Nose Pliers	6.76
6.3" - Diagonal Cutters	
10.0" - Adjustable Pliers	
Slotted: 5/32, 1/4" Phillips: 1, 2	
Torx: T15, T20, T25 Square: 1, 2	
Wrenches: 1/4"x5/16", 3/8x7/16", 1/2x9/16", 3/4x7/8"	

Wiha Precision Electronic Pliers & Cutters

Electronics pliers with cutting edges are designed especially for cutting soft to medium hard wires.

C70 tool steel HR60 hardness

Glare free
black finish

Precision ground
cutting edges for
smooth cuts



The Comfortable Precision Pliers & Cutters




Velvet soft ergonomically
designed multi component
handle

Lay-on, riveted
precision joint

Light weight design for maximum
user comfort in production work

Electronic Diagonal Cutters



Full Flush


#56818 Precision Electronic Diagonal Cutters, Wide Pointed Head

Cutting edge - full flush. With return spring. C70 special tool steel. For an absolutely flush cut of copper wire.

#56818	mm	Inch	Cut Capacity	Pkg.	lbs.
	138	5.5	1.3mm/16AWG	1	.22

SHOP

Electronic Diagonal Cutters



Semi Flush

#56815 Precision Electronic Diagonal Cutters, Wide Pointed Head

Cutting edge - semi flush. With return spring. C70 special tool steel. Universal small diagonal cutter for cutting copper wires.


Item No.	Cut		Medium		
#56815	mm	Inch	Capacity	Hard Wire	Pkg. lbs.
	138	5.5	2.0mm/16AWG	0.8	1 .23

SHOP

Electronic Diagonal Cutters



Wire Holding Spring



Full Flush


#56825 Precision Electronic Diagonal Cutters, Wide Shape With

Wire Holding Spring Wide, Pointed head. Cutting edge - full flush. With return spring & fixture for holding ends of wires that have been cut off. C70 special tool steel. For an absolutely flush cut of copper wire.

#56825	mm	Inch	Cut Capacity	Pkg.	lbs.
	138	5.5	1.3mm/16AWG	1	.23

SHOP

Electronic Diagonal Cutters



Full Flush


#56812 Precision Electronic Diagonal Cutters, Narrow Shape

Extra narrow, short head for working in particularly restricted spaces. Cutting edge - full flush. With return spring. C70 special tool steel. For absolutely flush cutting of copper wires in difficult to access locations.

#56812	mm	Inch	Cut Capacity	Pkg.	lbs.
	118	4.5	0.8mm/16AWG	1	.19

SHOP

Electronic Diagonal Cutters



Full Flush


Wire Holding Spring

56813 Precision Electronic Diagonal Full Flush Cutters With Wire Trapping Spring Extra narrow, short head for working in particularly restricted spaces. Cutting edge - full flush. With return spring. C70 special tool steel. For absolutely flush cutting of copper wires in difficult to access locations.

#56813	mm	Inch	Cut Capacity	Pkg.	lbs.
	128	5.0	1.0mm/16AWG	1	.19

SHOP

Electronic Oblique 48° Cutter



Full Flush


56833 Electronic Oblique 48° Cutter

Wide pointed head. Cutting edge - full flush. With cutting edge at 48° for cutting obliquely from above or from the side. C70 special tool steel. For absolutely flush cutting of copper wires in difficult to access locations.

#56833	mm	Inch	Cut Capacity	Pkg.	lbs.
	138	5.5	1.3mm/16AWG	1	.22

SHOP

Narrow Front Cutter/Long Nose Pliers



Full Flush


56830 Electronic Narrow 30° Front Cutter / Long Nose Pliers

Extremely narrow, short head for working in particularly restricted spaces. Cutting edge - full flush. Edge at 30° to face end of pliers for cutting obliquely from above or from the side. C70 special tool steel. For absolutely flush cutting of copper wires in difficult to access locations.

#56830	mm	Inch	Cut Capacity	Pkg.	lbs.
	118	4.5	0.6mm/16AWG	1	.19

SHOP

Electronic Pointed Pliers




56801 Electronic Short Nose Precision Pliers

Narrow, short head. Smooth jaws. Width at tip is only 1.2mm. C70 special tool steel. For holding small components as well as for holding and angling wires.

#56801	mm	Inch	Pkg.	lbs.
	138	5.5	1	.23

SHOP

Electronic Stripping Pliers



56871 Electronic Stripping Pliers

Wide long head with ridged gripping surface, shears blade and firm wire stripping stations. With opening spring and locking mechanism. Wire stripping stations 0.81 / 1.0 / 1.3 / 1.6 / 2.0 / 2.59mm, AWG 20 / 18 / 16 / 14 / 12 / 10.

#56871	mm	Inch	Ø	AWG	Pkg.	lbs.
	180	7.0	0.81-2.59	20-10	1	.15

SHOP

Wiha ESD Safe Pliers & Cutters

Beveled Cutter

Semi-Flush Cutter

Flush Cutter

Ultra Full Flush

Box joint for longer tool life & endurance, mirror polished finish

ESD standard IEC 61340-5-1

Two component handle with non-slip soft grip surface, protects the hand and reduces manual effort & user fatigue

Welded double leaf spring


Hardened & annealed high carbon tool steel, induction hardened cutting edges

Precision Cutters Tapered Head

Semi Flush



115mm


32703 Precision Cutters, Small Tapered Head, Semi Flush

Cutters drop-forged for an ideal material structure. Precise aligned cutting edges are additionally induction hardened at a hardness of Approx. 64°HRC. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1


#32703	mm	Inch	Copper	Head Wdth	Pkg.	lbs.
	115	4.5	1.0	9.5mm	1	.19

[SHOP](#)
Precision Cutters Tapered Head

Flush



115mm


32705 Precision Cutters, Small Tapered Head, Flush

Cutters drop-forged for an ideal material structure. Precise aligned cutting edges are additionally induction hardened at a hardness of Approx. 64°HRC. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1


#32705	mm	Inch	Copper	Head Wdth	Pkg.	lbs.
	115	4.5	1.0	9.5mm	1	.19

[SHOP](#)
Precision Cutters Tapered Head

Semi Flush



115mm


32702 Precision Cutters, Small Tapered Head With Hollow Ground Back, Semi Flush

Cutters drop-forged for an ideal material structure. Precise aligned cutting edges are additionally induction hardened at a hardness of Approx. 64°HRC. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1


#32702	mm	Inch	Copper	Head Wdth	Pkg.	lbs.
	115	4.5	1.0	9.5mm	1	.19

[SHOP](#)
Precision Cutters Tapered Head

Flush



115mm


32704 Precision Cutters, Small Tapered Head With Hollow Ground Back, Flush

Cutters drop-forged for an ideal material structure. Precise aligned cutting edges are additionally induction hardened at a hardness of Approx. 64°HRC. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1

#32704	mm	Inch	Copper	Head Wdth	Pkg.	lbs.
	115	4.5	1.0	9.5mm	1	.19

[SHOP](#)

Wiha ESD Safe Pliers & Cutters

Precision Cutters Wide Tapered Head

Bevel



115mm

11.5mm
7.5mm

#32706 Precision Cutters, Wide Tapered Head, Bevel

Cutters drop-forged for an ideal material structure. Precise aligned cutting edges are additionally induction hardened at a hardness of Approx. 64°HRC. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1

#32706	mm	Inch	Copper	Head Wdth	Pkg.	lbs.
	115	4.5	1.4	11.0mm	1	.20

SHOP

Precision Cutters Wide Tapered Head

Flush



115mm

11.0mm
7.5mm

#32708 Precision Cutters, Wide Tapered Head, Flush

Cutters drop-forged for an ideal material structure. Precise aligned cutting edges are additionally induction hardened at a hardness of Approx. 64°HRC. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1

#32708	mm	Inch	Copper	Head Wdth	Pkg.	lbs.
	115	4.5	1.2	11.0mm	1	.19

SHOP

Precision Cutters Wide Tapered Head

Full Flush



115mm

11.0mm
7.5mm

#32710 Precision Cutters, Wide Tapered Head, Full Flush

Cutters drop-forged for an ideal material structure. Precise aligned cutting edges are additionally induction hardened at a hardness of Approx. 64°HRC. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1

#32710	mm	Inch	Copper	Head Wdth	Pkg.	lbs.
	115	4.5	1.0	11.0mm	1	.23

SHOP

Precision Cutters Wide Tapered Head

Flush



115mm

11.5mm
7.5mm
(10.8mm) w/wire

#32711 Precision Cutters, Wide Tapered Head With Wire Trapping Device, Flush


Cutters drop-forged for an ideal material structure. Precise aligned cutting edges are additionally induction hardened at a hardness of Approx. 64°HRC. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1

#32711	mm	Inch	Copper	Head Wdth	Pkg.	lbs.
	115	4.5	1.2	11.0mm	1	.19

SHOP

Precision Cutters Slim Oval Form

Flush



115mm

10.5mm
7.5mm

#32712 Precision Cutters, Slim Oval Head, Flush


Cutters drop-forged for an ideal material structure. Precise aligned cutting edges are additionally induction hardened at a hardness of Approx. 64°HRC. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1

#32712	mm	Inch	Copper	Head Wdth	Pkg.	lbs.
	115	4.5	1.0	10.5mm	1	.23

SHOP

Wiha ESD Safe Pliers & Cutters
Precision Cutters Slim Oval Form

Full Flush



32714 Precision Cutters, Slim Oval Head, Full Flush

Cutters drop-forged for an ideal material structure. Precise aligned cutting edges are additionally induction hardened at a hardness of Approx. 64°HRC. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1

#32714	mm	Inch	Copper	Head Wdth	Pkg.	lbs.
	115	4.5	1.0	10.0mm	1	.23

[SHOP](#)
Precision Cutters Wide Oval Form

Bevel



32716 Precision Cutters, Wide Oval Head, Bevel

Cutters drop-forged for an ideal material structure. Precise aligned cutting edges are additionally induction hardened at a hardness of Approx. 64°HRC. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1

#32716	mm	Inch	Copper	Head Wdth	Pkg.	lbs.
	115	4.5	1.4	11.0mm	1	.19

[SHOP](#)
Precision Cutters Wide Oval Form

Flush



32720 Precision Cutters, Wide Oval Head, Flush

Cutters drop-forged for an ideal material structure. Precise aligned cutting edges are additionally induction hardened at a hardness of Approx. 64°HRC. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1

#32720	mm	Inch	Copper	Head Wdth	Pkg.	lbs.
	115	4.5	1.2	11.0mm	1	.19

[SHOP](#)
Precision Cutters Wide Oval Form And Carbide Edge

Bevel



32718 Precision Cutters, Wide Oval Head Carbide Cutting Edges, Bevel

Cutters drop-forged for an ideal material structure. Precise aligned carbide cutting edge. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1

#32718	mm	Inch	Copper	Head Wdth	Pkg.	lbs.
	110	4 3/8	1.6	11.0mm	1	.20

[SHOP](#)
Precision Cutters Wide Oval Form

Flush


32721 Precision Cutters, Wide Oval Head With Wire Trapping Device, Flush

Cutters drop-forged for an ideal material structure. Precise aligned cutting edges are additionally induction hardened at a hardness of Approx. 64°HRC. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1


#32721	mm	Inch	Copper	Head Wdth	Pkg.	lbs.
	115	4.5	1.2	11.0mm	1	.23

[SHOP](#)

Wiha ESD Safe Pliers & Cutters

Oblique Angled Cutters

Flush



32722 Oblique Angled Cutters, 29°, Flush


Oblique Cutters drop-forged for an ideal material structure. Precise aligned cutting edges are additionally induction hardened at a hardness of Approx. 64°HRC. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1

#32722	mm	Inch	Copper	Head Width	Pkg.	lbs.
	115	4.5	1.2	12.0mm	1	.24

SHOP

Oblique Angled Cutters

Ultra Full Flush



32724 Oblique Angled Cutters, 29°, Full Flush


Oblique Cutters drop-forged for an ideal material structure. Precise aligned cutting edges are additionally induction hardened at a hardness of Approx. 64°HRC. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1

#32724	mm	Inch	Copper	Head Width	Pkg.	lbs.
	115	4.5	1.0	12.0mm	1	.24

SHOP

Oblique Angled Cutters

Semi Flush



32726 Oblique Angled Cutters, 29°, Short Head, Semi Flush


Oblique Cutters drop-forged for an ideal material structure. Precise aligned cutting edges are additionally induction hardened at a hardness of Approx. 64°HRC. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1

#32726	mm	Inch	Copper	Head Width	Pkg.	lbs.
	115	4.5	1.2	12.0mm	1	.24

SHOP

Oblique Front Cutters

Flush



32728 Oblique Front Cutters, Very Small Head, 40°, Flush

Oblique Cutters drop-forged for an ideal material structure. Precise aligned cutting edges are additionally induction hardened at a hardness of Approx. 64°HRC. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1

#32728	mm	Inch	Copper	Head Width	Pkg.	lbs.
	130	5.1	0.8	8.5mm	1	.21

SHOP

ESD Safe Tool Set In Canvas Pouch



32793 11 Piece Set, 4 ESD Safe Pliers, Slotted & Phillips

Screwdrivers Pliers drop-forged for an ideal material structure. Two component non-slip soft grip handle. ESD standard IEC 61340-5-1

#32793 11 piece ESD Safe Pliers & Slotted/Phillips Precision Drivers

Set in custom case includes:

ESD Safe Pliers & Cutters

32705 4.5" Tapered Flush Cutters	32742 4.5" Snipe Nose Pliers
32728 4.375" Oblique Cutters	32746 5.7" Long Nose Pliers

ESD Safe Screwdrivers


27220 Slotted 2.0mm	27305 Phillips #00
27225 Slotted 2.5mm	27310 Phillips #0
27230 Slotted 3.0mm	27320 Phillips #1
27235 Slotted 3.5mm	

lbs. 2.43


SHOP

Wiha ESD Safe Pliers & Cutters
End Cutters Extra Slim

Semi Flush



Tip Width


#32732 End Cutters, Extra Slim, Semi Flush

End Cutters drop-forged for an ideal material structure. Precise aligned cutting edges are additionally induction hardened at a hardness of Approx. 64°HRC. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1

#32732	mm	Inch	Copper	Tip Width	Pkg.	lbs.
	130	5.1	0.6	4.1mm	1	.16

[SHOP](#)
End Cutters Wide Head

Flush




#32734 End Cutters, Wide Head, Flush

End Cutters drop-forged for an ideal material structure. Precise aligned cutting edges are additionally induction hardened at a hardness of Approx. 64°HRC. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1

#32734	mm	Inch	Copper	Head Width	Pkg.	lbs.
	115	4.5	1.4	11.0mm	1	.18

[SHOP](#)
ESD Safe Pliers

Short Snipe Nose



#32742 ESD Safe Pliers, Short Snipe Nose (Chain Nose) Straight, Serrated Jaws

Pliers drop-forged for an ideal material structure. Precisely aligned, jaws, hardened. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1

#32742	mm	Inch	Head Width	Pkg.	lbs.
	120	4 3/4	9.5mm	1	.20

[SHOP](#)
ESD Safe Pliers

Bent Snipe Nose 45°




#32744 ESD Safe Pliers, Snipe Nose (Chain Nose) Bent 45°, Smooth Jaws

Pliers drop-forged for an ideal material structure. Precisely aligned, jaws, hardened. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1

#32744	mm	Inch	Head Width	Pkg.	lbs.
	120	4 3/4	9.5mm	1	.20

[SHOP](#)
ESD Safe Pliers

Long Needle Nose


#32746 ESD Safe Pliers, Long Needle Nose Pliers, Straight, Serrated Jaws

Pliers drop-forged for an ideal material structure. Precisely aligned, jaws, hardened. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1

#32746	mm	Inch	Head Width	Pkg.	lbs.
	145	5 3/4	12.0mm	1	.27

[SHOP](#)

Wiha ESD Safe Pliers & Cutters

ESD Safe Pliers

Needle Nose, Bent 90°



32748 ESD Safe Pliers, Needle Nose Pliers, Bent 90°, Smooth Jaws

Pliers drop-forged for an ideal material structure. Precisely aligned, jaws, hardened. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1

#32748	mm	Inch	Head Wdth	Pkg.	lbs.
	145	5 3/4	12.0mm	1	.21

[SHOP](#)

ESD Safe Pliers

Short Round Nose Pliers



32750 ESD Safe Pliers, Short Round Nose Pliers, Smooth Jaws

Pliers drop-forged for an ideal material structure. Precisely aligned, jaws, hardened. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1

#32750	mm	Inch	Head Wdth	Pkg.	lbs.
	120	4 3/4	9.5mm	1	.17

[SHOP](#)

ESD Safe Pliers

Short Flat Nose Pliers



32752 ESD Safe Pliers, Short Flat Nose Pliers, Smooth Jaws

Pliers drop-forged for an ideal material structure. Precisely aligned, jaws, hardened. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1

#32752	mm	Inch	Head Wdth	Pkg.	lbs.
	120	4 3/4	9.5mm	1	.16

[SHOP](#)



32790 4 Piece ESD Safe Pliers Set In Custom Case Pliers drop-forged for an ideal material structure. Two component non-slip soft grip handle. ESD Safe Dissipative. ESD standard IEC 61340-5-1

#32790 4 piece ESD Safe Pliers Set

Set includes:

32716 4.5" Oval Side Cutters	32746 5.75" Long Nose Pliers
32752 4.75" Flat Nose Pliers	32728 4.375" Oblique Cutters

lbs. 2.06

[SHOP](#)



ESD standard
IEC 61340-5-1



[SHOP](#)

32791 11 Pc. Set, 4 ESD Safe Pliers, SYSTEM 4 Slotted & Phillips 5 Pc. Set & 2 ESD Safe Tweezers

Pliers drop-forged for an ideal material structure. Two component non-slip soft grip handle. ESD Safe Precision handle & 4 CVM tool steel blades. Tweezers anti-static conductive, ESD Safe Hypo allergenic, anti-magnetic stainless.

#32791 11 piece ESD Safe Pliers, Tweezers & SYS 4 precision

Set in custom case includes:

ESD Safe Pliers & Cutters

32716 4.5" Oval Side Cutters	32746 5.75" Long Nose Pliers
32752 4.75" Flat Nose Pliers	32728 4.375" Oblique Cutters

SYSTEM 4 Set in separate pouch

28000 ESD Safe Conductive Precision Handle

Slotted: 1.5, 2.0, 3.0 & 4.0

Phillips: 000, 00, 0 & 1

ESD Safe Tweezers: 44501 AA SA ESD 44510 7a SA ESD

lbs. 2.43

Wiha ESD Safe Protturn Pliers & Cutters

protturn

 Glare free
 black finish

 Surface resistance of handles is $10^6 - 10^9$ Ohms

 Hardened steel
 return spring


 ESD standard
 IEC 61340-5-1

 Tested ESD Safe
 handle with non-slip
 soft grip surface,
 protects the hand
 and reduces manual
 effort & user fatigue

ESD Safe Wire Stripper

protturn


165mm


45810 Protturn ESD Safe Wire Stripper

ESD standard IEC 61340-5-1. C70 special tool steel.

Glare free, black finish. ESD Safe handle with non-slip grips.


Strips 0.2, 0.3, 0.4, 0.5, 0.6, 0.8mm

#45810	mm	Inch	Strips AWG	A	B	C	Pkg.	lbs.
	165	6.5	30 to 20	30mm	12mm	4mm	1	.25


ESD Safe Long Nose Pliers

protturn


160mm


45811 Protturn ESD Safe Long Nose Pliers

ESD standard IEC 61340-5-1. C70 special tool steel.


Glare free, black finish. ESD Safe handle with non-slip grips.

#45811	mm	Inch	A	B	C	Pkg.	lbs.
	160	6.3	2mm	30mm	3mm	1	.18


ESD Safe Flat Nose Pliers

protturn


160mm


45812 Protturn ESD Safe Flat Nose Smooth Jaws Pliers

ESD standard IEC 61340-5-1. C70 special tool steel.

Glare free, black finish. ESD Safe handle with non-slip grips.


#45812	mm	Inch	A	B	C	Pkg.	lbs.
	160	6.3	2mm	32mm	3mm	1	.18



Wiha ESD Safe Protturn Pliers & Cutters

Surface resistance of handles is $10^6 - 10^9$ Ohms

ESD Safe Bent Nose Pliers



45813 Protturn ESD Safe Bent Nose Pliers


ESD standard IEC 61340-5-1. C70 special tool steel.

Glare free, black finish. ESD Safe handle with non-slip grips.

#45813	mm	Inch	A	B	C	Pkg.	lbs.
	152	6.0	2mm	30mm	4mm	1	.18

[SHOP](#)

ESD Safe Round Nose Pliers



45814 Protturn ESD Safe Round Nose Pliers


ESD standard IEC 61340-5-1. C70 special tool steel.

Glare free, black finish. ESD Safe handle with non-slip grips.

#45814	mm	Inch	A	B	C	Pkg.	lbs.
	152	6.0	2mm	22mm	3mm	1	.17

[SHOP](#)

ESD Safe Diagonal Cutters



45820 Protturn ESD Safe 21° Precision Cutters/Flush Cut

ESD standard IEC 61340-5-1. C70 special tool steel.

Glare free, black finish. ESD Safe handle with non-slip grips.

#45820	mm	Inch	AWG	A	B	C	Pkg.	lbs.
	127	5.0	18/1mm	13mm	12mm	3mm	1	.16

[SHOP](#)

ESD Safe Diagonal Cutters



45821 Protturn ESD Safe 45° Precision Cutters/Flush Cut


ESD standard IEC 61340-5-1. C70 special tool steel.

Glare free, black finish. ESD Safe handle with non-slip grips.

#45821	mm	Inch	AWG	A	B	C	Pkg.	lbs.
	127	5.0	18/1mm	10mm	9mm	2mm	1	.14

[SHOP](#)

ESD Safe Diagonal Cutters



45822 Protturn ESD Safe 21° Precision Cutters/Flush Cut

ESD standard IEC 61340-5-1. C70 special tool steel.

Glare free, black finish. ESD Safe handle with non-slip grips.


#45822	mm	Inch	AWG	A	B	C	Pkg.	lbs.
	140	5.5	16/1.3mm	13mm	12mm	3mm	1	.15

[SHOP](#)

Wiha ESD Safe Protturn Pliers & Cutters

Surface resistance of handles is $10^6 - 10^9$ Ohms

ESD Safe Diagonal Cutters



45823 Protturn ESD Safe 21° Precision Cutters/Flush Cut

ESD standard IEC 61340-5-1. C70 special tool steel. Glare free, black finish. ESD Safe handle with non-slip grips.

#45823	mm	Inch	AWG	A	B	C	Pkg.	lbs.
	133	5.25	14/1.6mm	10mm	10mm	2mm	1	.14

[SHOP](#)

ESD Safe Diagonal Cutters



45824 Protturn ESD Safe 45° Precision Cutters/Flush Cut

ESD standard IEC 61340-5-1. C70 special tool steel. Glare free, black finish. ESD Safe handle with non-slip grips.

#45824	mm	Inch	AWG	A	B	C	Pkg.	lbs.
	140	5.5	14/1.6mm	13mm	12mm	2.5mm	1	.16

[SHOP](#)

Wiha ESD Safe Protturn Pliers/Cutters, Precision Drivers & MicroBits Set

[SHOP](#)

45890 26 Pc. Set, Protturn ESD Safe Pliers, Precision Slotted & Phillips Screwdrivers, Precision Micro Bit Set & ESD Safe Tweezers
ESD Protturn Pliers glare free, black finish, ESD Safe non-slip soft grips. ESD Safe Precision Slotted & Phillips screwdrivers, CVM tool steel blades. Precision ESD Safe Micro Bit handle holds Micro Bit extension and 4mm Micro bits. Anti-static Tweezer conductive, ESD Safe Hypo allergenic, anti-magnetic stainless.

#45890 26 Piece ESD Safe Pliers, Precision Screwdrivers, Micro Bit Set & ESD Tweezer In Custom Case Includes:

ESD Safe Protturn Strippers, Pliers & Cutters

45810 - 6.5" Wire Stripper	45811 - 6.3" Long Nose Pliers
45813 - 6.0" Bent Nose Pliers	45823 - 5.25" 21° Precision Cutters

ESD Safe Slotted & Phillips Precision Screwdrivers

Slotted: 2.0, 2.5, 3.0mm	Phillips: 0, 1
--------------------------	----------------

ESD Micro Bit Handle, Micro Bit Extension & 14 Micro Bits 4mm

Hex: .7, .9, 1.3, 1.5, 2.0, 2.5, 3.0	Torx: T4, T5, T6, T7, T8, T9, T10
--------------------------------------	-----------------------------------

ESD Safe Tweezer: 44532 00 SA ESD - 120mm Heavy Duty Strong, Tapered To Strong Point

lbs. 2.05

protturn



ESD standard
IEC 61340-5-1

Surface resistance
of handles is
 $10^6 - 10^9$ Ohms

PortaCrimp Dies, Frame & Sets

PortaCrimp Tools



One piece dies - held together to prevent mix up and loss

Parallel action mimics applicator type performance



Tested to 50,000 Crimps

Reliable, ratchet controlled, ensures consistent and accurate crimp



- **Top Quality:** 50,000 cycle tested frame for longest life & consistent performance
- **Reliable:** Parallel, full cycle, ratchet controlled action ensures consistent accurate crimps
- **Easy To Use:** Designed to give user full visibility of the crimping process
- **Versatile:** Quickly and easily inter-change crimp dies on the job
- **No More Lost Die Parts!** Practical design uses guide pin to keeps die components together
- **Practical:** Pocket size dies are compact & easy to carry
- **Ergonomic:** Reduced effort ratchet assisted crimping use one hand or two with extended grip
- **Economical:** One tool frame to do the job of many, select only the dies you need

PortaCrimp Tool Sets



SHOP

43190 4 Piece PortaCrimp Die Set Electrical

Reliable, ratchet controlled, ensures consistent and accurate crimp.

Item				
No.	Set includes: Tool frame &	lbs.	Pkg.	
43190	43129, 43128, 43142	5.0	1	



SHOP

43191 4 Piece PortaCrimp Die Set Industrial

Reliable, ratchet controlled, ensures consistent and accurate crimp.

Item				
No.	Set includes: Tool Frame &	lbs.	Pkg.	
43191	43129, 43127, 43147	5.0	1	



SHOP

43192 4 Piece PortaCrimp Die Set Data Com Telco

Reliable, ratchet controlled, ensures consistent and accurate crimp.

Item				
No.	Set includes: Tool Frame &	lbs.	Pkg.	
43192	43144, 43136, 43132	5.0	1	

PortaCrimp Tool Frame



SHOP

43149 PortaCrimp Tool Frame Parallel action frame gives better performance. Symmetrical pressure with equal force mimics applicator performance. One piece die held together to prevent mix up and loss.

#43149	mm	Inch	lbs.	Pkg.
	234	9.75	1.1	1



Each die includes storage clip

PortaCrimp Dies

One piece die, held together to prevent mix up & loss. Easily interchangeable crimp dies are kept together with a special pin to simplify handling. Reliable crimping performance is consistent and accurate with a parallel action stroke, good to 50,000 cycles.


[SHOP](#)



43128 PortaCrimp Die Set For Green & Yellow Insulated Terminals & Splices

Item				
No.	Crimps	AWG	lbs.	Pkg.
43128	4-6 & 0.1-0.4mm ²	26-22 & 12-10	1.2	1

[SHOP](#)


43129 PortaCrimp Die Set For Red & Blue Insulated Terminals & Splices

Item				
No.	Crimps	AWG	lbs.	Pkg.
43129	1.5-2.5 & 0.5-1.5mm ²	22-16	1.2	1

[SHOP](#)


43142 PortaCrimp Die Set For Non-Insulated Terminals, Lugs & Splices

Item				
No.	Crimps	AWG	lbs.	Pkg.
43142	4-6 & 0.5-2.5mm ²	12-10 & 22-14	1.2	1

[SHOP](#)


43137 PortaCrimp Die Set For Non-Insulated Terminals, Lugs & Splices

Item				
No.	Crimps	Awg	lbs.	Pkg.
43137	2.5/1.5/0.75mm ²	14/16/20	1.2	1

[SHOP](#)


43139 PortaCrimp Die Set For Non-Insulated Terminals, Lugs & Splices

Item				
No.	Crimps	AWG	lbs.	Pkg.
43139	10/6/4mm ²	8/10/12	1.2	1

[SHOP](#)


43127 PortaCrimp Wire Ferrules - Insulated & Non-Insulated

Die set for 24-8 AWG (0.25-10mm).

Item				
No.	Crimps	AWG	lbs.	Pkg.
43127	10/6/4/2.5/1-1.5/25-.75mm ²	8-24	1.2	1

[SHOP](#)


43153 PortaCrimp Wire Ferrules - Insulated & Non-Insulated

Die set for 6-4 AWG (16-25mm).

Item				
No.	Crimps	AWG	lbs.	Pkg.
43153	25 & 16mm ²	6 & 4	1.2	1

[SHOP](#)


43154 PortaCrimp Wire Ferrules - Insulated & Non-Insulated

Die set for 2-1/0 AWG (35-50mm).

Item				
No.	Crimps	AWG	lbs.	Pkg.
43154	50 & 35mm ²	1/0 & 2	1.2	1

[SHOP](#)


43146 PortaCrimp Open Barrel, Non-Insulated Standard Commercial Terminals & Lugs - .250" (6.3mm) Push On Terminals

Item				
No.	Crimp	AWG	lbs.	Pkg.
43146	4-6/1.5-2.5/0.5-1.0mm ²	22-10	1.2	1

PortaCrimp Dies



One piece die, held together to prevent mix up & loss. Easily interchangeable crimp dies are kept together with a special pin to simplify handling. Reliable crimping performance is consistent & accurate with a parallel action stroke, good to 50,000 cycles.



43150 PortaCrimp Open Barrel Non-Insulated Push On Terminals DIN 46247-1 .110" (2.8mm) Tab

Item				
No.	Crimps	AWG	lbs.	Pkg.
43150	0.5-1.0/0.25-0.5/0.1-0.25mm ²	26-18	1.2	1



43151 PortaCrimp Open Barrel Non-Insulated Push On Terminals DIN 46247-2 .187" (4.8mm) Tab

Item				
No.	Crimps	AWG	lbs.	Pkg.
43151	1.5-2.5 & 0.5-1.5mm ²	22-14	1.2	1



43143 PortaCrimp Weather Pack Open Barrel Terminals

Item				
No.	Crimps	AWG	lbs.	Pkg.
43143	3.0-0.5mm ²	12-20	1.2	1



43141 PortaCrimp Fiber Optic Die set for SMA, SMB, SFR, ST, SC fiber optic connectors (.178"/.213"/.151"/.128" hex)

Item				
No.	Crimps		lbs.	Pkg.
43141	4.52/5.41/3.84/3.25mm	(.178"/.213"/.151"/.128")	1.2	1

[SHOP](#)

43136 PortaCrimp Coaxial Network & Communications

Die set for RG58, RG59, RG62AU BNC/TNC Coaxial Connectors (.213"/.255"/.068" hex).

Item	Crimps			
No.	1.69/5.41/6.48mm	lbs.	Pkg.	
43136	(.213"/.255"/.068"hex)	1.2	1	



43138 PortaCrimp Coaxial Network & Communications, CATV, HDTV, Video Die set for RG6, Belden 1694A, Twinax BNC, CATV F Coaxial Connectors (.360"/.324" Hex).

Item				
No.	Crimps	lbs.	Pkg.	
43138	9.14 & 8.23mm (.360"/.324")	1.2	1	



43140 PortaCrimp Coaxial Network & Communications


Die set for RG174, RG179 BNC/TNC Coaxil Connectors (.178"/.128"/.068" Hex, .028"(0.7mm)Sq.

Item	Crimps			
No.	4.52/3.25/1.69mm hex 0.7mm sq.	lbs.	Pkg.	
43140	(.178"/.128"/.068" hex, .028" sq.)	1.2	1	



43144 PortaCrimp Datacom/Telecom Modular Plug Die set for 8-position 8-contact (RJ45).

Item No.	RJ45	lbs.	Pkg.	
43144		1.2	1	



43132 PortaCrimp Datacom/Telecom Modular Plug

Die set for 6-position 6-contact (RJ11).

Item No.	RJ11	lbs.	Pkg.	
43132		1.2	1	

PortaCrimp Dies



One piece die, held together to prevent mix up & loss. Easily interchangeable crimp dies are kept together with a special pin to simplify handling. Reliable crimping performance is consistent & accurate with a parallel action stroke, good to 50,000 cycles.



43147 PortaCrimp Power Contacts

Item No.	Crimps	AWG	lbs.	Pkg.
43147	4 / .14-1 / 2.5 / 1.5mm	26-12	1.2	1



43148 PortaCrimp Power Contacts

Item No.	Crimps	AWG	lbs.	Pkg.
43148	6 & 10mm	10-8	1.2	1



43158 PortaCrimp Die set for heat shrink connectors:

0.5-1.5mm² red & 1.5-2.5mm² blue.

Item No.	Crimps	lbs.	Pkg.
43158	0.5-1.5mm ² (22-16AWG) red	1.2	1
	1.5-2.5mm ² (16-14 AWG) blue	1.2	1



43162 PortaCrimp Die set for heat shrink connectors:

4-6mm² yellow & 0.32-0.75mm² green.

Item No.	Crimps	lbs.	Pkg.
43162	4-6mm ² (12-10AWG) yellow	1.2	1
	0.32-0.75mm ² (22-18AWG) green	1.2	1

Professional Crimping Tools



SHOP

43652 Crimping Tool Frame Parallel action ratchet crimp tool designed to provide the best crimp without compromise on modular plug terminals. Ratchet action to ensure full crimp cycle with safety release.

#43652	mm	Inch	lbs.	Pkg.
	200	7.87		1

SHOP

43654 Tool Die D-RJ11

Item no.	lbs.	Pkg.
43654	1.0	1
Crimps:	6/6, 6/4	RJ11

SHOP

43657 Crimping Tool Die D-RJ45U (universal)

Item no.	lbs.	Pkg.
43657	1.0	1
Crimps:	8/8, 8/6, 8/4, Universal RJ45	
(Primary strain relief punch only)		

SHOP

43655 Tool Die D-RJ22

Item no.	lbs.	Pkg.
43655	1.0	1
Crimps:	4/4, 4/2	RJ22

SHOP

43658 Crimping Tool Die D-MMJ (DEC)

Item no.	lbs.	Pkg.
43658	1.0	1
Crimps:	6 pos. DEC/6	

SHOP

43656 Tool Die D-RJ45

Item no.	lbs.	Pkg.
43656	1.0	1
Crimps:	8/8, 8/6, 8/4	RJ45
(Primary & secondary strain relief punches)		

SHOP

43659 Tool Die D-10POS

Item no.	lbs.	Pkg.
43659	1.0	1
Crimps:	10 pos.	

Professional PortaCrimp Solar Connectors


[SHOP](#)

43164 PortaCrimp Die - Multi-Contact MC3

Item No.	lbs.	Pkg.
43164	.14	1
Crimps MC3 Solar Connectors: 14-10 AWG		


[SHOP](#)

43165 PortaCrimp Die - Multi-Contact MC4

Item No.	lbs.	Pkg.
43165	.16	1
Crimps MC4 Solar Connectors: 14-10 AWG		


[SHOP](#)

43166 PortaCrimp Die For Tyco Solarlok

Item No.	lbs.	Pkg.
43166	.14	1
SOLARLOK: 14-10 AWG		

Crimping Tools

Non-Insulated Crimping Tool



Self adjusting
side entry
crimp



Die Profile


[SHOP](#)

43632 Non-Insulated Crimping Tool For Non-insulated terminals, lugs, wire splices and solid/standard wires ranging from 0.75 - 6.0mm². Ratchet action to ensure full crimp cycle with safety release. Factory set for precise crimping to guarantee performance.

#43632	mm	Inch	AWG	lbs.	Pkg.
	255	10.0	22 - 10 (0.75-6.0mm ²)	1.2	1

50,000 Cycle Rated

Ergonomic Coaxial Crimping Tool



Crimp Profile
3.25/4.52/1.69mm
(.128/.178/.068"hex)



Die Profile


[SHOP](#)

43613 Ergonomic Coaxial SMA, SMB, SMC Crimping Tool

Precision ratchet crimp tool designed to provide consistent & reliable crimp connections on SMA, SMB, SMC coaxial connectors RG174, RG179 A/F. Ratchet action to ensure full crimp cycle with safety release. Factory set for precise crimping to guarantee performance.

#43613	mm	Inch	Hex Crimp Dim.	lbs.	Pkg.
	212	8.35	3.25/4.52/1.69mm (.128"/.178"/.068"hex)	1.1	1

50,000 Cycle Rated

Ergonomic Coaxial Crimping Tool



Crimp Profile
10.9/5.41/2.54/1.69mm
(.429/.213/.100/.068"hex)



Die Profile


[SHOP](#)

43628 Ergonomic Coaxial BNC, TNC Crimping Tool


Precision ratchet crimp tool designed to provide consistent & reliable crimp connections on BNC, TNC coaxial connectors RG58, RG8, RG11, Ethernet, Thinnnet. Ratchet action to ensure full crimp cycle with safety release. Factory set for precise crimping to guarantee performance.

#43628	mm	Inch	Hex Crimp Dim.	lbs.	Pkg.
	261	10.28	5.41/10.9/2.54/1.69mm (.429"/.213"/.100"/.068"hex)	1.2	1

50,000 Cycle Rated

Crimping Tools

Ergonomic Coaxial Crimping Tool



SHOP


43687 Ergonomic Coaxial Twinax CATV, F Crimping Tool

Precision ratchet crimp tool designed to provide consistent & reliable crimp connections on Twinax CATV, F coaxial connectors RG6, RG6 Quad, 1695, Twinax. Ratchet action ensures full crimp cycle with safety release. Factory set for precise crimping to guarantee performance.

#43687	mm	Inch	Hex Crimp Dim.	lbs.	Pkg.
	261	10.28	8.23/9.14/1.73mm (.360/.324/.068"hex)	1.2	1

50,000 Cycle Rated

Ergo D Sub UnInsulated/Open Barrel Crimping Tool



SHOP

43615 Ergonomic D Sub UnInsulated/Open Barrel Crimping Tool

Precision ratchet crimp tool designed to provide consistent & reliable crimp connections on UnInsulated/Open Barrel, D Sub wires ranging from 0.05 - 0.5mm². Ratchet action to ensure full crimp cycle with safety release. Factory set for precise crimping to guarantee performance.

#43615	mm	Inch	AWG	lbs.	Pkg.
	212	8.35	30 - 20 (0.08-0.5mm ²)	1.1	1

50,000 Cycle Rated

Ergo D Sub UnInsulated/Open Barrel Crimping Tool



SHOP

43617 Ergonomic D Sub UnInsulated/Open Barrel Crimping Tool

Precision ratchet crimp tool designed to provide consistent & reliable crimp connections on UnInsulated/Open Barrel, D Sub wires ranging from 0.08 - 0.5mm². Ratchet action to ensure full crimp cycle with safety release. Factory set for precise crimping to guarantee performance.

#43617	mm	Inch	AWG	lbs.	Pkg.
	212	8.35	28 - 20 (0.08-0.5mm ²)	1.1	1

50,000 Cycle Rated

Soft Grip Crimping Pliers



SHOP

326 Crimping Pliers DIN ISO 5743

Semi-circular profiles for secure connection between end sleeve and conductor. Long life is achieved through additional induction hardening. C70 special tool steel hardened & tempered. Soft vinyl grips.

Item	↔	↔	↔	↔	↔	↔
No.	mm	Inch	mm ²	AWG	Pkg.	lbs.
32604	145	5.75	0.25-2.5	14-32	1	.29
32605	180	7.0	0.25-16	6-32	1	.57

(See other soft vinyl grip pliers & cutters on pages 16-22)

Automatic Stripping Tool



Interchangeable stripping blade cassettes



Cuts & strips up to 10mm²/8 AWG - Strips PVC, THHW, TEFLON insulations



Ergonomic design with non-slip two component handles



Easy/snag free wire removal from tool - jaws stay open after strip

Self Adjusting Cut & Strip Tool



Straight Blade Cassette Stripping Range
0.02 - 10.0mm²



Cables: Conduit wire, Flex mains cable, Equipment wire, Flat modplug cable etc.

34-8 AWG

44212 Self Adjusting Cutting & Stripping Tool

Easily interchangeable stripping cassettes enables a wide range of insulations from PVC to PTFE. Light weight soft grip handle qualified for high volume production and portable/field usage.

#44212	mm	Inch	AWG	Strip Dim.	lbs.	Pkg.
	191	7.5	34 - 8	0.02-10mm²	.30	1

[SHOP](#)

Replaceable Cassette - Straight Blade



Straight Blade Cassette Stripping Range
0.02 - 10.0mm²



34-8 AWG

Straight

[SHOP](#)

44214 Straight Blade Cassette, PVC Insulations

Fine adjustability ensures that thin insulations can be stripped without damage to conductors. At the end of the stripping function, the stripping blades open and remain open during the return phase of the strip cycle facilitating easy/snag free wire removal from the tool.

#44214	AWG	Strip Range	lbs.	Pkg.
	34 - 8	0.02-10mm²	.02	1

Replaceable Cassette - 4-16mm²



Stripping Range
4-16mm²



10-5 AWG

Radius Blade

[SHOP](#)

44269 Replaceable Cassette, 4-16mm Stripping Range

Fine adjustability ensures that thin insulations can be stripped without damage to conductors. At the end of the stripping function, the stripping blades open and remain open during the return phase of the strip cycle facilitating easy/snag free wire removal from the tool.

#44269	AWG	Strip Range	lbs.	Pkg.
	10 - 5	4-16mm²	.02	1

Replaceable Cassette - "V" Blade



"V" Blade Stripping Range
0.1 - 4mm²



28-12 AWG

VBC for PTFE

[SHOP](#)

44213 Replaceable VBC or PTFE Cassette, "V" Blade

Fine adjustability ensures that thin insulations can be stripped without damage to conductors. At the end of the stripping function, the stripping blades open and remain open during the return phase of the strip cycle facilitating easy/snag free wire removal from the tool.

#44213	AWG	Strip Range	lbs.	Pkg.
	28 - 12	0.1-4mm²	.02	1




Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page
10250	7	32621	13	32693	19	32850	8	34626	21	44269	45
11625	7	32623	13	32694	18	32852	8	34627	21	45810	36
11630	7	32625	13	32695	18	32854	8	34697	21	45811	36
11960	6	32626	19	32696	18	32859	8	34698	21	45812	36
11975	6	32627	19	32697	18	32860	5	34699	21	45813	37
11980	6	32628	19	32698	16	32861	5	43127	40	45814	37
29240	7	32629	19	32702	30	32870	6	43128	40	45820	37
29250	7	32630	13	32703	30	32871	7	43129	40	45821	37
30901	24	32633	13	32704	30	32872	7	43132	41	45822	37
30903	24	32638	15	32705	30	32873	7	43136	41	45823	38
30905	24	32639	15	32706	31	32889	8	43137	40	45824	38
30907	24	32642	15	32708	31	32891	8	43138	41	45890	38
30909	24	32645	13	32710	31	32917	9	43139	40	56801	29
30911	25	32646	15	32711	31	32923	9	43140	41	56812	28
30912	24	32648	16	32712	31	32926	9	43141	41	56813	29
30913	25	32649	15	32714	32	32927	10	43142	40	56815	28
30915	25	32652	15	32716	32	32929	9	43143	41	56818	28
30917	25	32653	17	32718	32	32930	10	43144	41	56825	28
30919	25	32654	18	32720	32	32933	9	43146	40	56830	29
30921	25	32655	17	32721	32	32945	10	43147	42	56833	29
30923	26	32656	18	32722	33	32947	10	43148	42	56871	25,29
30925	26	32657	16	32724	33	32951	9	43149	39	57872	13
30926	26	32658	16	32726	33	32954	10	43150	41	76208	9
30927	26	32659	16	32728	33	32956	10	43151	41	76210	9
30928	26	32660	14	32732	34	32969	27	43153	40	76212	9
30929	26	32661	14	32734	34	32970	22	43154	40	76215	9
30931	26	32662	18	32742	34	32971	22	43158	42	76290	9
30933	26	32663	14	32744	34	32972	22	43162	42	91230	8
30937	26	32664	14	32746	34	32974	22	43164	43	91256	4
30939	26	32665	14	32748	35	32975	22	43165	43		
30943	26	32666	18	32750	35	32976	22	43166	43		
30947	24	32667	14	32752	35	32978	22	43190	39		
30990	27	32668	14	32790	35	32979	22	43191	39		
30991	27	32669	14	32791	35	32980	22	43192	39		
30993	27	32670	14	32793	33	32981	10	43612	23		
30998	27	32671	16	32804	6	32983	10	43613	43		
32390	11	32672	16	32806	6	32984	10	43615	44		
32600	15	32674	16	32807	6	32985	11	43617	44		
32601	17	32676	16	32808	6	32986	11	43618	23		
32602	15	32678	16	32810	6	32987	11	43624	23		
32603	12	32679	17	32814	4	32988	11	43628	43		
32604	15,44	32680	16	32816	4	32995	22	43632	43		
32605	15,44	32681	18	32818	4	32996	22	43643	23		
32606	12	32682	18	32820	4	32999	11	43652	42		
32607	15	32683	18	32821	4	34610	20	43654	42		
32608	17	32684	18	32826	5	34611	20	43655	42		
32609	12	32685	18	32828	5	34612	20	43656	42		
32610	16	32686	18	32830	5	34615	20	43657	42		
32611	16	32687	18	32832	5	34616	20	43658	42		
32612	12	32688	18	32834	5	34617	20	43659	42		
32614	15	32689	18	32835	5	34620	21	43687	44		
32615	12	32690	18	32836	5	34621	21	44212	45		
32616	12	32691	18	32838	5	34622	21	44213	45		
32618	13	32692	18	32841	4	34625	21	44214	45		

This image shows a single sheet of white paper with horizontal ruling lines. The lines are evenly spaced and run across the width of the page. There are no margins, text, or other markings on the paper.

(800) 494-6104
 fax: (800) 494-7456
 email: cservice@wiha.com
www.wiha.com

**SEE OUR GREAT
 WEB SPECIALS!**



Wiha Quality Tools

1348 Dundas Circle
 Monticello, MN 55362
 tel: 763.295.6591
 fax: 763.295.6598

Wiha Tools Canada Ltd.


www.wiha.com
 Brampton, ONT L6T 4X4
 tel: 866.494.0096 or 763.295.6591
 fax: 763.295.6598

To:


Catalog Item No. 99977.wo
 version - 5/15/14

Subject to change
 without notice

©2014 Willi Hahn Corporation




91330.wo - Tooling Catalog



99004.wo - Shop Tools Catalog



99914.wo - TORX Catalog



99002.wo - Screwdrivers Catalog



99919.wo - Insulated Catalog



99001.wo - TorqueControl Catalog



99934.wo - Hex Tools Catalog



99006.wo - Tech Tools Catalog



99945.wo - ESD Catalog



99951.wo - Bits Catalog