



SUB-MINIATURE LAMPS

vch
INTERNATIONAL

T-1 ³ / ₄	6mm	Lamp Number	Volts	Amps	Lumens	MSCP	Life (hours)	Filament Shape
Midget Groove (S5.7s) 	FIG. 23	CM8705	6.0	0.04	0.40	0.03	10,000	C-2R
		CM337	6.0	0.20	7.50	0.60	1,000	C-2R
		CM379	6.3	0.20	5.00	0.40	20,000	C-2R
		CM398	6.3	0.20	6.90	0.55	3,000	C-2R
		CM7354	12.0	0.04	1.50	0.12	10,000	C-2V
		CM386	14.0	0.08	3.80	0.30	15,000	C-2F
		CM336	14.0	0.08	6.30	0.50	1,000	C-2F
		CM393	14.0	0.10	6.30	0.50	10,000	C-2F
		CM346	18.0	0.04	1.90	0.15	10,000	C-2F
		CM7355	28.0	0.04	2.50	0.20	20,000	C-2F
		CM388	28.0	0.04	4.00	0.30	7,000	C-2F
		CM334	28.0	0.04	4.50	0.34	4,000	C-2F
		788	36.0	0.03	3.50	0.28	5,000	C-2F
		790	48.0	0.025	2.80	0.22	5,000	CC-2F
		799	60.0	0.02	2.20	0.17	3,000	CC-2F
Bayonet (BA7s) 	FIG. 24	282	6.0	0.6	2.50	0.20	5,000	C-2R
		284	12.0	1.2	5.00	0.40	5,000	C-2V
		1120	12.0	1.4 ¹	7.5 ¹	0.60 ¹	1,000 ¹	C-2F
		281	12.0	2.0 ²	7.50 min ²	0.60 min ²	1,000 ²	C-2V
		285	24.0	1.0	3.00	0.24	7,000	C-2F
		283	24.0	3.0 ³	10.00	0.80	3,000	C-2F
		¹ at 13V	² at 13.5V	³ at 28V				