




1LN1-5RH
DRAWING NUMBER
ISSUE 5
CHECK
REVISIONS
A CO16227
L M H
SEP 61
B CO18346
VDF
14 NOV 63
C CO55988
M A M
OCT 84
CHECK
D
E
F
G
H
I
J
K
L
M
N
O
P
Q
R
S
T
U
V
W
X
Y
Z
LMH 5 SEP 61
DRAWN
FC-30378-003

MICRO SWITCH
A DIVISION OF MINNEAPOLIS HONEYWELL REGULATOR COMPANY
FREEPORT, ILLINOIS
FED. MFR. CODE 91929

SWITCH - ENCLOSED

CATALOG LISTING
1LN1-5RH



NOTE -
1- DOWEL HOLES WILL ACCEPT .187 MAX DIA DOWEL PINS
ON 3.250 X .375±.002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.		
CHARACTERISTICS	ELECTRICAL DATA	
OPERATING FORCE - - - - - 6 LB MAX	CONTACT ARRANGEMENT	SCALE FULL
RELEASE FORCE - - - - - 1 LB MIN	(SEE CIRCUIT DIAGRAM)	DO NOT SCALE PRINT
DIFFERENTIAL TRAVEL - - - .030 MAX	-L25- 10 A-125 OR 250 VAC 1/2 HP-125 VAC RU	UNLESS OTHERWISE SPECIFIED
OVERTRAVEL - - - - - .172 MIN		DIMENSIONS ARE IN INCHES
		TOLERANCES ARE:
		ONE PLACE (.0) ±.030
		TWO PLACE (.00) ±.015
		THREE PLACE (.000) ±.005
		ANGLES ±
		WEIGHT