




Four sizes each with a stack height of .17" (4.3mm) to accommodate different flat cable widths. All sizes are available with adhesive backing or can be screw applied.

Part Number: FCM1-S6-C14

Product Family: Latching Flat Cable Mounts

Product Line: Flat/Ribbon Cable

RoHS Compliancy Status: Compliant

Part Description: Adhesive Backed Latching Flat Cable Holder

Product Type: Mounting Device

Material: Nylon 6.6

Color: Gray

UL Recognized: E136577

Length (In.): 1.21

Length (mm): 30.7

Width (In.): 1.00

Width (mm): 25.4

Cable Width (In.): 1.06

Cable Width (mm): 26.7

Environment: Indoors

Flammability Rating: UL94 V-2

Max. Flat Cable Width (In.): 1.00

Max. Flat Cable Width (mm): 25.4

Metric Screw Size: M3

Mounting Method: #6 (M3) Screw

Open Length (In.): 2.90

Open Length (mm): 73.7

Screw Size: #6 (M3)

Std. Pkg. UOM: PK

UOM: PC

Std. Pkg. Qty.: 100

Min. Order Qty.: 100