

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

15-91-6029

Status:

Active

Overview:

SL™ Modular Connectors

Description:

2.54mm Pitch SL™ Wire-to-Board Header, Low Profile, Surface Mount, Single Row, Right Angle, 3.05mm Pocket, Shrouded, with Press-fit Plastic Peg, 2 Circuits, Tin (Sn) Plating, Embossed Tape Packaging



Series

image - Reference only

Documents:

- [Drawing \(PDF\)](#)
- [Product Specification PS-70400 \(PDF\)](#)
- [Product Specification PS-70541 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

General

|                |                        |
|----------------|------------------------|
| Product Family | PCB Headers            |
| Series         | 70634                  |
| Application    | Signal, Wire-to-Board  |
| Overview       | SL™ Modular Connectors |
| Product Name   | SL™                    |
| UPC            | 800756084244           |

Physical

|                                |                                |
|--------------------------------|--------------------------------|
| Breakaway                      | No                             |
| Circuits (Loaded)              | 2                              |
| Circuits (maximum)             | 2                              |
| Color - Resin                  | Black                          |
| Durability (mating cycles max) | 25                             |
| Flammability                   | 94V-0                          |
| Glow-Wire Compliant            | No                             |
| Lock to Mating Part            | Yes                            |
| Material - Metal               | Brass, Phosphor Bronze         |
| Material - Plating Mating      | Tin                            |
| Material - Plating Termination | Tin                            |
| Material - Resin               | High Temperature Thermoplastic |
| Net Weight                     | 1.840/g                        |
| Number of Rows                 | 1                              |
| Orientation                    | Right Angle                    |
| PCB Locator                    | Yes                            |
| PCB Retention                  | Yes                            |
| PCB Thickness - Recommended    | 1.60mm                         |
| Packaging Type                 | Embossed Tape on Reel          |
| Pitch - Mating Interface       | 2.54mm                         |
| Plating min - Mating           | 3.810µm                        |
| Plating min - Termination      | 3.810µm                        |
| Polarized to Mating Part       | Yes                            |
| Polarized to PCB               | Yes                            |
| Shrouded                       | Fully                          |
| Stackable                      | No                             |
| Temperature Range - Operating  | -40°C to +105°C                |
| Termination Interface: Style   | Surface Mount                  |

Electrical

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 3A   |
| Voltage - Maximum             | 250V |

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series  
70634Series

Mates With  
SL™ Crimp Housing 70066 Option N, 70066 Option G, 70066 Option A, 70430 Option G, 70400 Option G

**Solder Process Data**

|                              |                           |
|------------------------------|---------------------------|
| Lead-free Process Capability | Reflow Capable (SMT only) |
| Process Temperature max. C   | 260                       |

**Material Info**

|                 |            |
|-----------------|------------|
| Old Part Number | 70634-0106 |
|-----------------|------------|

**Reference - Drawing Numbers**

|                       |                    |
|-----------------------|--------------------|
| Product Specification | PS-70400, PS-70541 |
| Sales Drawing         | SDA-70634-****     |

This document was generated on 10/15/2014

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15-91-6029](#)