



Dimensions: mm (in)



Switch Function

| POS.1 | POS.2 |
|---------|---------|
| | |
| ON | ON |
| 2-3,5-6 | 2-1,5-4 |
| | |



P.C. Mounting

Electrical Specifications:

- Contact Resistance: 20mΩ max. initial @ 2-4VDC 100mA
- Insulation Resistance: 1,000MΩ min.
- Dielectric Strength: 1,000 V RMS@ sea level.
- Rating:
1A/250 VAC
3A/120 VAC or 28 VDC

Mechanical Specifications:

- Operating Temperature: -30° C to +85° C.
- Mechanical Life: 50,000 make-and-break cycles

Soldering Process:

- Manual Soldering: Use soldering iron of 30 watts, controlled at 350°C approximately 5 sec. while applying solder.
- Wave Soldering: Recommended Soldering Temperature: 260±5°C
Duration of Solder Immersion: 5±1sec. (PCB is 1.6mm in thickness)

Note:

- RoHS compliant by exemption.

Toggle Switch
108-2AD1T1718-EVX

Mountain
Switch

Available from Mouser Electronics

www.mouser.com

1-800-346-6873

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[108-2AD1T1718-EVX](#)