


Miniature Radial Electrolytic Capacitors



Visit Mallory's Website at www.nacc-mallory.com

Type SK Miniature Aluminum Electrolytic Capacitors

The SK series is a radial lead, high CV miniature aluminum electrolytic capacitor which is smaller in case size than other general use products. This series is suitable for those electronic products requiring small size. It is suitable for consumer electronic equipment, such as stereo radios, TV sets, etc. The aluminum case is enclosed in a vinyl sleeve. **Tolerance:** ±20%. **Operating Temperature Range:** -40 ~ +85°C.




Stock No.	Mfr.'s Type	MFD	VDC	Size (mm)	EACH	
					1-49	50-99
852-1501	SK470M010ST	47.00	10	5.0 × 11	.27	.16
852-1503	SK101M010ST	100.00	10	5.0 × 11	.30	.18
852-1505	SK221M010ST	220.00	10	6.3 × 11	.33	.18
852-6500	SK471M010ST	470.00	10	8.0 × 11	.58	.33
852-6502	SK102M010ST	1000.00	10	10.0 × 16	1.14	.77
852-6504	SK222M010ST	2200.00	10	13.0 × 21	1.32	.90
852-6506	SK332M010ST	3300.00	10	13.0 × 21	1.58	1.07
852-6508	SK472M010ST	4700.00	10	16.0 × 25	2.62	1.78
852-6510	SK682M010ST	6800.00	10	16.0 × 32	3.61	2.47
852-6512	SK103M010ST	10000.00	10	18.0 × 35	4.57	3.11
852-6516	SK220M016ST	22.00	16	5.0 × 11	.27	.15
852-6518	SK330M016ST	33.00	16	5.0 × 11	.27	.16
852-6520	SK470M016ST	47.00	16	5.0 × 11	.15	.08
852-6522	SK101M016ST	100.00	16	6.3 × 11	.36	.20
852-6524	SK221M016ST	220.00	16	8.0 × 11	.58	.33
852-6526	SK331M016ST	330.00	16	8.0 × 11	.57	.33
852-6528	SK471M016ST	470.00	16	10.0 × 13	.60	.39
852-6530	SK102M016ST	1000.00	16	10.0 × 21	.86	.60
852-6532	SK222M016ST	2200.00	16	13.0 × 21	1.46	1.00
852-6534	SK332M016ST	3300.00	16	13.0 × 26	2.16	1.47
852-6536	SK472M016ST	4700.00	16	16.0 × 32	2.52	1.76
852-6538	SK682M016ST	6800.00	16	16.0 × 35	4.95	3.36
852-6542	SK100M025ST	10.00	25	5.0 × 11	.27	.16
852-6544	SK220M025ST	22.00	25	5.0 × 11	.26	.16
852-6546	SK330M025ST	33.00	25	5.0 × 11	.27	.16
852-6548	SK470M025ST	47.00	25	5.0 × 11	.27	.15
852-6550	SK101M025ST	100.00	25	6.3 × 11	.42	.24
852-6562	SK221M025ST	220.00	25	8.0 × 11	.57	.33
852-6564	SK331M025ST	330.00	25	10.0 × 13	.59	.39
852-6566	SK471M025ST	470.00	25	10.0 × 16	1.31	.90
852-6568	SK102M025ST	1000.00	25	13.0 × 21	1.17	.79
852-6570	SK222M025ST	2200.00	25	13.0 × 26	1.72	1.17
852-6572	SK332M025ST	3300.00	25	16.0 × 32	2.92	2.00
852-6574	SK472M025ST	4700.00	25	18.0 × 35	3.30	2.25
852-6576	SK100M035ST	10.00	35	5.0 × 11	.27	.16
852-6578	SK220M035ST	22.00	35	5.0 × 11	.27	.16
852-6580	SK330M035ST	33.00	35	5.0 × 11	.27	.16
852-6582	SK470M035ST	47.00	35	6.3 × 11	.35	.21
852-6584	SK101M035ST	100.00	35	8.0 × 11	.54	.30
852-6586	SK221M035ST	220.00	35	10.0 × 13	.55	.37

Stock No.	Mfr.'s Type	MFD	VDC	Size (mm)	EACH	
					1-49	50-99
852-6590	SK331M035ST	330.00	35	10.0 × 16	.79	.55
852-6592	SK471M035ST	470.00	35	10.0 × 21	.90	.61
852-6594	SK102M035ST	1000.00	35	13.0 × 21	1.55	1.05
852-6596	SK222M035ST	2200.00	35	16.0 × 32	2.53	1.74
852-6600	SK332M035ST	3300.00	35	18.0 × 35	3.89	2.64
852-6602	SK472M035ST	4700.00	35	18.0 × 42	4.47	3.05
852-6604	SK010M050ST	1.00	50	5.0 × 11	.32	.20
852-6606	SK2R2M050ST	2.20	50	5.0 × 11	.27	.16
852-6608	SK3R3M050ST	3.30	50	5.0 × 11	.27	.16
852-6610	SK4R7M050ST	4.70	50	5.0 × 11	.27	.16
852-6612	SK100M050ST	10.00	50	5.0 × 11	.27	.15
852-6614	SK220M050ST	22.00	50	5.0 × 11	.27	.15
852-6616	SK330M050ST	33.00	50	6.3 × 11	.42	.24
852-6618	SK470M050ST	47.00	50	6.3 × 11	.38	.22
852-6620	SK101M050ST	100.00	50	8.0 × 11	.61	.36
852-6622	SK221M050ST	220.00	50	10.0 × 16	.78	.55
852-6624	SK331M050ST	330.00	50	10.0 × 21	1.01	.67
852-6626	SK471M050ST	470.00	50	13.0 × 21	1.22	.85
852-6630	SK102M050ST	1000.00	50	16.0 × 25	1.10	.76
852-6632	SK222M050ST	2200.00	50	18.0 × 35	4.39	3.00
852-6636	SK4R7M063ST	4.70	63	5.0 × 11	.27	.16
852-6640	SK220M063ST	22.00	63	6.3 × 11	.43	.26
852-6642	SK330M063ST	33.00	63	6.3 × 11	.45	.26
852-6644	SK470M063ST	47.00	63	8.0 × 11	.66	.37
852-6646	SK101M063ST	100.00	63	10.0 × 13	.56	.38
852-6648	SK221M063ST	220.00	63	10.0 × 21	.91	.61
852-6652	SK470M063ST	470.00	63	13.0 × 26	1.62	1.11
852-6654	SK102M063ST	1000.00	63	16.0 × 32	3.05	2.09
852-6658	SK010M100ST	1.00	100	5.0 × 11	.27	.15
852-6660	SK2R2M100ST	2.20	100	5.0 × 11	.27	.16
852-6662	SK4R7M100ST	4.70	100	5.0 × 11	.34	.19
852-6664	SK100M100ST	10.00	100	6.3 × 11	.45	.27
852-6666	SK220M100ST	22.00	100	8.0 × 11	.68	.38
852-6668	SK330M100ST	33.00	100	10.0 × 13	.59	.40
852-6670	SK470M100ST	47.00	100	10.0 × 16	.74	.49
852-6672	SK101M100ST	100.00	100	13.0 × 21	1.17	.79
852-6676	SK331M100ST	330.00	100	16.0 × 25	2.85	1.98
852-6678	SK471M100ST	470.00	100	16.0 × 32	3.40	2.31
852-6686	SK4R7M200ST	4.70	200	8.0 × 11	.71	.37
852-6688	SK100M200ST	10.00	200	10.0 × 13	.59	.40
852-6694	SK470M200ST	47.00	200	13.0 × 21	1.52	1.10
852-6696	SK101M200ST	100.00	200	16.0 × 25	2.68	1.83
852-6698	SK221M200ST	220.00	200	18.0 × 42	6.11	4.26
852-6702	SK2R2M250ST	2.20	250	6.3 × 11	.39	.22
852-6708	SK100M250ST	10.00	250	10.0 × 16	.98	.66
852-6710	SK220M250ST	22.00	250	13.0 × 21	5.34	3.71
852-6712	SK330M250ST	33.00	250	13.0 × 21	1.29	.88
852-6716	SK101M250ST	100.00	250	16.0 × 32	2.92	2.00
852-6718	SK010M350ST	1.00	350	8.0 × 11	.48	.34
852-6730	SK470M350ST	47.00	350	16.0 × 25	2.96	2.02
852-6732	SK101M350ST	100.00	350	18.0 × 35	6.14	4.22
852-6736	SK2R2M450ST	2.20	450	10.0 × 13	.62	.41
852-6742	SK100M450ST	10.00	450	13.0 × 21	1.59	1.08
852-6748	SK470M450ST	47.00	450	18.0 × 35	4.66	3.18

10

Type SEK Miniature High Temperature Electrolytic Capacitors

The SEK series is a radial lead, high temperature, general use miniature electrolytic capacitor. The SEK series is suitable for consumer electronic equipment, telecommunication equipment and general industry products requiring high temperatures. The aluminum case is enclosed in a vinyl sleeve. **Tolerance:** ±20%. **Operating Temperature Range:** -40 ~ +105°C.



Stock No.	Mfr.'s Type	MFD	VDC	Size (mm)	EACH	
					1-49	50-99
852-7000	SEK330M016ST	33.00	16	5.0 × 11	.35	.20
852-7002	SEK470M016ST	47.00	16	5.0 × 11	.35	.20
852-7004	SEK101M016ST	100.00	16	6.3 × 11	.43	.26
852-7006	SEK221M016ST	220.00	16	8.0 × 11	.66	.38
852-7009	SEK331M016ST	330.00	16	8.0 × 11	.51	.34
852-7012	SEK102M016ST	1000.00	16	10.0 × 21	.85	.59
852-7016	SEK332M016ST	3300.00	16	13.0 × 26	2.27	1.53
852-7018	SEK472M016ST	4700.00	16	16.0 × 32	3.04	2.06
852-7020	SEK682M016ST	6800.00	16	18.0 × 35	3.43	2.33
852-7023	SEK100M025ST	10.00	25	5.0 × 11	.24	.18
852-7022	SEK220M025ST	22.00	25	5.0 × 11	.34	.19
852-7026	SEK470M025ST	47.00	25	5.0 × 11	.36	.20
852-7029	SEK101M025ST	100.00	25	6.3 × 11	.38	.22
852-7030	SEK221M025ST	220.00	25	8.0 × 11	.68	.36
852-7032	SEK331M025ST	330.00	25	10.0 × 13	.54	.36
852-7055	SEK471M025ST	470.00	25	10.0 × 16	.82	.55
852-7036	SEK102M025ST	1000.00	25	13.0 × 21	1.23	.83
852-7038	SEK222M025ST	2200.00	25	13.0 × 26	1.90	1.32
852-7040	SEK332M025ST	3300.00	25	16.0 × 32	2.45	1.67
852-7042	SEK472M025ST	4700.00	25	18.0 × 35	4.05	2.76
852-7021	SEK682M025ST	6800.00	25	18.0 × 42	6.46	6.22
852-7044	SEK220M035ST	22.00	35	5.0 × 11	.36	.22
852-7046	SEK330M035ST	33.00	35	5.0 × 11	.38	.22
852-7048	SEK470M035ST	47.00	35	6.3 × 11	.49	.27
852-7050	SEK101M035ST	100.00	35	8.0 × 11	.56	.31
852-7052	SEK221M035ST	220.00	35	10.0 × 13	.59	.39
852-7054	SEK331M035ST	330.00	35	10.0 × 16	.87	.61
852-7056	SEK471M035ST	470.00	35	10.0 × 21	.93	.63
852-7058	SEK102M035ST	1000.00	35	13.0 × 21	1.70	1.16
852-7062	SEK332M035ST	3300.00	35	18.0 × 35	4.42	3.08

Stock No.	Mfr.'s Type	MFD	VDC	Size (mm)	EACH	
					1-49	50-99
852-7063	SEK472M035ST	4700.00	35	18.0 × 42	5.20	3.38
852-7064	SEK010M050ST	1.00	50	5.0 × 11	.35	.19
852-7066	SEK2R2M050ST	2.20	50	5.0 × 11	.35	.19
852-7068	SEK3R3M050ST	3.30	50	5.0 × 11	.30	.18
852-7070	SEK4R7M050ST	4.70	50	5.0 × 11	.35	.19
852-7072	SEK100M050ST	10.00	50	5.0 × 11	.35	.19
852-7074	SEK220M050ST	22.00	50	5.0 × 11	.35	.19
852-7076	SEK330M050ST	33.00	50	6.3 × 11	.49	.27
852-7078	SEK470M050ST	47.00	50	6.3 × 11	.58	.33
852-7080	SEK101M050ST	100.00	50	8.0 × 11	.68	.38
852-7082	SEK221M050ST	220.00	50	10.0 × 16	.76	.51
852-7084	SEK331M050ST	330.00	50	10.0 × 21	.99	.68
852-7086	SEK471M050ST	470.00	50	13.0 × 21	1.30	.88
852-7088	SEK102M050ST	1000.00	50	16.0 × 25	2.97	2.02
852-7090	SEK222M050ST	2200.00	50	18.0 × 35	3.92	2.66
852-7079	SEK010M063ST	100.00	63	10.0 × 13	.86	.48
852-7092	SEK010M100ST	1.00	100	5.0 × 11	.35	.19
852-7094	SEK2R2M100ST	2.20	100	5.0 × 11	.35	.19
852-7096	SEK3R3M100ST	3.30	100	5.0 × 11	.36	.19
852-7098	SEK4R7M100ST	4.70	100	5.0 × 11	.36	.19
852-7100	SEK100M100ST	10.00	100	6.3 × 11	.48	.27
852-7102	SEK220M100ST	22.00	100	8.0 × 11	.51	.35
852-7104	SEK330M100ST	33.00	100	10.0 × 13	.64	.42
852-7106	SEK470M100ST	47.00	100	10.0 × 16	.79	.54
852-7108	SEK101M100ST	100.00	100	13.0 × 10	1.22	.83
852-7110	SEK221M100ST	220.00	100	16.0 × 25	2.30	1.56
852-7112	SEK331M100ST	330.00	100	16.0 × 25	2.75	1.88
852-7114	SEK010M200ST	1.00	200	6.3 × 11	.66	.39
852-7118	SEK3R3M200ST	3.30	200	6.3 × 11	.43	.23
852-7124	SEK100M200ST	10.00	200	10.0 × 13	.97	.66
852-7126	SEK220M200ST	22.00	200	10.0 × 21	1.07	.68
852-7130	SEK470M200ST	47.00	200	13.0 × 21	1.62	1.11
852-7134	SEK221M200ST	220.00	200	18.0 × 42	5.61	3.81
852-7136	SEK010M250ST	1.00	250	6.3 × 11	.42	.24
852-7142	SEK4R7M250ST	4.70	250	8.0 × 11	.66	.37
852-7144	SEK100M250ST	10.00	250	10.0 × 16	.98	.66
852-7146	SEK220M250ST	22.00	250	13.0 × 21	1.40	.95
852-7148	SEK330M250ST	33.00	250	13.0 × 21	1.61	1.11
852-7150	SEK470M250ST	47.00	250	13.0 × 26	3.31	2.05
852-7152	SEK101M250ST	100.00	250	16.0 × 32	4.14	2.14
852-7166	SEK220M350ST	22.00	350	13.0 × 26	1.97	1.34
852-7170	SEK470M350ST	47.00	350	16.0 × 35	2.79	1.91
852-7180	SEK100M400ST	10.00	400	13.0 × 21	1.38	.94
852-7182	SEK220M400ST	22.00	400	13.0 × 26	2.24	1.52