

GRF1-P-C-08-1000-C1-S-S

GRF1-P-C-04-0600-C1-S-S

GRF1-P-C-04-0600-C1-S-S

GRF1-C SERIES

50 Ω GANGED MICRO-MINI RF CABLE

UL[®]
FILE NO. E111594

Technical drawing of a 5-position, 10-pin D-sub connector assembly. The drawing includes three views: a front view (top left), a side view (top right), and a detail view of the connector housing (bottom).

Front View Dimensions:

- Overall width: (6.00) .236
- Pin pitch (between positions 1-4): (5.00) .197
- Distance from centerline to position 5: (7.20) .283
- Label: **-S OPTION SHOWN**

Side View Dimensions:

- Overall length: Assembled Length = XXXX
- Distance from mounting flange to pin 1: (28.58) 1.125
- Pin pitch (between positions 1-4): (5.00) .197
- Distance from centerline to position 5: (11.60) .457
- Label: **-D-S**

Detail View Dimensions:

- Distance from mounting flange to pin 1: (15.50) .610
- Pin pitch (between positions 1-4): (5.00) .197
- Distance from centerline to position 5: (4.60) .181
- Label: **-D**

Additional Dimensions:

- Distance from mounting flange to pin 1 (detail view): (8.89) .350
- Distance from mounting flange to pin 1 (side view): (2.77) .109
- Key Up End 1
- Key Down End 1

*All parts within this catalog are built to Samtec's specifications.
Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.*