



FEATURES:

- Fits most Fluke, Tektronix, H.P. and Wavetek meters.
- Ideal for testing circuit board components.

MATERIALS:

Minigrabber®:

Insulation – Glass filled nylon

Spring – Stainless steel

Contact – Gold plated Beryllium copper.

Sheathed Banana Plug:

Insulation – Polypropylene

Spring – Nickel plated Beryllium Copper

Plug Base – Nickel plated brass.

Wire: 18 AWG, 65 x 36 t.c., PVC insulation.

RATINGS:

Operating Voltage: 300 VRMS/DC

Operating Temperature: +50°C. (+122°F.) Max.

Current 5 Amperes

ORDERING INFORMATION: Model 5428-48-XX-*

XX = Cable Lengths, Standard Lengths: 48" (1219). Additional lengths can be quoted upon request.

*= Color, -0 Black, -2 Red

Ordering Example: 5428-48-2 Indicates 48" in length, color is Red.

Ordering Example: 6231 Kit contains one 5428-48-2 Red and one 5428-48-0 Black

Additional Pop Jack accessories available: Minigrabber®: Pomona Access 90451, Multimeter Test Leads 90452, Minipincer 90453

1All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[6231](#) [5428-48-2](#) [5428-48-0](#)