

798-289 to 393

Van Damme 1 Pair Technical Specification

Pair conductor:	7 x 0.20mm (0.22mm sq.) 24AWG high purity OFC
Pair insulation:	Cross linked polyethylene (XLPE)
Pair colours:	1 x white/1 x blue ~ 1.00mm diameter
Screen:	Aluminium/polyester foil tape
Drain wire:	7 x 0.20mm (0.22mm sq.) 24AWG high purity tinned OFC
Overall jacket:	Abrasion resistant anti-kink PVC/Neoprene composite
Jacket colour:	Black ~ RAL 9005 Light green ~ RAL 6018 Blue ~ RAL 5002 Violet ~ RAL 4008 Red ~ RAL 3001 Orange ~ RAL 2007
Temp.range:	-25' ~ +70' Centigrade
D.C.resistance:	<78 ohms per Km
Capacitance:	<90pF per metre core to core <189pF per metre cores to screen
Voltage rating:	250V
Weight:	17Kg/Km
O.D:	3.50mm +/-0.10mm

Construction: Twin conductors of plain (non tinned) Oxygen Free Copper with cross linked polyethylene insulation twisted together with a tinned OFC drain wire. Shielded with an aluminium/polyester foil tape. Over-sheathed with a flexible matt PVC/Neoprene outer jacket.

Stock Code	Description
798-289	1 Pair black 100m reel
798-290	1 Pair black 500m reel
798-307	1 Pair blue 100m reel
798-119	1 Pair blue 500m reel
798-320	1 Pair red 100m reel
798-332	1 Pair red 500m reel
798-344	1 Pair light green 100m reel
798-356	1 Pair light green 500m reel
798-368	1 Pair violet 100m reel
798-370	1 Pair violet 500m reel
798-381	1 Pair orange 100m reel
798-393	1 Pair orange 500m reel