

6Way mounting base for 1170 series Circuit Breakers.



This base for the 1170 type circuit breaker will accommodate up to 6 circuit breakers of the same or mixed amperage ratings. The range is available from 3 amps to 30 amps and the amperage rating is etched on top of each circuit breaker. Each rating is also identified with an industry standard colour coded manual release trip lever.

The base will mount into a 96.50 x 27.00 mm panel cut out and is retained by one 4mm screw at each end. The polarised detachable lid is secured in place by a central thumbscrew and seats against a gasket on the base unit. Each position is fitted with two spade terminals on the input and output for 6.3 x 0.8mm female cable receptacles, these are accessible from the rear of the panel after the base is installed.

Ordering Information

Mounting Base		Plug in Breaker Type		Design Standard		Current ratings	
1170 6way Base		1170		01	Blade terminal for automotive fuse block (standard) with retaining clips	3 30A	
				02	Blade terminal for automotive fuse block without retaining clips		
				21	As design 01 but with higher interrupting capacity		
				22	As design 02 but with higher interrupting capacity		
				31	Blade terminal for automotive fuse blocks with retaining clips and ribs for higher pull-out force		
1170 6way Base	1170	01	15A	Ordering example			

E-T-A Circuit Breakers Ltd

Telford Close

Aylesbury

Bucks

HP19 8DG

Tel [01296 420336](tel:01296420336)

Fax [01296 488497](tel:01296488497)

Internet www.e-t-a.com

E-mail info@e-t-a.co.uk