




MATERIALS:

Connector:

1st End – Spade Lug

Brass per QQ-B-626, Alloy 360, ½ Hard.

Finish: Nickel plated per QQ-N-290, Class 2, 200/300 microinches.

Insulation: Polypropylene molded to spade lug body and wire. Color matches color of wire.

Wire: 18 AWG stranding 65 x 36 t.c., PVC insulated, 3.66 (.144) O.D. Marking: 1743-“*”

Connector:

2nd End – Spade Lug

Brass per QQ-B-626, Alloy 360, ½ Hard.

Finish: Nickel plated per QQ-N-290, Class 2, 200/300 microinches.

Insulation: Polypropylene molded to spade lug body and wire. Color matches color of wire.

Wire: 18 AWG stranding 65 x 36 t.c., PVC insulated, 3.66 (.144) O.D. Marking: 1743-“*”

RATINGS:

Operating Temperature: +55° C. (+131°F.) Max.

Operating Voltage: 5000 VDC

Current: 7 Amperes

ORDERING INFORMATION: Model 1743-*

*=Color Code, -0 Black, -2 Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[1743-36-2](#) [1743-36-0](#) [1743-60-2](#) [1743-60-0](#) [1743-48-0](#) [1743-48-2](#) [1743-24-2](#) [1743-12-0](#) [1743-12-2](#) [1743-24-0](#)