


| ITEM NO. | PART NUMBER | DESCRIPTION                                                      | QTY. | NOTES          |
|----------|-------------|------------------------------------------------------------------|------|----------------|
| 1        | TLY-13      | NEMA 5-15P                                                       | 1    | white overmold |
| 2        | TLY-18      | C13                                                              | 1    | white overmold |
| 3        | 30-00249    | Wire, 3C, 18 AWG, UL SJT, 300V, 105°C, 7.75 mm, VW-1, PVC, white | 1    |                |



|          |            |                 |                                                                                                                                                                |                                                                                                                  |                                                                                                                                                              |                         |         |              |
|----------|------------|-----------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------|---------|--------------|
| Revision | Date       | Description     | Notes                                                                                                                                                          |                                                                                                                  | <div>TENSILITY</div> <div>20802 Sockeye Place #130<br/>Bend, OR 97701 USA<br/>tel 541.323.3228 fax 541.323.4202<br/>800 877.670.7118 www.tensility.com</div> |                         |         |              |
| A        | 12/19/2012 | Initial release | Rated for 10 A at 125 Vac<br>RoHS, REACH and Dodd-Frank conflict materials compliant<br>Function test: no open, no reversed polarity, no short circuit, no INT |                                                                                                                  |                                                                                                                                                              |                         |         |              |
|          |            |                 |                                                                                                                                                                |                                                                                                                  |                                                                                                                                                              |                         |         |              |
|          |            |                 |                                                                                                                                                                |                                                                                                                  |                                                                                                                                                              |                         |         |              |
|          |            |                 | DIMENSIONS ARE IN MILLIMETERS<br><br>TOLERANCES:<br>X: ± 0.5 mm<br>X.X: ± 0.3 mm<br>X.XX: ± 0.05 mm                                                            | DESCRIPTION:<br>Ac cord, 1000 mm, U.S. NEMA 5-15P plug, TLY-13 to C13, TLY-18, 18 AWG, SJT wire, 30-00249, white | SIZE<br>A                                                                                                                                                    | Part number<br>11-00037 |         |              |
|          |            |                 |                                                                                                                                                                |                                                                                                                  | SCALE:1:2                                                                                                                                                    |                         | WEIGHT: | SHEET 1 OF 1 |