



Search Results

Evaluate

- FAQ's

Design a Solution

- Part Drawings
- PDF-NetKey Optic ..
- Specification Sheets
- PDF-NetKey Fiber ..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) Search Tips 

 Text Search: 'NKFSCMPC6EI-C'

Your search criteria matched only one product, shown below

NKFSCMPC6EI-C



- Meets TIA/EIA-568-B.3 requirements
- Insertion loss: .1dB typical (multimode), .2dB typical (singlemode)
- Return loss: >20dB (multimode), >40dB (singlemode)
- Non-optical disconnect maintains data transmission under tensile loads
- Each duplex plug includes housing, insert, two ferrule assemblies, two crimp sleeves, one boot for 3mm jacketed cable and two dust caps
- Fiber cable type: tight-buffered recommended
- Fiber cable size: 3.0mm jacketed cable or 1.6mm - 2.0mm jacketed cable (noted in part description)
- Field polish termination -- Panduit recommends anaerobic adhesive
- Use Field Polish Termination Kit (FIELDKIT)

▪ Part Number	NKFSCMPC6EI-C
▪ RoHS Compliancy Status	RoHS directive is not applicable
▪ Part Description	NetKey® SC Opticam® Composite Ferrule 62.5/125µm multimode simplex connector, 100 pack.
▪ Product Type	NetKey® Network Components
▪ Color	Electric Ivory (EI)
▪ Pricing Description	Netkey SC Opticam Composite Ferrule 62.5/125µm Multimode Simplex (100 Pack)
▪ Min. Order UOM	PC
▪ Min. Order Qty.	100
▪ BOM Qty. (# of Pkgs.)	0
▪ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.