

Search Results

- Evaluate
 - FAQ's
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) [Search Tips](#) 

 **Text Search: 'F5PE10H-NM5'**

Your search criteria matched only one product, shown below

F5PE10H-NM5



- Pass all TIA/EIA-568-B.3 performance requirements
- Insertion loss per connection: 0.10dB typical; 0.30dB maximum
- Include color-specific keys with positive and negative keying features to mechanically and visually distinguish connections to prevent unauthorized mating with unlike keyed or non-keyed adapters
- Part of a complete Keyed LC System that includes Opti-Core® Patch Cords and Pigtails, OptiCam® Pre-Polished Cam Connectors, Opticom® Fiber Adapter Panels (FAPs), and Mini-Com® Adapter Modules
- Factory terminated and 100% tested for insertion loss
- Insertion loss data recorded for every multimode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- Highest quality flame retardant fiber optic cable with tight-buffered coating on each optical fiber

Additional lengths and availability: Keyed LC patch cords and pigtails are available in 1m – 10m lengths in 1m increments, and 15m, 20m, and 30m lengths. For other lengths, contact Customer Service for actual lead times.

Additional keyed colors include the following: G– Violet, H– Aqua, J– Rose, K– Slate, L– Brown, P– White, Q– Charcoal, R– Lavender, S– Peach, T– Steel Blue, V– Maroon and W– Mint.

▪ Part Number	F5PE10H-NM5
▪ RoHS Compliance Status	RoHS directive is not applicable
▪ Note	Intended for use in fixed installations which are outside the scope of RoHS.
▪ Part Description	LC (keyed H - Aqua) to pigtail multimode duplex plenum pigtail, 1.6mm jacketed cable (one keyed LC connector on one end and open on the other end) – 50/125µm.
▪ Length (m)	5
▪ Fiber Compatibility	50/125µm
▪ Fiber Cable Size	1.6mm
▪ Fiber Cable Type	Jacketed
▪ Fiber Type	Multimode 50/125
▪ Cable Type	Duplex
▪ Connector 1 Type	LC Connector - Keyed H (Aqua)
▪ Connector 2 Type	Pigtail
▪ Fiber Count	2
▪ Flammability Rating	Plenum (OFNP)
▪ Key Type and Color	Keyed H Aqua
▪ No. of Fibers	2
▪ Pricing Description	LC (keyed H - Aqua) to pigtail 50µm OFNP dupl 1.6mm pigtail 5m
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	<input type="checkbox"/>

[Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.](#)