

NetManager® Horizontal Cable Managers

- Patented design
- Lightweight plastic construction provides durability and easy installation
- Removable front cover hinges 180° up or down to allow access without removing cover
- Curved surfaces maintain cable bend radius
- Pass-through holes allow for front to rear cabling
- Built in cable retainers hold cable in place for easy moves, adds, and changes
- Mount to 19" EIA racks and cabinets
- Covers, #12-24 and M6 mounting screws included


NCMHF1


NCMH2

Part Number	Part Description	No. of Rack Spaces [^]	Std. Pkg. Qty.
NCMHF1	1.7"H x 19.0"W x 3.7"D (44mm x 483mm x 95mm).	1	1
NCMHF2	3.5"H x 19.0"W x 3.7"D (88mm x 483mm x 95mm).	2	1
NCMH2	3.5"H x 19.0"W x 9.8"D (88mm x 483mm x 248mm). Snap-on rear cover.	2	1

[^]One rack space = 1.75" (44.45mm).
All product color is black.

High Capacity Horizontal Cable Managers

- Manage cables on switches with vertical cards
- Curved cable management fingers support cables as they transition to the vertical pathway
- Can be used to create cable pathways for routing cable
- Steel hinged cover provides easy access to pathway
- Pass-through holes on top and back of manager
- Mount to 19" EIA racks and cabinets
- Mounting hardware included


NCMHAEF2

NCMHAEF4

Part Number	Part Description	No. of Rack Spaces [^]	Cable Capacity				
			Cat. 6A (.298")	Cat. 6A (.289")	Cat. 6 (.250")	Cat. 5e (.187")	Fiber (3mm)
NCMHAEF2	Horizontal manager with hinged cover. Dimensions 3.5"H x 19.0"W x 8.0"D (88mm x 483mm x 204mm)	2	77	91	108	144	432
NCMHAEF4	Horizontal manager with hinged cover. Dimensions 7.0"H x 19.0"W x 8.0"D (177mm x 483mm x 204mm)	4	154	182	216	288	864

[^]One rack space = 1.75" (44.45mm).
All product color is black.