


SPECIFICATIONS

1. Rated Voltage.....12Vp-p Square Wave
2. Operating Voltage.....3~30Vp-p Square Wave
3. Max. Rated Current.....4mA
4. Min. Sound Pressure Level.....80dB/10cm
5. Capacitance at 100Hz9500 $\pm$ 30%pF
6. Resonant Frequency.....4.0 $\pm$ 0.5KHz
7. Shell Material/Color.....PC/Black
8. Operating Temperature.....-20~+80°C
9. Store Temperature.....-30~+100°C
10. Weight.....1.5g

				KEPO KEPO ELECTRONIC CO., LTD. http://www.kepo.com.tw	
No.	DESCRIPTION	APPROVED	DATE	KPT-1340	
TOLERANCES UNLESS NOTED OTHERWISE X = XX = XXX = 90° FORMED $\pm$2° ANGLES .1°		APPROVALS	DATE		
		DRAWN		UNIT	DWG NO.
		CHECKED		mm	KP3.840.202
FIRST ANGLE PROJECTION		APPROVED	03.05.30	SCALE	SHEET
				NOT TO SCALE	VER 1.2