




ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1355	A	Released	JWM	12/1/03	HO	12/19/03	JC	1/16/04



Specifications:

- Rating: 1,200V AC/DC, 12 amps
- Internal Resistance: 15 milliohms
- Operating Temp: -20°C to 80°C

Materials:

- Cable Type: Flexible PVC, Conductor: 0.75mm²
- Body: Polyamide (Nylon)
- Plug: Bronze and Brass, Nickel Plated

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
Jeff McVicker	12/1/03
CHECKED BY:	DATE:
Hisham Odish	12/19/03
APPROVED BY:	DATE:
John Cole	1/16/04

DRAWING TITLE:
Retractable Sleeve 4mm Plug to Plug Lead, Black

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	76-092	84N2134.dwg	A
SCALE: NTS	U.O.M.: Inches	SHEET: 1	OF 1