




FCIconnect.com

Copyright FCI

PRODUCT NO

SEE TABLE



mat'l. code				surface ISO 1302 ☒	tolerance ISO 406 ISO 1101	projection 	product family CARD CONN
ltr	ecn no	dr	date	tolerances unless otherwise specified		INCH/MM scale 4:1	title 1X.100/2.54 CARD CONNECTOR
F	V31419	MRC	11/5/93	angles	linear		
G	V61642	LSS	11/26/96				
H	V7098	EPK	9/25/97	0'±2'			
J	V02518	MDF	10/30/00	dr	B. ASHREFI	10/21/81	
K	M05-0199	ERE	09/15/05	enr	D.NEIDICH	11/14/85	
L	M06-0210	MHT	6/03/06	chr	D.NEIDICH	11/14/85	
				appd	D.NEIDICH	11/20/85	
sheet index	revision sheet	L	L	L	L		
		1	2	3	4		

dwg no	sheet 1 of 4	size
67207		A3
type	Product	Customer Drawing

form: A3




FCIconnect.com

Copyright FCI

PRODUCT NO

SEE TABLE



NOTES.

- ① HOUSING MATERIAL.
FILLED HIGH TEMPERATURE NYLON
COLOR. BLACK
- ② TERMINAL MATERIAL.
BODY. BRASS .010/.25 THICK.
SPRING. BE-CU. HEAT TREATED
BODY PLATING.
15u"/.38u Au OVER 50u"/1.27u Ni
IN CONTACT AREA.
SPRING PLATING. GOLD FLASH
3. MARK FCI PART NUMBER AND DATE CODE LEGIBLE
ON TUBE LABEL.
4. APPLICATION INFORMATION.
A. RECOMMENDED MOUNTING HOLE PATTERN IS SHOWN IN
FIG."1".
B. ALL MATING PINS TO BE .025/.64 SQUARE ON TRUE CENTER
OF GIVEN TERMINAL SPACINGS WITHIN .015/.38 DIA.
C. SUGGESTED MATING PIN LENGTH .350±.020/8.89±.51.
- ⑤ ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD
FREE OPTION.
- ⑥ THESE PRODUCT MEET EUROPEAN UNION DIRECTIVES AND
OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
7. THIS PART WILL WITHSTAND EXPOSURE TO 260°C PEAK
TEMPERATURE FOR 20 SECONDS IN WAVE SOLDER,
INFRA-RED OR VAPOR PHASE SOLDER PROCESS.

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101	projection INCH/MM	product family CARD CONN			
ltr	ecn no	dr	date	tolerances unless otherwise specified				title			
L				angles	linear	.XX±.01/.X±.3 .XXX±.0.005/.XX±.13 .XXXX±.0020/.XXX±.051	INCH/MM	1X.100/2.54 CARD CONNECTOR			
				0'±2'			scale 4:1	dwg no sheet 2 of 4 size			
				dr	B. ASHREFI	10/21/81		67207 A3			
				enrg	D.NEIDICH	11/14/85					
				chr	D.NEIDICH	11/14/85					
				appd	D.NEIDICH	11/20/85					
sheet index	revision sheet							type	Product	Customer	Drawing

form: A3



FCIconnect.com

Copyright FCI

PRODUCT NO	NO. OF POS.	DIM. A ±. 010/0. 25	DIM. B ±. 020/0. 51	LEAD FREE OPTION	
67207-001	1X1	. 000/-. 00	. 140/3. 56		OBSOLETE
-002	1X2	. 100/2. 54	. 240/6. 10	NOTE 5	
-003	1X3	. 200/5. 08	. 340/8. 64		
-004	1X4	. 300/7. 62	. 440/11. 18		
-005	1X5	. 400/10. 16	. 540/13. 72		
-006	1X6	. 500/12. 70	. 640/16. 26		
-007	1X7	. 600/15. 24	. 740/18. 80		
-008	1X8	. 700/17. 78	. 840/21. 34		
-009	1X9	. 800/20. 32	. 940/23. 88		
-010	1X10	. 900/22. 86	1. 040/26. 42		
-011	1X11	1. 000/25. 40	1. 140/28. 96		
-012	1X12	1. 100/27. 94	1. 240/31. 50		
-013	1X13	1. 200/30. 48	1. 340/34. 04		
-014	1X14	1. 300/33. 02	1. 440/36. 58		
-015	1X15	1. 400/35. 56	1. 540/39. 12		
-016	1X16	1. 500/38. 10	1. 640/41. 66		
-017	1X17	1. 600/40. 64	1. 740/44. 20		
-018	1X18	1. 700/43. 18	1. 840/46. 74		
-019	1X19	1. 800/45. 72	1. 940/49. 28		
-020	1X20	1. 900/48. 26	2. 040/51. 82		
-021	1X21	2. 000/50. 80	2. 140/54. 36		
-022	1X22	2. 100/53. 34	2. 240/56. 90		
-023	1X23	2. 200/55. 88	2. 340/59. 44		
-024	1X24	2. 300/58. 42	2. 440/61. 98		
-025	1X25	2. 400/60. 96	2. 540/64. 52		
-026	1X26	2. 500/63. 50	2. 640/67. 06		
-027	1X27	2. 600/66. 04	2. 740/69. 60		
-028	1X28	2. 700/68. 58	2. 840/72. 14		
-029	1X29	2. 800/71. 12	2. 940/74. 68		
-030	1X30	2. 900/73. 66	3. 040/77. 22		
-031	1X31	3. 000/76. 20	3. 140/79. 76		
-032	1X32	3. 100/78. 74	3. 240/82. 30		
-033	1X33	3. 200/81. 28	3. 340/84. 84		
-034	1X34	3. 300/83. 82	3. 440/87. 38		
-035	1X35	3. 400/86. 36	3. 540/89. 92		
-036	1X36	3. 500/88. 90	3. 640/92. 46		
-037	1X37	3. 600/91. 44	3. 740/95. 00		
-038	1X38	3. 700/93. 98	3. 840/97. 54		
-039	1X39	3. 800/96. 52	3. 940/100. 08		
67207-040	1X40	3. 900/99. 06	4. 040/102. 62	NOTE 5	

mat'l. code				surface ISO 1302 ☒	tolerance ISO 406 ISO 1101	projection 	product family CARD CONN
ltr	ecn no	dr	date	tolerances unless otherwise specified		INCH/MM scale 4:1	title 1X.100/2.54 CARD CONNECTOR
L				angles	linear .XX±.01/.X±.3		
				0'±2'	.XXX±.0.005/.XX±.13 .XXXX±.0020/.XXX±.051		
				dr	B. ASHREFI 10/21/81		dwg no 67207 sheet 3 of 4 size A3
				enr	D.NEIDICH 11/14/85		
				chr	D.NEIDICH 11/14/85		
				appd	D.NEIDICH 11/20/85		
sheet index	revision sheet						type Product Customer Drawing

form: A3



FCIconnect.com

Copyright FCI

form: A3

PRODUCT NO	NO. OF POS.	DIM. A ±. 010/0. 25	DIM. B ±. 020/0. 51	LEAD FREE OPTION
67207-041	1X41	4. 000/101. 60	4. 140/105. 16	NOTE 5
-042	1X42	4. 100/104. 14	4. 240/107. 70	
-043	1X43	4. 200/106. 68	4. 340/110. 24	
-044	1X44	4. 300/109. 22	4. 440/112. 78	
-045	1X45	4. 400/111. 76	4. 540/115. 32	
-046	1X46	4. 500/114. 30	4. 640/117. 86	
-047	1X47	4. 600/116. 84	4. 740/120. 40	
-048	1X48	4. 700/119. 38	4. 840/122. 94	
-049	1X49	4. 800/121. 92	4. 940/125. 48	
-050	1X50	4. 900/124. 46	5. 040/128. 02	
-051	1X51	5. 000/127. 00	5. 140/130. 56	
67207-052	1X52	5. 100/129. 54	5. 240/133. 10	NOTE 5

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family CARD CONN
ltr	ecn	no	dr	date	tolerances unless otherwise specified	INCH/MM scale 4:1 	title 1X.100/2.54 CARD CONNECTOR
L					angles linear .XX±.01/.X±.3		
					0'±2' .XXX±.0.005/.XX±.13 .XXXX±.0020/.XXX±.051		
				dr	B. ASHREFI	10/21/81	dwg no 67207 type Product Customer Drawing
				enr	D.NEIDICH	11/14/85	
				chr	D.NEIDICH	11/14/85	
				app	D.NEIDICH	11/20/85	sheet4 of 4 size A3
sheet index	revision sheet						