



Mechanical latch unit

Applying contactors	Type	Rebound coil voltage	
		Nominal volt.	Rated volt.
CGC-9 to 40 type (9 to 40A frame)	AL-40	AC100V	100~127V 50/60Hz
		AC200V	200~240V 50/60Hz
CGC-50 to 85 type (50 to 85A frame)	AL-85	AC300V	260~350V 50/60Hz
		AC400V	380~440V 50/60Hz
		AC500V	460~550V 50/60Hz
		DC12V	DC12V
		DC24V	DC24V
		DC48V	DC48V
		DC100V	DC100~110V
		DC125V	DC120~125V
		DC200V	DC200~220V
CGC-100, 125 type (100, 125A frame)	AL-125		
CGC-150 type (150A frame)	AL-150	AC100V	100~127V 50/60Hz
CGC-180, 220 type (180, 220A frame)	AL-220	AC200V	200~240V 50/60Hz
CGC-300, 400 type (300, 400A frame)	AL-400		

Terminal cover unit for Contactors

Applying contactors	Type		Remarks
	for 3 Pole	for 4 Pole	
CGC-100, 125 type (100, 125A frame)	AP100	AP220/4	2 pcs included
CGC-150 type (150A frame)	AP150		
CGC-180, 220 type (180, 220A frame)	AP220		
CGC-300, 400 type (300, 400A frame)	AP400	AP400	
CGC-600, 800 type (600, 800A frame)	AP600	AP600	

Terminal cover unit for Thermal overload relays

Applying relays	Type	Remarks
CGT-125	APT125	
CGT-150	APT150	
CGT-220	APT220	
CGT-400	APT400	
CGT-600	APT600	