




PRODUCT NUMBER
73305-XXXXLF

PLATING OPTION			PACKAGE OPTION		
1=	GXT	0.76 μ m	1=	TAPE ON REEL	
3=	GOLD	0.76 μ m	2=	TUBE	
5=	GOLD	1.27 μ m	3=	TAPE ON REEL IN PLASTIC BAG	

TERMINAL LOADING		
1=	FULLY LOADED	
2=	POS 2,3,4,5	
3=	POS 1,2,5,6	


WHEN NEEDED, SUFFIX LETTER "LF" INDICATES THE PRODUCT IS ROHS COMPATIBLE, SEE NOTE 4.



REFERENCE PLAN
DEFINED BY THE
2 HOLD DOWN
BEARING SURFACE

- NOTES:
- 1 - MATERIAL: HOUSING: HIGH TEMP. NYLON, COLOUR BLACK.
TERMINAL: PHOSPHOR BRONZE.
 - 2 - PLATING: CONTACT AREA: SEE TABLE.
SOLDER TAIL : 90/10 SnPb 2 μ m MIN.
WHEN SUFFIX "LF" IS REQUIRED, 2 μ m MIN MATTE TIN OVER 1.27 MIN Ni IS SUPPLIED INSTEAD OF SnPb.
NO RAW EDGES EXCEPT SOLDER TAIL TIPS
 - 3 - SOLDER TAILS COPLANARITY : 0.1 mm
 - 4 - ROHS COMPATIBLE PRODUCT SPECIFICATIONS

- 5 - PACKAGING FOR OPTION 3 : EACH REEL IS WRAPPED INTO A PLASTIC BAG TO PROTECT FROM MOISTURE DURING STACKING TIME.
- 6 - LEGAL STATEMENT: SEE GS-22-008
- 7 - LABELING:
- MEETS PACKAGING SPECS AS PER GS-14-920
- 8 - MANUFACTURING PROCESS COMPATIBILITY
- THE HOUSING WILL WITHSTAND EXPOSURE TO 245°C PEAK TEMPERATURE FOR 30 SECONDS MAX IN A CONVECTION, INFRA-RED OR VAPOR PHASE OR REFLOW OVEN.




CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code				surface				tolerance				projection				product family			
ISO 1302				ISO 1302				ISO 406				ISO 1101				MOD JACK			
tr	ecm no	dr	date	tolerances unless otherwise specified	angles	linear	±0.13	mm	scale 2:1	title				SMT RA JACK				sheet 1 of 3	
H	F06-0244	DLE	06.07.18							6 POS OUTSIDE				A3				CUSTOMER Drawing	
J	F09-0070	LSA	09.07.23							FCI				73305				sheet 1 of 3	
K	B-15798	JFA	13.09.09	±2°						D LEGRAND				P NIZZI				A3	
E	F03020	DLE	03.01.27	engf						D LEGRAND				P NIZZI				A3	
F	F04-0363	DLE	04.10.18	chr						D LEGRAND				P NIZZI				A3	
G	F05-0247	DLE	05.09.12	qpdd						P NIZZI				P NIZZI				A3	
sheet	revision	K	E	B						type				CUSTOMER Drawing				A3	
index	sheet	1	2	3															




FCIconnect.com

Copyright FCI



CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code				surface ISO 1302		✓	tolerance ISO 406 ISO 1101		projection 		product family MOD JACK										
ltr	ecn no		dr	date		tolerances unless otherwise specified						title									
A	F04-0363		DLE	04.10.18		angles	linear	±0.13			SMT RA JACK 6 POS OUTSIDE										
B	F06-0240		DLE	06.07.18																	
						±2°				scale 2:1											
						dr	D LEGRAND		04.10.18			dwg no				sheet 3 of -				size	
						engr	P NIZZI		04.10.18			73305				A4					
						chr	D LEGRAND		04.10.18												
						appd	P NZ		04.10.18												
sheet index		revision sheet										type CUSTOMER Drawing									