

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 19202-0035
Status: Active
Overview: Splices
Description: NylaKrimp™ Butt Splice for 14-16 AWG Wire, Tape and Reel

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#)
[Product Specification PS-19902-015 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
UL E32244

General

Product Family Splices
Series 19202
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview Splices
Product Name Butt, NylaKrimp™
UPC 800753047907

Physical

Barrel Type Closed - Brazed
Color - Resin Blue
Flammability 94V-2
Insulation Nylon (PA)
Material - Metal Copper
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 1.328/g
Packaging Type Adhesive Tape on Reel
Wire Size AWG 14, 16

Material Info

Old Part Number BS-N-331T

Reference - Drawing Numbers

Product Specification PS-19902-011, PS-19902-015
Sales Drawing 60002-11C, 6000211C



image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
19202Series

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Crimp Dies for MTA-100 Tape Applicator used in 3BF Press, MTA-105 Tape Applicator used in TM-2000™ Press, and ATP-301 Air Crimping Press for Mylar Tape Mounted Terminals	0192880098

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION