



**PRODUCT FINDER**

- ▶ [Large Cabinet Racks](#)
- ▶ [Communications Cabinets/Racks](#)
- ▶ [Cabinets](#)
- ▶ [Open Racks](#)
- ▶ [Server Racks](#)
- ▶ [Aluminum Enclosures and Chassis](#)
- ▶ [Small Metal Enclosures](#)
- ▶ [Die Cast Boxes](#)
- ▶ [Plastic Enclosures](#)
- ▶ [NEMA Boxes \(Water-tight Plastic and Fiberglass\)](#)
- ▶ [NEMA Boxes \(Water-tight Sheet Metal\)](#)
- ▶ [NEMA Boxes \(Water-tight Aluminum\)](#)
- ▶ [Accessories](#)
- ▶ [Brackets](#)
- ▶ [Custom Enclosures](#)

Follow BUD On:



## NEMA 4 Enclosures

### SNB Series NEMA Sheet Metal Boxes



*Click on Image for Larger View*

Designed to meet NEMA 1, 2, 4, 4X, 12, 13 and IP66 ratings. UL listed and tested to UL508-4X, UL meets UL50E requirements

**NEW!! Additional large size boxes, with enhanced design and continuous gasket (^) for superior performance.**

**[CLICK HERE TO VIEW A VIDEO](#)**

## Design Features

- Continuous seam welded 16 ga. steel or [stainless steel](#) construction
- Hinged cover clamps to the base with keyed quarter turn latch for a watertight seal
- External mounting brackets allow box to be mounted on a wall or panel without having to remove the cover and exposing internal components to the environment
- Bonding studs for grounding are provided on base and door
- Internal panel and hardware included
- UL Listed Type 1, 2, 4, 4X and 12. IP65 and IP66 ratings
- Easily machined and modified to your particular requirements
- Finish: Smooth Gray powder coat, Internal Panel - Clear Zinc plate

## New Design features(^)

- Rigid door design
- Continues gasket
- Bar folded flange to enhance seal performance
- Additional rubber washer inside mounting brackets to enhance water resistant seal
- Added locks in larger size enclosures

### SNB SERIES NEMA 4 SHEET METAL BOX WITH MOUNTING BRACKETS

| Catalog Number | External Dimensions (Base) | Wall Mounting Dimensions | Internal Panel Dimensions | Wgt. | 304 Stainless Steel Version |
|----------------|----------------------------|--------------------------|---------------------------|------|-----------------------------|
| Drawings       |                            |                          |                           |      |                             |

| Powder Coated Steel         |                         | Height | Width  | Depth | Height | Width  | Height | Width  | Lbs. | Catalog Number | Details                    |
|-----------------------------|-------------------------|--------|--------|-------|--------|--------|--------|--------|------|----------------|----------------------------|
| SNB-3730                    | <a href="#">PDF DXF</a> | 9.84"  | 7.87"  | 5.91" | 11.14" | 6.42"  | 8.46"  | 5.91"  | 7    | SNB-3730-SS    | <a href="#">Click Here</a> |
| SNB-3731                    | <a href="#">PDF DXF</a> | 11.81" | 9.84"  | 5.91" | 13.11" | 8.39"  | 10.43" | 7.87"  | 9    | SNB-3731-SS    | <a href="#">Click Here</a> |
| SNB-3732                    | <a href="#">PDF DXF</a> | 11.81" | 9.84"  | 7.87" | 13.06" | 8.39"  | 10.43" | 7.87"  | 11   | SNB-3732-SS    | <a href="#">Click Here</a> |
| SNB-3733                    | <a href="#">PDF DXF</a> | 11.81" | 11.81" | 5.91" | 13.11" | 10.35" | 10.43" | 9.84"  | 11   | SNB-3733-SS    | <a href="#">Click Here</a> |
| SNB-3734                    | <a href="#">PDF DXF</a> | 11.81" | 11.81" | 7.87" | 13.11" | 10.35" | 10.43" | 9.84"  | 12   | SNB-3734-SS    | <a href="#">Click Here</a> |
| SNB-3735                    | <a href="#">PDF DXF</a> | 15.75" | 11.81" | 5.91" | 17.05" | 14.29" | 14.37" | 9.84"  | 15   | SNB-3735-SS    | <a href="#">Click Here</a> |
| SNB-3736                    | <a href="#">PDF DXF</a> | 15.75" | 11.81" | 7.87" | 17.05" | 14.29" | 14.37" | 9.84"  | 16   | SNB-3736-SS    | <a href="#">Click Here</a> |
| SNB-3737                    | <a href="#">PDF DXF</a> | 15.75" | 15.75" | 7.87" | 17.05" | 14.29" | 14.37" | 13.78" | 22   | SNB-3737-SS    | <a href="#">Click Here</a> |
| SNB-3738                    | <a href="#">PDF DXF</a> | 7.87"  | 5.91"  | 5.91" | 9.17"  | 4.46"  | 6.49"  | 3.94"  | 5.2  | SNB-3738-SS    | <a href="#">Click Here</a> |
| SNB-3739                    | <a href="#">PDF DXF</a> | 7.87"  | 7.87"  | 3.98" | 9.17"  | 6.42"  | 6.49"  | 5.91"  | 4.6  | SNB-3739-SS    | <a href="#">Click Here</a> |
| SNB-3740                    | <a href="#">PDF DXF</a> | 9.84"  | 9.84"  | 5.91" | 11.14" | 8.39"  | 8.46"  | 7.87"  | 9.7  | SNB-3740-SS    | <a href="#">Click Here</a> |
| SNB-3741                    | <a href="#">PDF DXF</a> | 9.84"  | 7.87"  | 3.98" | 11.14" | 6.42"  | 8.46"  | 5.91"  | 5.7  | SNB-3741-SS    | <a href="#">Click Here</a> |
| SNB-3743                    | <a href="#">PDF DXF</a> | 15.75" | 13.98" | 7.87" | 17.05" | 12.53" | 14.37" | 12.01" | 19.8 | SNB-3743-SS    | <a href="#">Click Here</a> |
| SNB-3746^                   | <a href="#">PDF DXF</a> | 20"    | 16"    | 8"    | 21.27  | 14.54  | 18.62  | 14.03  | 20.3 | SNB-3746-SS    | <a href="#">Click Here</a> |
| SNB-3749^                   | <a href="#">PDF DXF</a> | 20"    | 20"    | 12"   | 21.27  | 18.54  | 18.62  | 18.03  | 29.4 | SNB-3749-SS    | <a href="#">Click Here</a> |
| SNB-3751^                   | <a href="#">PDF DXF</a> | 24"    | 16"    | 8"    | 25.27  | 14.54  | 22.62  | 14.03  | 23.5 | SNB-3751-SS    | <a href="#">Click Here</a> |
| SNB-3752^                   | <a href="#">PDF DXF</a> | 24"    | 20"    | 8"    | 25.27  | 18.54  | 22.62  | 18.03  | 27.8 | SNB-3752-SS    | <a href="#">Click Here</a> |
| SNB-3754^                   | <a href="#">PDF DXF</a> | 24"    | 24"    | 10"   | 25.27  | 22.54  | 22.62  | 22.03  | 35.3 | SNB-3754-SS    | <a href="#">Click Here</a> |
| * New sizes    ^ New Design |                         |        |        |       |        |        |        |        |      |                |                            |

[DXF](#) Autocad DXF Specifications File

[PDF](#) Adobe PDF Specifications File

(Right Click and save link to your computer. Requires CAD software such as AutoCAD)



[Download PDF Viewer](#)

For the majority of our enclosures we offer 3D STEP files upon request

