









Bridge Diodes (Schottky Barrier)

Parameter Type No.	Absolute Maximum Ratings					Electrical Characteristics (Ta=25°C)						Others		
	V _{RM} (V)	I _{F(AV)} (A) With Heatsink	I _{FSM} (A) 50Hz Half-cycle Sinewave Single Shot	T _J (°C)	T _{stg} (°C)	V _F (V)		I _R (mA)	I _R (H) (mA)	t _{rr} (ns)	R _{th(j-c)} (°C/W)	Mass (g)	Fig.	
RBA-404B	40	4.0	40	-40 to +125		0.55	2.0	2.0	20	100	100/100	5.0	4.25	Ⓐ
RBA-406B	60					0.62								
RBA-1004B	40					10.0								





RBA-404B



RBA-406B



RBA-1004B



External Dimensions

(Unit: mm)

Flammability:
UL94V-0 or Equivalent

Fig. A

