






| LOC | DIST | REVISIONS |                                            |    |      |  |
|-----|------|-----------|--------------------------------------------|----|------|--|
|     |      | REV       | DATE                                       | BY | APPD |  |
| DF  | FO   | J         | 28APR11                                    | CT | DH   |  |
|     |      | J         | TYCO LOGO REPLACED WITH THE AMP BRAND LOGO |    |      |  |



- 1 AMP TRADEMARK LOCATED IN APPROX AREA SHOWN.
- 2 STANDOFFS: POSN 12 (9) STANDOFFS AS SHOWN.  
POSN 16 (12) STANDOFFS, 3 PER DIAGONAL ROW.  
POSN 20 (15) STANDOFFS, 3 PER DIAGONAL ROW.  
POSN 24 (18) STANDOFFS, 3 PER DIAGONAL ROW.  
POSN 28 (21) STANDOFFS, 3 PER DIAGONAL ROW.  
POSN 32 (24) STANDOFFS, 3 PER DIAGONAL ROW.  
POSN 36 (27) STANDOFFS, 3 PER DIAGONAL ROW.  
POSN 40 (30) STANDOFFS, 3 PER DIAGONAL ROW.  
POSN 44 (33) STANDOFFS, 3 PER DIAGONAL ROW.  
POSN 48 (36) STANDOFFS, 3 PER DIAGONAL ROW.  
POSN 52 (39) STANDOFFS, 3 PER DIAGONAL ROW.  
POSN 56 (42) STANDOFFS, 3 PER DIAGONAL ROW.  
POSN 60 (45) STANDOFFS, 3 PER DIAGONAL ROW.
- 3 FINISH: BRIGHT TIN-LEAD .000100-.000200 THK OVER NICKEL .000050 MIN THK.
- 4 HEIGHT AFTER TERMINATION IS .238 REF.
- 5 CAVITY IDENTIFICATION MOLDED IN THIS AREA.
- 6 FINISH: BRIGHT TIN .000100-.000200 THK OVER NICKEL .000050 MIN THK.



|          |        |       |       |       |       |       |    |            |             |
|----------|--------|-------|-------|-------|-------|-------|----|------------|-------------|
|          | 6      | 2.950 | 2.950 | 3.274 | 2.950 | 2.950 | 59 | 60         | 6-111035-3  |
|          | 6      | 2.150 | 2.150 | 2.474 | 2.150 | 2.150 | 43 | 44         | 5-111035-9  |
|          | 6      | 1.950 | 1.950 | 2.274 | 1.950 | 1.950 | 39 | 40         | 5-111035-8  |
|          | 6      | 1.750 | 1.750 | 2.074 | 1.750 | 1.750 | 35 | 36         | 5-111035-7  |
|          | 6      | 1.550 | 1.550 | 1.874 | 1.550 | 1.550 | 31 | 32         | 5-111035-6  |
|          | 6      | 1.150 | 1.150 | 1.474 | 1.150 | 1.150 | 23 | 24         | 5-111035-4  |
|          | 6      | .950  | .950  | 1.274 | .950  | .950  | 19 | 20         | 5-111035-3  |
|          | 6      | .750  | .750  | 1.074 | .750  | .750  | 15 | 16         | 5-111035-2  |
|          | 3      | 2.950 | 2.950 | 3.274 | 2.950 | 2.950 | 59 | 60         | 1-111035-3  |
| OBSOLETE | 3      | 2.750 | 2.750 | 3.074 | 2.750 | 2.750 | 55 | 56         | 1-111035-2  |
| OBSOLETE | 3      | 2.550 | 2.550 | 2.874 | 2.550 | 2.550 | 51 | 52         | 1-111035-1  |
| OBSOLETE | 3      | 2.350 | 2.350 | 2.674 | 2.350 | 2.350 | 47 | 48         | 1-111035-0  |
|          | 3      | 2.150 | 2.150 | 2.474 | 2.150 | 2.150 | 43 | 44         | 111035-9    |
|          | 3      | 1.950 | 1.950 | 2.274 | 1.950 | 1.950 | 39 | 40         | 111035-8    |
|          | 3      | 1.750 | 1.750 | 2.074 | 1.750 | 1.750 | 35 | 36         | 111035-7    |
|          | 3      | 1.550 | 1.550 | 1.874 | 1.550 | 1.550 | 31 | 32         | 111035-6    |
| OBSOLETE | 3      | 1.350 | 1.350 | 1.674 | 1.350 | 1.350 | 27 | 28         | 111035-5    |
|          | 3      | 1.150 | 1.150 | 1.474 | 1.150 | 1.150 | 23 | 24         | 111035-4    |
|          | 3      | .950  | .950  | 1.274 | .950  | .950  | 19 | 20         | 111035-3    |
|          | 3      | .750  | .750  | 1.074 | .750  | .750  | 15 | 16         | 111035-2    |
| OBSOLETE | 3      | .550  | .550  | .874  | .550  | .550  | 11 | 12         | 111035-1    |
|          | FINISH | F     | E     | D     | C     | B     | A  | NO OF POSN | PART NUMBER |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN J. PEACHEY 05-MAR-86  
CHK M. SCULLY 23-MAY-86  
APPD D. HOFFMAN 23-MAY-86  
NAME  
PRODUCT SPEC  
APPLICATION SPEC 114-40005  
WEIGHT  
CUSTOMER DRAWING

DIMENSIONS: INCHES

0 PLC ± -  
1 PLC ± -  
2 PLC ± -  
3 PLC ± .005  
4 PLC ± -  
ANGLES ± -

FINISH

MATERIAL MOLDED PARTS: 94V-0 RATED  
THERMOPLASTIC COLOR BLACK  
CONTACTS PH BRZ PER QQ-B-750

TE Connectivity

KIT, AMP-LATCH PADDLEBOARD  
PREASSEMBLED, .100 LONG POSTS  
FULL ROW, FULL TIN PLATED CONTACTS

SIZE CAGE CODE DRAWING NO  
A1 00779 111035

RESTRICTED TO

SCALE 10:1

SHEET 1 OF 1

REV J

4805 (3/11)