

LOC	DIST	REVISIONS					
P	LTR	DESCRIPTION			DATE	DWN	APVD
		REVISED PER ECO-11-023039			21FEB12	KH	MS

MATERIAL:
HOUSING: THERMOPLASTIC, UL94V-2, BLACK.
TERMINAL: BRASS, BRIGHT TIN PLATED.
SCREWS: 6-32, STEEL, ZINC AND CHROMATE PLATED.

ELECTRICAL:
MAXIMUM CURRENT: 20A.
OPERATING VOLTAGE: 600V.
WIRE RANGE: 12 AWG MAX.

ENVIRONMENT:
OPERATING TEMP.: -60°C TO +105°C



- 1

WHITE INK MARKING, APPROX AS SHOWN.
- 2

NICKEL PLATED BRASS SCREW.
- 3


OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 4

ALL SCREWS BOTTOMED, TORQUE 2 TO 4 IN-LBS



SEE FIGURE 3 OBSOLETE

7.562	17	SSB7FP170201	1-1546972-7
7.125	16	SSB7FP16020111	9-796602-4
7.125	16	SSB7FP160201	1-1546972-6
6.687	15	SSB7FP150201	4-1437416-6
6.250	14	SSB7FP140203	1546561-4
6.250	14	SSB7FP140201	4-1437416-5
5.812	13	SSB7FP130201	4-1437416-3
5.375	12	SSB7FP120201	4-1437416-0
4.937	11	SSB7FP110201	1-1546972-1
4.500	10	SSB7FP100203	3-1437416-6
4.500	10	SSB7FP100201	3-1437416-4
4.062	9	SSB7FP090203	1-1546561-9
4.062	9	SSB7FP090201	1546972-9
3.625	8	SSB7FP08020111	1986330-3
3.625	8	SSB7FP080203	2-1437416-9
3.625	8	SSB7FP080201	1546972-8
3.187	7	SSB7FP070203	2-1437416-6
3.187	7	SSB7FP07020111	2-1437416-5
3.187	7	SSB7FP070201	2-1437416-4
2.750	6	SSB7FP06020111	1986330-2
2.750	6	SSB7FP060203	2-1437416-3
2.750	6	SSB7FP060201	2-1437416-1
2.312	5	SSB7FP050203	2-1546972-7
2.312	5	SSB7FP050201	1-1437416-5
1.875	4	SSB7FP04020111	1986330-1
1.875	4	SSB7FP040203	1-1437416-3
1.875	4	SSB7FP040201	1-1437416-1
1.437	3	SSB7FP030201	1437416-6
1.000	2	SSB7FP020201	1437416-2
DIM A	NO. OF POS.	CATALOG NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLGEL 2/10/05		 TE Connectivity							
		CHK S YODER 2/10/05									
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S YODER 2/10/05		NAME					
		0 PLC ± —		SSB7FPXX0201							
		1 PLC ± —									
		2 PLC ± .02									
		3 PLC ± .010									
4 PLC ± —		PRODUCT SPEC									
ANGLES ± 1°		APPLICATION SPEC									
MATERIAL		FINISH		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
—		—		A3		00779		C-9-796602-2		—	
CUSTOMER DRAWING						SCALE		SHEET		REV	
						NTS		1 OF 2		A	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC
FT

DIST
0

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

1

2

3

4

5

6

7

2-1437416-5

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

16

1986330-1

1

2

3

4

5

6

1986330-2

1

2

3

4

5

6

7

8

1986330-3

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

16

17

18

19

20

21

22

23

24

1986330-5

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

16

17

18

19

20

21

22

23

24

1986330-1

2

11.937

27

SSB7FP270201

9-796602-2

11.500

26

SSB7FP260203

1-1546561-8

11.500

26

SSB7FP260201

2-1546972-6

11.062

25

SSB7FP250201

2-1546972-5

10.625

24

SSB7FP24020111

1986330-5

10.625

24

SSB7FP240201

2-1546972-4

10.187

23

SSB7FP230201

2-1546972-3

9.750

22

SSB7FP220201

2-1546972-2

9.312

21

SSB7FP210201

2-1546972-1

8.875

20

SSB7FP200201

2-1546972-0

8.437

19

SSB7FP190201

1-1546972-9

8.000

18

SSB7FP180201

1-1546972-8

DIM A

NO. OF POS.

CATALOG NUMBER

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

0

1

2

3

4

PLC

± -

± -

± .02

± .010

± -

ANGLES

± 1°

0

1

2

3

4

PLC

± -

± -

± .02

± .010

± -

FINISH

-

DWN
S SCHL GEL

2/10/05

CHK
S YODER

2/10/05

APVD
S YODER

2/10/05

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

SCALE
NTS

TE Connectivity

SSB7FPXX0201

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-9-796602-2

RESTRICTED TO
-

SHEET
2 OF 2

REV
A

1470-19

(3/11)