

| NUMBER<br>OF POSITIONS | DIMENSION |       |
|------------------------|-----------|-------|
|                        | A         | B     |
| 08                     | 7.62      | 14.86 |
| 10                     | 10.16     | 17.40 |
| 12                     | 12.70     | 19.94 |
| 14                     | 15.24     | 22.48 |
| 16                     | 17.78     | 25.02 |
| 18                     | 20.32     | 27.56 |
| 20                     | 22.86     | 30.10 |
| 22                     | 25.40     | 32.64 |
| 24                     | 27.94     | 35.18 |
| 26                     | 30.48     | 37.72 |
| 30                     | 35.56     | 42.80 |
| 34                     | 40.64     | 47.88 |
| 36                     | 43.18     | 50.42 |
| 40                     | 48.26     | 55.50 |
| 44                     | 53.34     | 60.58 |
| 50                     | 60.96     | 68.20 |
| 60                     | 73.66     | 80.90 |
| 64                     | 78.74     | 85.98 |

# NOTES:

Insulator Material: PBT, UL 94V-0

Contact Plating: Nickel 50μ"

Contact Material: Brass

Current Rating : 1A AC,DC

Contact Resistance: 20MΩ Max.










Dielectric Withstanding: AC 500V

Insulator Resistance: 1000MΩ Min.

Operating Temp.: -40°C~+105°C

RoHS


| REV. | DESCRIPTION | DATE      |
|------|-------------|-----------|
| A    | RELEASE     | 2012/11/7 |



8P


10P-12P

14P-64P



# Mating Part Number

|                   |                   |                   |
|-------------------|-------------------|-------------------|
| 3020-ALL          | 3010-XX-001-11-XX | 3010-XX-001-12-XX |
| 3010-XX-002-12-XX | 3010-XX-003-12-XX |                   |

|                                                                                                  |              |            |        |                                                                        |
|--------------------------------------------------------------------------------------------------|--------------|------------|--------|------------------------------------------------------------------------|
| UNLESS TOLERANCE                                                                                 |              | DRAW BY    |        | <div>CnC Tech,LLC</div> <div>Part NO.</div> <div>3030-XX-0102-99</div> |
| GENERAL                                                                                          | ANGLE        | DESIGN BY  |        |                                                                        |
| X. ± 0.30                                                                                        | X.* ± 3.0°   | CHECK BY   |        |                                                                        |
| .X ± 0.25                                                                                        | .X* ± 2.0°   | APPROVE BY |        |                                                                        |
| .XX ± 0.20                                                                                       | .XX* ± 1.0°  |            |        |                                                                        |
| .XXX ± 0.10                                                                                      | .XXX* ± 0.5° |            |        |                                                                        |
| <div></div> |              | SCALE      | SHEET  | UNIT                                                                   |
|                                                                                                  |              | 1:1        | 1/1    | MM                                                                     |
|                                                                                                  |              | DRW NO:    |        |                                                                        |
|                                                                                                  |              |            | REV: A |                                                                        |