





JKL LAMP NUMBER	VOLTS RATED	AMPS $\pm 10\%$	MSCP $\pm 25\%$	LUMENS $\pm 25\%$	AVERAGE LIFE HRS.	FILAMENT TYPE
24E1	24.0	.035	.160	2.01	8,000	C-2F
24B1	24.0	.040	.239	3.00	4,000	C-2F
24C1	24.0	.072	.278	3.49	6,000	C-2V
35A1	35.0	.040	.239	3.00	7,500	C-2F
48D1	48.0	.021	.160	2.01	20,000	CC-2F
55C1	55.0	.050	.478	6.01	5,000	CC-2F



DIMENSIONS ARE IN MILLIMETERS
TOLERANCE UNLESS OTHERWISE SPECIFIED
1 PL +/- 0.2
2 PL +/- 0
ANGLE +/- 0

JKL

COMPONENTS CORPORATION

TITLE

T-2 TELEPHONE SLIDE BASE ANSI #1

DRAWN BY
L. WENGSTROM

APPVD BY DATE
S.C. 4/11/07

SIZE
A

FSCM NO.
55335

DRAWING NO.

SLIDE BASE ANSI #1

- CAD DRAWING -
MANUAL REVISIONS NOT PERMITTED

SCALE

NONE

RELEASED DATE
8/16/00

REVISION DATE
4/11/07

REV. NO. **A**

SHEET
1 OF 1

REV. NO.	DESCRIPTION/ECO NUMBER	APPVD DATE
A	ADD PART NO. 24C1 RELEASED	4/11/07 8/16/00