




FCI

FCI P/N	"L"
(NOTE 1)	
54176-YXXX	XXX



SPECIFICATIONS		
	MTRJ	ST
INSERTION LOSS	0.5dB MAX	0.6dB MAX
RETURN LOSS	20dB MIN	N/A
FIBER PROTRUSION	100nm MAX	50nm MAX
APEX OFFSET	N/A	45um MAX
FIBER UNDERCUT	SEE TELECORDIA GR-326	

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	 www.fciconnect.com
ltr	ecn no	dr	date				
A	V12300	JJK	10/01/01	linear	NOMINALS ONLY	projection	title
B	V12373	JJK	1/3/02		UNLESS NOTED		
C	V20480	JRW	4/1/02	angles		 MM	product family FIBER OPTICS
				dr	J. KILE	10/01/01	
				enrg	S. CLARK	10/01/01	size
				chr	S. CLARK	10/01/01	
				appd	S. CLARK	10/01/01	dwg no
sheet index	revision					scale	A4
	sheet					1:1	
							54176
							sheet 1 of 1
							cage code
							22526

- NOTES:
- FCI PART NUMBER CONSISTS OF THE DWG NO, A DASH, AND A SUFFIX YXXX WHERE Y IS THE UNIT OF LENGTH (Y=M IS METERS, Y=F IS FEET) AND WHERE XXX IS THE LENGTH OF "L"
(EX. 54176-M004 IS 4 METERS IN LENGTH)
 - LENGTH IS MEASURED IN A LINEAR STATE FROM CONNECTOR TIP TO CONNECTOR TIP.

ACAD

PDM: Rev:C

STATUS:Released

Printed: Aug 14, 2008