

■ CHARACTERISTICS

LU-085

Range of Values (Ω): 1K, 5K, 10K, 50K, 100K, 500K

Tolerance: $\pm 20\%$

Resistance Taper: Linear

Wattage Rating: 0.1W

Minimum Resistance: 5% max.

Rotational Torque: 50 ~ 350gcm

Rotational Life: $\pm 15\%$ max. after 100 rotations

Stop-end Torque: 1kg-cm min.

Rotational Angle: $230^\circ \pm 20^\circ$

Temperature Characteristic: +5% and -20% max. after 250 hours at 70°C

LU-083

Range of Values (Ω): 1K, 5K, 10K, 50K, 100K, 500K


Wattage Rating: 0.1W

Rotational Torque: 40 ~ 300gcm

Rotational Angle: $25^\circ \pm 20^\circ$

Max. Ambient Temperature: $+50^\circ\text{C}$

■ PART NUMBERING SYSTEM



■ DIMENSIONS (mm)

