

VN-711PC

- USB connection for fast downloading to PC
- Recording Scenes
- 5 folders for file storage, 200 messages per folder
- Long battery life
- 2GB internal memory / up to 800 hours recording (LP mode)
- Low Cut-Filter
- Voice activated recording (VCVA)
- Built-in stand



Speak. Record. Transfer

The new VN-PC series is absolutely ideal for anybody looking for a user-friendly voice recorder with outstanding long battery life. As an excellent entry-level device the VN-711PC offers fine WMA recording quality and 2GB memory enabling an outstanding recording time of more than 800 hrs in LP mode. As well as featuring probably the best low-noise microphone in its class for superior sound reproduction, it also has a high-speed USB connection for organising and archiving recordings on a PC or Mac, or sharing them via e-mail – and all this with great ease. And the benefits don't stop here either. They include the low-cut filter for noise reduction while recording, the Scene Select and Automatic Recording (VCVA) features and 99 Index Marks – all designed for maximum user-friendliness.

Specifications

Storage Media

Internal / Removable Media	Internal only
microSD / microSDHC card	No
Internal memory	2GB

USB functionality

USB Speed	USB 2.0 High Speed
USB Classes	USB Storage class

Display

Display colour	White
Display Size	29 x 29mm / 1.61"
Display Type	Full Dot Matrix Display (108 x 84)
Font size setting	Yes

Device operation

HOLD switch	Yes
Power switch	Yes

Recording Modes

Recording format	WMA
Maximum Recording Time	823h (LP mode)
HQ	131h
SP	258h
LP	823h

Playback Modes

Playback format	WMA
-----------------	-----

Sampling frequency

HQ	44.1kHz / 32kbps
SP	22kHz / 16kbps
LP	8kHz / 5kbps

Frequency response

HQ	70 - 16.000Hz
SP	70 - 8.000Hz
LP	70 - 3.000Hz

Record function

Index	Up to 99 per file
Operation	
Auto recording	VCVA recording
Recording Scenes	Memo Meeting User Defined Setting Conference
Sound control	Rec Monitor Low Cut-Filter

Playback function

Playback speed	Fast (10 steps Max. x2.0) / Slow (5 steps Min. x0.5)
Playback control	Playback Speed Control
File operation	Forward / Reverse Skip FF/REW
File selection	Folder Playback File Playback
Repeat functions	A-B repeat playback Repeat playback
Sound enhancement	Voice Filter

Data organisation

No. of folders for Voice	5
Files per folder	200
File divide	No
Calendar Search	No
Erase	Erase all files Erase single files

Other Features

Beep signal (system sound)	Yes
----------------------------	-----

Software

Corresponding Audio software (name)	Sonority
-------------------------------------	----------

Interfaces Input

Microphone sensitivity / gain	HI/LO
PC interface	USB Storage class
Microphone jack	Yes
Microphones	Built-in mono microphone

Interfaces Output

Speaker Diameter	Built-in ø 28 mm round dynamic speaker
Max. working output	250mW
Earphone jack	Yes

Power Supply

Power Supply	2 x AAA batteries or Ni-MH rechargeable batteries
Alkaline battery life	Recording: 72h (LP mode) Playback: 68h via earphones

Dimensions

WxHxD	108 x 39 x 16.8mm
Weight	71g
Housing colour	Grey
Housing material	Plastic

Languages

Menu languages	JP/EN/FR/DE/IT/ES/RU/PL/ BU/CS/SV/NL/DA/CN
----------------	---

Hardware Security

Lock single files	Yes
-------------------	-----

Operating Systems & Requirements

Windows	Operating system: Windows XP (SP2 or later), Windows Vista, Windows 7
Macintosh	Operating system: Mac OS X 10.4.11 - 10.7