




REV.	DATE	ECR NO.	DESCRIPTION
NC	06/05/10	—	INITIAL RELEASE



RECOMMENDED CABLE STRIPPING DIM'S

NOTE:

1. CRIMPED FERRULE
HEX CRIMP SIZE .178"

11	NUT	BRASS	NICKEL	1
10	FERRULE	BRASS	NICKEL	1
9	WASHER	BRASS	NICKEL	1
8	RING	DELIRIN	NATURAL	1
7	RETAINER RING	BRASS	NICKEL	1
6	GASKET	RUBBER	RED	1
5	CONTACT PIN	BRASS	GOLD	1
4	INSULATOR	DELIRIN	NATURAL	1
3	BARREL	BRASS	NICKEL	1
2	HOUSING	BRASS	NICKEL	1
1	SHELL	BRASS	NICKEL	1
	DESCRIPTION	MATERIAL	FINISH	QTY

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE
IN MILLIMETERS. DIMENSIONS IN [] ARE IN
INCHES AND FOR CUSTOMER REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED
TOLERANCES FOR MILLIMETERS ARE:

0.5 - 8mm	± 0.20mm
8 - 30mm	± 0.40mm
30 - 120mm	± 0.50mm

UNLESS OTHERWISE SPECIFIED
TOLERANCES FOR INCHES ARE:

.020 - .315	= ± 0.007"
.315 - 1.180	= ± 0.015"
1.180 - 4.724	= ± 0.020"

DO NOT SCALE DRAWING

APPROVALS		DATE		Amphenol Connex				
DRAWN	J.CHENG	06/05/10						
CHECKED								
ISSUED								
SHEET	1 OF 1							
				PART DESCRIPTION				
				TNC R/A CRIMP PLUG (FOR RG-179/U,187A/U CABLE)				
				PART NO.				
				122149				
CAD FILE				DWG. NO.		REV.	SIZE	SCALE
C:/CONNEX/122149.DWG				122149.DWG		NC	A	NA