



Features

- 1 - 5 pole terminal strip with 5x20mm fuse holder to IEC257
 - Interlocking fuse holder CFTBN/1
 - Anti-rotation spigot
 - IP20 finger protection
 - Cable entry 4mm² (2.5mm² with wire protector)
 - Wire protector on fuse terminal as standard
 - Standard 1 to 5 pole with earth screw, without wire protectors
 - Version 2 – 5 WP without earth, with wire protector on all poles
 - Version 3 – 5 EWP with earth, wire protector on all poles but earth
 - Version 3 – 5 NE without earth, without wire protectors
 - Meets creepage and clearance requirements of IEC (8mm)
 - 16mm fixing pitch
 - Screw/dust protection cover available
- 
- CFTBN/3C**
- CFTBN/5C**
- | Type No. |
|----------|
| CFTBN/3C |
| CFTBN/5C |




Type No.	
CFTBN/3C	3 pole cover
CFTBN/5C	5 pole cover

Specification

Voltage rating:	Fuse holder 250Vac, terminal 450Vac
Current rating:	Fuse holder 13Amp, terminal 20Amp
Working temperature:	-20°C to 125°C
Short period:	160°C
Moulding:	UL94-V0 flame retardant PA 66

CFTBN series



On CFTBN/1
spigot to
mounting
hole =
10mm

Type No.	Poles	Type No.	Poles
CFTBN/1	1	CFTBN/3EWP	3 with wire protector & earth screw (no WP on earth connection)
CFTBN/2	2	CFTBN/4EWP	4 with wire protector & earth screw (no WP on earth connection)
CFTBN/3	3 with earth screw	CFTBN/5EWP	5 with wire protector & earth screw (no WP on earth connection)
CFTBN/4	4 with earth screw	CFTBN/3EWPg	3 with wire protector & earth screw
CFTBN/5	5 with earth screw	CFTBN/4EWPg	4 with wire protector & earth screw
CFTBN/3NE	3 no earth screw facility	CFTBN/5EWPg	5 with wire protector & earth screw
CFTBN/4NE	4 no earth screw facility		
CFTBN/5NE	5 no earth screw facility		
CFTBN/2WP	2 with wire protector/ no earth screw		
CFTBN/3WP	3 with wire protector/ no earth screw		
CFTBN/4WP	4 with wire protector/ no earth screw		
CFTBN/5WP	5 with wire protector/ no earth screw		

Terminal:	Brass, nickel plated
Wire protector/fuse clip:	Phosphor bronze
Fuse holder:	5 x 20mm glass or ceramic
Screws:	M3, 6 μ zinc, colour passivated and tropicalised
Approvals:	Semko, Fimko, VDE, IMQ, Nemko, UL

Features


- 2 or 3 pole terminal block
 - Accepts 5x20mm & 6.3x25mm (1"x1/4") fuses
 - To IEC257
 - Anti rotation spigot
 - IP20 finger protection
 - Cable entry 10mm² (3x1.5mm² or 2x2.5mm²)
 - Meets creepage and clearance requirements of IEC (8mm)
 - 16mm fixing pitch
 - 2 pole supplied in 3 pole housing
 - Supplied complete with earth screw and washer
- 



Specification

Voltage rating:	Fuse holder 250Vac, terminal 450Vac
Current rating:	Fuse holder 13Amp, terminal 20Amp
Working temperature:	-20°C to 125°C
Moulding:	UL94-V0 flame retardant PA66
Terminal:	Brass, nickel plated
Fuse clip:	Phosphor bronze
Fuse size:	5x20mm & 6.3x25mm (1"x1/4") glass or ceramic
Screws:	M3.5, 6μ zinc colour passivated and tropicalised
Approvals:	CE
Terminal Marking:	L=live/ ≠(earth sign) =Earth/N=neutral

CMFTB series



Type No.	Poles
CMFTB/2	2
CMFTB/3	3