


ITX 19 L
SCREWDRIVER BIT SOCKET 1/2" for recessed TORX® head screws, long pattern

- ✓ Square drive as per DIN 3120 - C 12.5, ISO 1174, with ball retaining groove
- ✓ Hand-operated, knurled grip
- ✓ Chrome-plated
- ✓ With pressed-in pin in GEDORE vanadium special steel, gun-metal finish
- ✓ TORX® = reg. trademark of Acument Intellectual Properties, LLC. USA

12.5

1/2"



Code	No.	Φ	mm	mm	L ₁	L ₂	d	mm	mm	£
6188020	ITX 19 L T20-100	T20	M4 - M5	3.86	100	62	22.5	95	5	
6188100	ITX 19 L T25-100	T25	M4,5 - M5	4.43	100	62	22.5	95	5	
6188370	ITX 19 L T27-100	T27	M4,5 - M6	4.99	100	62	22.5	96	5	
6152500	ITX 19 L T30-100	T30	M6 - M7	5.52	100	62	22.5	96	10	
6152690	ITX 19 L T40-100	T40	M7 - M8	6.65	100	62	22.5	96	10	
6155870	ITX 19 L T45-100	T45	M8 - M10	7.82	100	62	22.5	98	10	
6158700	ITX 19 L T50-100	T50	M10	8.83	100	62	22.5	124	10	
6159940	ITX 19 L T55-100	T55	M12	11.22	100	62	23.0	151	10	
6188450	ITX 19 L T60-100	T60	M14	13.25	100	60	24.7	197	5	
6105180	ITX 19 L T70-100	T70	M16	15.55	100	60	28.0	277	5	

ITX 19 B
SCREWDRIVER BIT SOCKET 1/2" for recessed TORX® head screws with pilot

- ✓ Square drive as per DIN 3120 - C 12.5, ISO 1174, with ball retaining groove
- ✓ Hand-operated, knurled grip
- ✓ Chrome-plated
- ✓ With pressed-in pin in GEDORE vanadium special steel, gun-metal finish
- ✓ TORX® = reg. trademark of Acument Intellectual Properties, LLC. USA

12.5

1/2"




Code	No.	Φ	mm	mm	L ₁	L ₂	d	Bore	mm	mm	£
6192720	ITX 19 B T20	T20	M4 - M5	3.86	55	17	22.5	1,55 x 1,86	75	5	
6195660	ITX 19 B T25	T25	M4,5 - M5	4.43	55	17	22.5	1,93 x 2,04	75	5	
6196390	ITX 19 B T27	T27	M4,5 - M6	4.99	55	17	22.5	2,18 x 2,29	76	5	
6200170	ITX 19 B T30	T30	M6 - M7	5.52	55	17	22.5	2,56 x 2,92	76	5	
6200410	ITX 19 B T40	T40	M7 - M8	6.65	55	17	22.5	2,92 x 3,28	91	5	
6200840	ITX 19 B T45	T45	M8 - M10	7.82	55	17	22.5	3,45 x 3,68	92	5	
6201300	ITX 19 B T50	T50	M10	8.83	55	17	23.0	3,83 x 3,78	105	5	
6202700	ITX 19 B T55	T55	M12	11.22	55	15	24.7	4,85 x 4,79	133	5	
6203270	ITX 19 B T60	T60	M14	13.25	56	16	28.0	5,63 x 7,87	182	5	

IS 19
SCREWDRIVER BIT SOCKET 1/2" for slotted head screws

- ✓ Square drive as per DIN 3120 - C 12.5, ISO 1174, with ball retaining groove
- ✓ Hand-operated, knurled grip
- ✓ Chrome-plated
- ✓ With pressed-in pin in GEDORE vanadium special steel, manganese-phosphated
- ✓ Blade as per DIN ISO 2380-1, Form B

12.5

1/2"




Code	No.	mm	mm	L ₁	L ₂	d	mm	mm	£
6161760	IS 19 6,5x1,2	1.2	6.5	60	22	22.5	71	10	
6656060	IS 19 8x1,2	1.2	8.0	60	22	22.5	80	5	
6656140	IS 19 10x1,6	1.6	10.0	60	22	22.5	115	5	
6656220	IS 19 12x2	2.0	12.0	60	22	23.0	110	5	
6162140	IS 19 14x2,5	2.5	14.0	60	20	24.7	138	5	
6656490	IS 19 16x2,5	2.5	16.0	60	20	28.0	190	5	
6656570	IS 19 18x2,5	2.5	18.0	60	20	27.0	193	10	

IKS 19
SCREWDRIVER BIT SOCKET 1/2" for cross-slotted head screws PH

- ✓ Square drive as per DIN 3120 - C 12.5, ISO 1174, with ball retaining groove
- ✓ Hand-operated, knurled grip
- ✓ Chrome-plated
- ✓ With pressed-in pin in GEDORE vanadium special steel, gun-metal finish
- ✓ Tip as per DIN ISO 8764-1 PH

12.5

1/2"




Code	No.	Φ PH	L ₁	L ₂	d	mm	mm	£
6656650	IKS 19 2	2	60	22	22.5	77	10	
6656730	IKS 19 3	3	60	22	22.5	92	10	
6656810	IKS 19 4	4	60	22	23.0	106	10	

IKS 19 PZD
SCREWDRIVER BIT SOCKET 1/2" for cross-slotted head screws PZ

- ✓ Square drive as per DIN 3120 - C 12.5, ISO 1174, with ball retaining groove
- ✓ Hand-operated, knurled grip
- ✓ Chrome-plated
- ✓ With pressed-in pin in GEDORE vanadium special steel, gun-metal finish
- ✓ Tip as per DIN ISO 8764-1 PZ

12.5

1/2"




Code	No.	Φ PZ	L ₁	L ₂	d	mm	mm	£
6156680	IKS 19 PZD 2	2	60	22	22.5	77	10	
6156760	IKS 19 PZD 3	3	60	22	22.5	91	10	
6156840	IKS 19 PZD 4	4	60	22	23.0	108	5	

IN 19
SCREWDRIVER BIT SOCKET 1/2" for in-hex screws

- ✓ Acc. to DIN 7422
- ✓ Square drive as per DIN 3120 - C 12.5, ISO 1174, with ball retaining groove
- ✓ Hand-operated, knurled grip
- ✓ Chrome-plated
- ✓ With pressed-in pin in GEDORE vanadium special steel, manganese-phosphated
- ✓ **IN 19 17** for oil filter and drain plug screws
- ✓ * not standardised

12.5

1/2"



mm

Code	No.	*	mm	L ₁	L ₂	d	mm	mm	£
6153070	IN 19 4	*	4	60	22	22.5	68	10	
6153150	IN 19 5	*	5	60	22	22.5	69	10	
6153230	IN 19 6		6	60	22	22.5	70	10	
6153310	IN 19 7		7	60	22	22.5	75	10	
6153580	IN 19 8		8	60	22	22.5	82	10	
6153660	IN 19 9	*	9	60	22	22.5	91	10	
6153740	IN 19 10		10	60	22	22.5	99	10	
6153820	IN 19 12		12	60	22	23.0	113	10	
6153900	IN 19 14		14	60	20	24.7	149	10	
6154040	IN 19 17	*	17	60	20	28.0	210	10	
6154120	IN 19 19	*	19	60	20	27.0	222	10	