



# T&B®

## Rigid/IMC Conduit Fittings T&B Catalog Number:

UPC Number:	3994
Status:	78621003994
Description:	Active

3 in. Threaded insulated Grounding Bushing, Aluminum-Electro Zinc Plated, wire range-6-4/0, thermoplastic insulator. For use with Rigid/IMC Conduit.

### Application

For quick installation of bonding jumper to multiple metal conduits (Rigid and IMC).

Designed to bush conductors and prevent insulation damage.

### General

Trade Size (inches)	3
Material	Malleable Iron
Finish	Electro Zinc Plated
Wire Range	6-4/0

### Dimension Information

Bushing Diameter (inches)	4.234
Throat Diameter (inches)	2.761
Lug Length (inches)	2.23
Swing Radius (inches)	3.287
Bushing Height (inches)	0.975
Conduit Size (inches)	3

### Specifications

3dmodel	Available on Website
---------	----------------------

### Packaging

Package in Units	5
T&B Sold in UOM	Each
T&B Weight Per UOM	84 lbs. per 100

### Application Support

T&B Instruction Sheets	ta00375-tb2
------------------------	-------------

### Notes

Available with DURA-PLATE Finish

### Certifications

RoHS Compliance	No
-----------------	----

### Certifications



File Nbr:

E 3060

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:[techsupport@tnb.com](mailto:techsupport@tnb.com)