





71918-YXXZLF

- TOTAL NB OF POSITIONS, SEE SHEET 2

2= LOW PROFILE LATCH

d - LEGAL STATEMENT: SEE GS-47-0004.




mat'l. code SEE NOTES					surface ISO 1302 ✓		tolerance ISO 406 ISO 1001		projection 		product family QUICKIE			
ltr	ecn	no	dr	date	tolerances unless otherwise specified					 mm scale 2:1	title SHR.EL.HEADER STR DR TMT			
Y	F12-0838	LMU	12.12.06	angles linear		.X ±0.3								
AA	B-16776	LMU	14.01.23			.XX ±0.13								
						.XXX ±0.05								
			dr	D.LE		01.01.24			dwg no		sheet 1 of 2		size A3	
V			F08-0146	YOV	08.04.11	enrg	JM.C		01.01.24					
W			F09-0232	LMU	09.12.15	chr	JF.N		01.01.24					
X			F12-0011	LMU	12.02.06	appd	JM.C		01.01.24					
sheet	revision		AA	V										
index	sheet		1	2										

PRODUCT NUMBER	SIZE	LATCHING AVAILABILITY	MISSING PIN POSITIONS
71918-X06(B)(LF)	2x3	0/1/2	
71918-X08(B)(LF)	2x4	0/1/2	
71918-X10(B)(LF)	2x5	0/1/2	
71918-X14(B)(LF)	2x7	0/1/2	
71918-X16(B)(LF)	2x8	0/1/2	
71918-X18(B)(LF)	2x9	0/1/2	
71918-X20(B)(LF)	2x10	0/1/2	
71918-X26(B)(LF)	2x13	0/1/2	
71918-X27(B)(LF)	2x13	0/1/2	PIN 21 & 22
71918-X28(B)(LF)	2x13	0/1/2	PIN 5 to 12
71918-X30(B)(LF)	2x15	0/1/2	
71918-X34(B)(LF)	2x17	0/1/2	
71918-X35(B)(LF)	2x17	0/1/2	PIN 2 & 3
71918-X40(B)(LF)	2x20	0/1/2	
71918-X44(B)(LF)	2x22	0/1/2	
71918-X50(B)(LF)	2x25	0/1/2	
71918-X51(B)(LF)	2x25	0/1/2	PIN 39 to 46
71918-X60(B)(LF)	2x30	0/1/2	
71918-X64(B)(LF)	2x32	0/1/2	


PLATING :

- 0.76µm GOLD/GXT
(PdNi WITH GOLD FLASH) ON CONTACT AREA
3.81µm TIN-LEAD ON TAIL
UNDERPLATE : 1.27µm Ni MIN
- WHEN SUFFIX LETTER "LF" IS REQUIRED,
2µm MIN MATTE TIN OVER 1.27µm MIN
NICKEL IS PROVIDED INSTEAD OF TIN-LEAD

PIN POSITION INDICATION FOR POLARIZED VERSIONS



LATCHING FEATURES :



1= STANDARD LATCH

2= LOW PROFILE LATCH

mat'l. code				surface	tolerance	projection	product family
				ISO 1302	ISO 406 ISO 1101		QUICKIE
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
R	F07-0195	LMU	07.05.25	angles	.X ±0.3	mm	SHR.EL.HEADER
S	F08-0146	YOV	08.04.11	linear	.XX ±0.15		STR DR TMT
T	F12-0011	LMU	12.02.06		.XXX ±0.05	scale 2:1	
U	F12-0838	LMU	12.12.06	dr	D.LE		dwg no
V	B-16776	LMU	14.01.23	engr	JM.C		71918
				chr	JF.N		sheet 2 of - size
				appd	JM.C		A3
							type
							CUSTOMER Drawing
sheet index	revision sheet						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI:

[71918-144](#) [71918-210-SP](#) [71918-220](#) [71918-226](#) [71918-010](#) [71918-016](#) [71918-026](#) [71918-034](#) [71918-040](#)
[71918-234](#) [71918-260](#) [71918-440](#)