



Heyco® Glossy Plugs

Mounting Hole Diameter Range: .187" (4,7 mm) to 2.000" (50,8 mm)

- **Smooth, glossy head** provides easy glide and shiny finish.
- Close unneeded panel openings.
- Quick and easy installation.
- Locking fingers in fractional increments up to the maximum panel thickness.
- Multiple sizes for use in .187" (4,7 mm) to 2.000" (50,8 mm) diameter holes.
- Lock firmly in panel up to .125" (3,2 mm) thick.

MOUNTING HOLE DIAMETER		PART NO.			DESCRIPTION	PART DIMENSIONS			
in.	mm.	Black	White	Colors xx**		A Head Diameter		B Overall Height	
						in.	mm.	in.	mm.

Single Locking Step for Panel Thickness up to .062" (1,6 mm)

.187	4,7	2590	2591	2592xx	DP 187*	.250	6,4	.234	5,9
.250	6,4	2600	2601	2602xx	G 250	.312	7,9	.312	7,9
.312	7,9	2610	2611	2612xx	G 312	.375	9,5		

Multiple Locking Steps for Panel Thickness up to .125" (3,2 mm)


.375	9,5	2620	2621	2622xx	G 375	.468	11,9	.406	10,3
.437	11,1	2630	2631	2632xx	G 437	.531	13,5		
.500	12,7	2640	2641	2642xx	G 500	.563	14,3		
.562	14,3	2650	2651	2652xx	G 562	.656	16,7		
.625	15,9	2660	2661	2662xx	G 625	.734	18,6		
.750	19,1	2680	2681	2682xx	G 750	.859	21,8	.453	11,5
.875	22,2	2700	2701	2702xx	G 875	.953	24,2		
1.000	25,4	2710	2711	2712xx	G 1000	1.125	28,6		
1.093 - 1.125	27,8 - 28,6	2720	2721	2722xx	G 1093	1.218	30,9		
1.187	30,1	2730	2731	2732xx	G 1187	1.312	33,3		
1.375	34,9	2760	2761	2762xx	G 1375	1.486	37,7	.453	11,5
1.500	38,1	2770	2771	2772xx	G 1500	1.609	40,8		
1.750	44,4	2780	2781	2782xx	G 1750	1.875	47,6		
2.000	50,8	2795	2796	***	G 2000	2.127	54,8		

Standard color black. Consult Heyco for other colors (see below).



*Convex, glossy finished head tapers to a thin edge.

** "xx" indicates that, following the color match process, Heyco adds a two letter suffix to the Root Part No. shown. This suffix will identify your particular CUSTOM Color selection. Consult Heyco for molded nylon color chips for accurate matching. For details as well as information regarding our Stock Colors, see page 45.

***Consult Heyco for Root Part No.



SINGLE PANEL THICKNESS DESIGN



MULTIPLE PANEL THICKNESS DESIGN

Quick Specs

Material Certifications

Flammability Rating
Temperature Rating



Nylon 6/6
Recognized under the Component Program of Underwriters' Laboratories, File E51579
Certified by Canadian Standards Association, File 8919
94V-2
-40°F (-40°C) to 221°F (105°C)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[1311](#) [1316](#) [1312](#) [1309](#) [1319](#) [1305](#) [1301](#) [1303](#) [1300](#)