

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex			
7	HEX NUT	BRASS	NICKEL	1		DRAWN	M.ZHANG	09/24/09					
6	LOCK WASHER	BRASS	NICKEL	1		CHECKED			PART DESCRIPTION BNC BULKHEAD JACK TO PUSH-ON PLUG ADAPTOR				
5	RETAINER RING	BER. COPPER	NICKEL	1		ISSUED							
4	INSULATOR	PTFE	NATURAL	1		SHEET	1 OF 1						
3	CONTACT PIN	BER. COPPER	GOLD	1						PART NO. 112769			
2	LOCK RING	BRASS	NICKEL	1									
1	BODY	BRASS	NICKEL	1						DWG. NO. 112769.DWG REV. NC SIZE A SCALE NA			
DESCRIPTION		MATERIAL	FINISH	QTY	CAD FILE		C:/CONNEX/112769.DWG						