


BG-P TYPE



ITEM NO.	A	B	C
BG-10P	7.4±0.4	10.2±0.4	2.64
BG-14P	10.7±0.4	14.1±0.4	2.04
BG-16P	10.7±0.4	16.0±0.4	3.30
BG-18P	13.8±0.4	17.5±0.4	3.10
BG-20P	14.1±0.4	20.0±0.4	3.70
BG-22P	17.2±0.4	22.0±0.4	3.10
BG-25P	18.3±0.4	25.0±0.4	4.10
BG-26P	21.2±0.4	25.8±0.4	3.10
BG-32P	24.3±0.4	32.0±0.4	3.61
BG-34P	28.7±0.4	34.0±0.4	3.10
BG-40P	31.2±0.4	40.0±0.4	4.12
BG-42P	34.9±0.4	42.0±0.4	3.10
BG-48P	40.0±0.5	48.0±0.5	2.85
BG-50P	39.6±0.5	50.0±0.5	4.85
BG-55P	47.5±0.5	54.5±0.5	2.0
BG-60P	52.0±0.4	60.0±0.4	5.80
BG-76P	62.0±0.4	76.0±0.4	5.80
BG-89P	80.0±0.4	89.0±0.4	5.80



		MATERIAL		ITEM NO.	
		P.E.		BG-P TYPE	
SCALE		FINISH		NAME	
				FLEXIBLE CONDUIT	
△ (. .)		TOLERANCE±0.5mm		△ 04-02-2008 DATE	
				REVISIONS K003	
				R.NO.	

