


模具編號:
內模:A-TDB008
外模:A-TDB007
螺絲模:A-TSW003



WIRING LIST

P1	1	2	3	4	5	6	7	8	9	SHELL
P2	1	2	3	4	5	6	7	8	9	SHELL

REMARK:

- 1.CABLE: 9C×28AWG(7/0.127) B.C INSULATION: PVC+DRAIN WIRE: 26AWG (7/0.16)+AL/MYLAR+OUTER JACKET:PVC COLOR: BEIGE(A-K0) OD=ø5.0±0.2mm. NON-UL .
- 2.CONNECTOR: P1: DB 9P MALE PIN:G/F ;SHELL:NICKEL PLATED.
P2: DB 9P FEMALE PIN:G/F ;SHELL:NICKEL PLATED.
- 3.HOOD: P1&P2 MUST BE 45P PVC MOLDED.COLOR:BEIGE(A-K0).
- 4.ELECTRICAL TEST:100% OPEN SHORT MISSWIRE TEST.

A02-0033-8(W01)	8CCBLW01100424AA	15000±200
A02-0033-7(W01)	8CCBLW01100422AA	500 ± 20
A02-0033-6(W01)	8CCBLW01100426BB	3000 ± 50
A02-0033-5(W01)	8CCBLW01100421BB	2000 ± 50
A02-0033-4(I01)	8CCBLI01100440AA	9000 ± 100
A02-0033-4(W01)	8CCBLW01100440AA	9000 ± 100
A02-0033-3(I01)	8CCBLI01100425AA	3000 ± 50
A02-0033-3(W01)	8CCBLW01100425AA	3000 ± 50
A02-0033-2(I01)	8CCBLI01100430AA	4500 ± 50
A02-0033-2(W01)	8CCBLW01100430AA	4500 ± 50
A02-0033-1(I01)	8CCBLI01100420AA	1800 ± 30
A02-0033-1(W01)	8CCBLW01100420AA	1800 ± 30
DWG. NO.	CUST. P/N	L ± T(mm)

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ACROX Co., LTD. AND SHALL NOT BE REPRODUCED COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ACROX Co., LTD. UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MILLIMETERS ANGULAR TOLERANCE: ±10°		APPD. 核准	REV. 審核	
		CUST 客戶	Maxxtro® CHKD. 校對	
		SCALE 比例	UNIT 單位 mm	DR. 製圖
		11/19' 09		
DIMENSIONS		TOLERANCE		
0.00 TO 30.00mm		±0.10mm		
30.01 TO 80.00mm		±0.13mm		
80.01 TO 150.00mm		±0.15mm		
150.01		±0.20mm		
TITLE 名稱		DB 9M/DB 9F CABLE		
DWG NO. 圖號		A02-0033		
MATERIAL 材質		FILE NAME 檔案名稱	SHEET 張	1/1
		REV. 更改	1.2	

A02-0033-9(W01)	8CCBLW01100421AA	1800 ± 30
DWG. NO.	CUST. P/N	L ± T(mm)